

Project: \_\_\_\_\_

Location: \_\_\_\_\_

Cat.No: \_\_\_\_\_

Type: \_\_\_\_\_


Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_

Notes: \_\_\_\_\_

### Ordering Guide

Example: PTH3030 P3 A

<b>Product Code</b>	PTH3030	Triple
<b>Post diameter</b>	P3 P4	3" Post Mount 4" Post Mount
<b>Finish</b>	A B H G J	Black White Bronze Verde Green



### Specifications

**HOUSING:**

6061-T6 Extruded Aluminum.

**FINISH:**

Thermoset polyester powdercoat is electrostatically applied after a five-stage conversion cleaning process and bonded by heat fusion thermosetting. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B117 specifications. For larger projects where a custom color is required, contact the factory for more information.

**MOUNTING:**

Extruded Aluminum Hub mounts to a 2 3/8" OD x 4" long (P2) [if applicable] or 3" OD x 4" long (P3) [if applicable] tenon and is secured with six (6) 3/8"-16 stainless steel set screws.

**WARRANTY:**

Three-year limited warranty.

**Height :**

12" (30.48 cm)

**Length:**

36" (91.44 cm)

**EPA:**

1.35 sq. ft.

