



Project: _____
 Location: _____
 Cat.No: _____
 Type: _____
 Lamps: _____ Qty: _____
 Notes: _____

Ordering Guide

Example: DWC2 A

Product Code	DWC2	Beacon
Finish	A	Black

Spacing Chart

Specifications

HOUSING:

Single-piece compression molded fiberglass reinforced polyester composite, factory pressure tested to ensure water will not wick or leak through. Gasketing is silicone. Fasteners are 300 series stainless steel. Two (2) 1/2" conduit inlets at bottom. Note: Watertight connectors and potting compound (by others) must be used to maintain a watertight seal at conduit entry points.

FINISH:

Composite is textured, pressure formed, molded-in-color.

OPTICAL ASSEMBLY:

Ribbed clear acrylic.

LAMPING:

20W maximum T3 bi-pin lamp. Lamp is included with fixture. Lower wattage lamps are acceptable.

ELECTRICAL ASSEMBLY:

Bi-pin socket type (G4) with 250° C high temperature teflon coated wire leads. Fixture is 12 volt. Internal electronic transformer has 120 volt input. Pre-wired with high temperature 18 AWG wire.

WARRANTY:

Ten-year limited warranty.

CERTIFICATIONS:

ETL listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations. Manufactured to ISO 9001:2008 Standards.

Height : 7 3/8" (188mm) **Width:** 5 5/16" (135mm) **Max. Weight:** 3 lb.

