

Project: _____


Location: _____

Cat.No: _____

Type: _____

Lamps: _____ Qty: _____

Notes: _____



Ordering Guide

Example: 197-EB 3 V ABS A B WHT 15

Product Code	197-EB	Street Sign
Fitter Size	3	3" Round
Lettering	V	Vinyl
Finish	ABS ACP ARD ASI BLK BRN BRZ FGN GRA IRN RBZ SRT VBZ VCP VGN VTC WBZ WHT	Antique Brass Antique Copper Antique Red Antique Silver Black Brown Bronze Forest Green Granite Ironstone Rustic Bronze Shadow Rust Verde Bronze Verde Copper Verde Vintage Copper Weathered Bronze White
Print	A B N	Single Sided Double Sided None
Vinyl Lettering Style	B	Block *1
Letter Color	WHT	White
Wording	15	Spaces (15)

*1 Vinyl Lettering Style Only

Specifications

CONSTRUCTION:

Extruded aluminum 24" x 6" sign with engineer grade reflective green vinyl both sides. attached to cast aluminum post fitter. (Sign has 23" x 4" lettering area on both sides.)

FINISH:

Resilient TGIC thermoset polyester powdercoat paint is electrostatically applied to every fixture. Specially formulated for Philips Outdoor Lighting, it provides UV protection, and the highest temperature rating in the industry. In addition to the standard color choices shown, a spectrum of custom colors is available.

MOUNTING:

Fits over 3" dia. post. (Post must be ordered separately.)

WARRANTY:

Three-year limited warranty.

197-EB Accessories

Street sign

Specifications

Height:

8 3/8"

Width:

24"

