



Project: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Cat.No: \_\_\_\_\_  
 Type: \_\_\_\_\_  
 Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_  
 Notes: \_\_\_\_\_

### Ordering Guide

Example: MSL18 A S7

<b>Product Code</b>	MSL18	
<b>Finish</b>	A	Black
	H	Bronze
	G	Verde
<b>Mounting</b>	S7	Mounting Stake

### Specifications

**HOUSING:**

Die-cast aluminum. Hidden fasteners and aluminum stem. Fasteners are 300 series stainless steel. 1/2" NPS male threads to screw onto accessory mounting stake or junction box, sold separately.

**FINISH:**

Thermoset polyester powdercoat is electrostatically applied after a five-stage conversion cleaning process and bonded by heat fusion thermosetting. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B117 specifications.

**LAMPING:**

27W maximum S-8 (1156) lamp. Lamp is included with fixture. Lower wattage lamps are acceptable.

**ELECTRICAL ASSEMBLY:**

Single contact bayonet (S-8). 12 Volt fixture is pre-wired with 3-ft pigtail of 18-2 AWG, 105° C, SPT-1W wire. Low voltage quick connector, catalog #LVC3 included for easy hook-up to the low voltage supply cable, not included. 12 Volt system requires remote transformer, not included.

**WARRANTY:**

Three-year limited warranty.

**CERTIFICATIONS:**

ETL Listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations. Manufactured to ISO 9001:2008 Standards.

**Height :** 19 1/2" (495mm)      **Width:** 4 1/2" (114mm)      **Max. Weight:** 1.5 lb.

