



FRAME-IN KIT



REFLECTOR TRIM

Project: _____
 Location: _____
 Cat.No: _____
 Type: _____
 Lamps: _____ Qty: _____
 Notes: _____

Complete Fixture consists of Reflector Trim & Frame-In Kit. Select each separately.

2002P1	Reflector Trims — See Individual Reflector Trim Specification Sheets							
	Open Downlight					Wall Washer	Open Wet Location	Enclosed Wet Location
Specular Reflector	Cone	Satin Cone	Baffles	Pinhole				
2045	2012	2008	2005	2011	2095	2084CD	2090	
2046	2012NM	2010NM	2005BNM		2096	2084WH		
2046CD	2013	2010	2005NM		2096CD			
	2013NM	2008NM	2005WH					
	2013BKNM							
	2013BK							
	2013CD							
	2013CDNM							
	2013WH							

Features

- 1. Mounting Frame:** .036" (#20 ga.) galvanized steel. Accommodates all ceilings up to 1" thick. Push-in/twist-out rotoclips hold reflector flush to ceiling.
- 2. Junction Box:** 4" x 3 1/2" x 2", .063" (#14 ga.) galvanized steel. U.L. listed for maximum of 8 No. 12 ga. 75° C through branch circuit conductors (60° C for end of run). Integral cable clamps permit attachment of nonmetallic Romex® or armored cable without need of additional connectors.
- 3. Mounting Bars:** .059" (#16 ga.) galvanized steel. 13" long bars extend to 27" with integral nailing tabs. Attaches to wood joist without need of accessories.
- 4. Socket Housing:** Aluminum or galvanized steel.

Options & Accessories

- Mounting Bars:** 1964 - 20" set of (2)
- T-Bar Ceiling Clips:** 1956 - set of (4)
- Plaster Ceiling Ring:** 1960 - 7/8" depth for wet plaster ceilings.
- 277V Remote Step-Down Transformer:** 7997 - 277V down to 120V, 300W maximum load
- Extra Thick Ceiling Ring (2" max):** 1967C

Labels

UL (Suitable for Damp Locations), I.B.E.W.

