

Day-Brite

CFI

by  Signify

Industrial

HCY

Sealed high bay



Modern industrial design, energy-saving technology

Functional high bay lighting has a new look with Day-Brite / CFI HCY LED sealed high bay luminaires.

You don't need to sacrifice smart looks for affordable, dependable lighting in your functional spaces anymore. This Sealed high bay delivers up to 33,000 lumens with efficacies up to 151 LPW. Bring your retail and institutional spaces to life with this cost-effective luminaire built to last with a corrosion-resistant finish.

Performance meets style – no more sacrifice, just great looks, dependability and energy-savings.

DesignLights Consortium qualified
Please see the DLC QPL list for exact catalog numbers (<http://www.designlights.org/QPL>)

HCY LED sealed high bay

Indoor Industrial Luminaire

Features

Construction

Die cast frame and driver containment housing.

Finish

Corrosion resistant black finish.

Performance

Field CCT and lumen selectable.

Lens

Clear polycarbonate lens protects LEDs.

Installation

Heavy duty hook provided for connection to customer-supplied suspension.

Wiring

Exposed leads for wiring connection with sleeving for environmental protection with 6' cord provided for power connection and dimming connection.

Lumen maintenance

Up to 70% (L70) at 50,000 hours.

Certifications

Components are RoHS compliant, IP65 rated and cULus listed for use in wet locations for -20C to 50C ambient.

Accessories (order separately)

- HCY2-PRSM 16" Clear polycarbonate reflector for HCY1421L
- HCY2-PRLG 16" Clear polycarbonate reflector for HCY2833L
- HCY-SURFACE BKT SM Surface mount bracket for HCY1421L
- HCY-SURFACE BKT LG Surface mount bracket for HCY2833L
- HCY-SENSOR Field installed microwave sensor
- HCY-REMOTE Remote hand-held programmer for HCY-SENSOR



Reflector Bracket Remote Sensor

NOTE: Many luminaire components, such as reflectors, lenses, sockets, lampholders, and LEDs are made from various types of plastics which can be adversely affected by airborne contaminants. If sulfur based chemicals, petroleum based products, cleaning solutions, or other contaminants are expected in the intended area of use, consult factory for compatibility.



Ordering guide


example: HCY1421L8CST-UN3-DIM

Series	Lumens ¹ (nom)	Color Temp. (K)	Voltage	Dimming
HCY		8CST -	UN3 -	DIM
HCY Sealed high bay	1421L 14,000/ 21,000 lm 2833L 28,000/ 33,000 lm	8CST 80 CRI, Color Select (4000/5000K)	UN3 Universal voltage (120-347V)	DIM 0-10V dimming


1. Nominal delivered lumens at 25°C ambient.

Dimensions

HCY14/HCY21



HCY28/HCY33



5 year limited warranty
Visit Signify.com/warranties
for more information on Signify's
standard 5-year limited warranty on
complete luminaire systems.



© 2021 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation
200 Franklin Square Drive,
Somerset, NJ 08873
Telephone 855-486-2216

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.