


Frame-in Kit



Reflector Trim

Project: _____
 Location: _____
 Cat.No: _____
 Type: _____
 Lamps: _____ Qty: _____
 Notes: _____

Complete Fixture consists of Reflector Trim & Frame-In Kit. Select each separately.

2000IC	Reflector Trims — See Individual Reflector Trim Specification Sheets						
	Open Downlight			Recessed		Enclosed	Open Wet
Frame-In Kit	Aperture Cone	Baffles	Satin Cone	Adjustable	Eyeball	Diffuser	Location
	2012 2012NM 2013 2013BKNM 2013BK 2013CDNM 2013CD 2013NM 2013WH 2013WD 2013WDP	2005 2005BNM 2005NM 2005WH	2008 2008NM 2010 2010NM	2027 2027BNM 2027NM 2029WH 2029BK 2029BKNM 2029CD 2029CDNM 2029CL 2029CLNM 2029GD 2029GDNM 2027WH	2022 2022WH	2090	2084WH 2084CD

Features

- Housing:** .032" aluminum. U.L. Listed for direct contact with thermal insulation. Access door for inspection of junction box.
- Mounting Frame:** .036" (#20 ga.) galvanized steel. Accommodates all ceilings up to 1" thick. Push-in/twist-out rotoclips hold reflector flush to ceiling.
- Junction Box:** 4" X 3 1/2" X 2"; .063" (#14 ga.) galvanized steel. U.L. listed for maximum of 4 No. 12 ga. 75° C through branch circuit conductors. Access door inside of housing allows easy inspection of wiring without removal of housing. Integral cable clamps permit attachment of nonmetallic Romex® or armored cable without need of additional connectors.
- Mounting Bars:** .059" (#16 ga.) galvanized steel. 13" long bars extend to 27" with integral nailing tabs. Attaches to wood joist without need of accessories.
- Socket Housing:** .036" (#20 ga.) galvanized steel.
- Socket:** Porcelain medium base; nickel plated screw shell. Pre-wired with #18 ga. SF1 leads to junction box.
- Thermal Protector:** Meets NEC and UL requirements. Located inside housing.

2000IC Lytecaster INC 3 3/4"

IC frame

Options and Accessories

Mounting Bars:	1964 - 20" set of (2)
T-Bar Ceiling Clips:	1956 - set of (4)
Plaster Ceiling Ring:	1959 - 7/8" depth for wet plaster ceilings
277V Remote Step	7997 - 277V down to 120V
Down Transformer:	300W max. load.
Extra Thick Ceiling Mounting Ring:	1967C

Labels

UL (Suitable for Damp Locations), I.B.E.W

Romex® is a registered trademark is General Cable Industries Inc.

