

**Day-Brite**

**CFI**

by  **Signify**

Linear

FluxStream luminaires

**interact**  
ready.



**Genuine convenience  
consistently supports  
your success**

# It all adds up

Now, more than ever, working efficiently is a critical component in the success of your projects, especially when it comes to lighting.



From planning and design, through installation, integration, and beyond — even small time-consuming tasks can add up to big project delays that prevent you from moving on to the next job.

At the same time, customer satisfaction is equally important, so you need robust solutions that look, perform and withstand equal to or beyond your customer's expectations.

This is why we expanded the rugged and reliable Day-Brite / CFI FluxStream luminaire family to include strip, industrial and wraparound luminaires.

Before, during, and after installation, you can trust the FluxStream luminaire family to help you quickly complete projects without hassles or troubleshooting, while delivering consistent comfort and long-term energy savings throughout the space.






FluxStream strip

# Convenience

## Add convenience before

The FluxStream linear strip family you already depend upon is now expanded to include industrials and wraparounds. The consistent, coordinated family selection provides you with mix & match flexibility while maintaining a similar aesthetic style and light output throughout the space.



FluxStream Wraparound

### FluxStream linear strip

- Efficacy: 114–133 lm/W
- Lengths: 2, 3, 4, 8 feet
- Lumen outputs: 2000lm–14000lm
- Color temperatures: 3000K, 3500K, 4000K, 5000K

### FluxStream linear industrial


- Efficacy: 126–134 lm/W
- Lengths: 4, 8 feet
- Lumen outputs: 4000lm–14000lm
- Color temperatures: 3000K, 3500K, 4000K, 5000K

### FluxStream linear wraparound

- Efficacy: 104–122 lm/W
- Lengths: 2, 4, 8 feet
- Lumen outputs: 2000lm–14000lm
- Color temperatures: 3000K, 3500K, 4000K, 5000K


### FluxStream strip

FSS




### FluxStream industrial

FSI



### FluxStream wraparound

FSW



----- Denotes light  
output direction



### Add convenience during

**FluxStream linear strip, industrial and wraparound luminaires have a consistent ordering nomenclature to save time when specifying and ordering, and offer quick, familiar and hassle-free installation.** All versions are dimmable using a variety of drivers, including 0-10V, Mark X, DALI and can be integrated with control systems for advanced functionality along with enhanced energy savings. Additionally, the luminaires accept an integrated emergency (EMLED) battery to provide standby light in the event of an unexpected power loss.

“EZ” models are available with FluxStream linear strip and wraparound luminaires to satisfy budget-conscious projects. See specifications for additional detail.

### Add convenience after


With a consistent look and consistent light output throughout any space, the broad FluxStream luminaire family creates comfortable spaces so that your customers are satisfied. Over time, FluxStream luminaires provide reliable, long-lasting performance with low maintenance, so you don't have to return to troubleshoot, and your customers will enjoy reduced maintenance costs.



*FluxStream strip*




*FluxStream industrial*



*FluxStream wraparound*








# Integrated sensor

## Reduce operating costs

In addition to convenience and consistency from FluxStream luminaires, your customers will enjoy the obvious benefits of LED technology – reduced lighting-related energy expenses and reduced operating expenses over the long lifetime of the luminaires.

For additional energy saving or code compliance, a Philips EasySense sensor is available integral to the luminaire that provides occupancy sensing, daylight harvesting, and task tuning.

\*Integrated sensor option not available in FluxStream EZ models.











## Product details


### FluxStream strip FSS



### FluxStream industrial FSI




### FluxStream wraparound FSW




## Ordering guide

Series	Length (nominal)	Lumens <sup>2</sup> (nominal)	Color	Voltage	Driver	Options
<b>FSS</b> <b>FSW</b>	2 2' length	<b>20L</b> 2000 lumens <b>30L</b> 3000 lumens	<b>830</b> 80 CRI, 3000K <b>835</b> 80 CRI, 3500K	<b>UNV</b> Universal voltage 120-277V <b>120<sup>4</sup></b> 120V <b>277<sup>4</sup></b> 277V <b>347</b> 347V	<b>DIM</b> 0-10V dimming <b>SDIM<sup>5,6</sup></b> Step dimming to 40% input power <b>XDIM<sup>4,5,6</sup></b> MarkX phase dimming <b>DALI<sup>7</sup></b> DALI	<b>EMLED<sup>5,8</sup></b> Factory wired Philips Bodine BSL310LP integrated emergency pack. Nominal 1100lm <b>IAP<sup>9</sup></b> Integral Interact Pro sensor, enables wireless connected lighting control <b>IAO<sup>9,10</sup></b> Integral Interact Office daylighting and occupancy sensor, enables wireless connected lighting control <b>SWZDT<sup>9</sup></b> Integral sensor, daylighting and occupancy sensing, advanced grouping with dwell time <b>PAF</b> Paint after fabrication (white) <b>LSXR10</b> 120-347V motion sensor, factory installed on end cap <b>LSXR10ADC</b> 120-347V motion sensor with photocell and hi/lo trim dimming, factory installed on end cap <b>PCSR</b> Pull chain switch right, 120V only, (FSW only) <b>PCSL</b> Pull chain switch left, 120V only, (FSW only) <b>BK</b> Matte black paint color (FSS and FSI only) <b>ST</b> Satin aluminum paint color (FSS and FSI only)
<b>FSS</b>	3 3' length	<b>30L</b> 3000 lumens				
<b>FSS</b> <b>FSI</b> <b>FSW</b>	4 4' length	<b>40L</b> 4000 lumens <b>55L</b> 5500 lumens <b>70L</b> 7000 lumens	<b>840</b> 80 CRI, 4000K <b>850<sup>3</sup></b> 80 CRI, 5000K			
<b>FSS</b> <b>FSI</b> <b>FSW</b>	8 8' length <sup>1</sup>	<b>80L</b> 8000 lumens <b>110L</b> 11000 lumens <b>140L</b> 14000 lumens				

### FluxStream EZ strip



### FluxStream EZ wraparound



## FluxStream EZ ordering guide

Series	Length (nominal)	Lumens <sup>2</sup> (nominal)	Color	Voltage	Options
	<b>4</b>	<b>40L</b>		<b>UNV</b>	
<b>FSSEZ</b> <b>FSWEZ</b>	4 4' length	<b>40L</b> 4000 lumens	<b>830</b> 80 CRI, 3000K <b>835</b> 80 CRI, 3500K <b>840</b> 80 CRI, 4000K	<b>UNV</b> Universal voltage 120-277	<b>EMLED</b> Factory wired Philips Bodine BSL310LP integral emergency pack. Nominal 1100 lm

- 8' is tandem (2) 4' lenses with single piece 8' body.
- Nominal delivered lumens at 25C ambient.
- Not available in 3' model.
- XDIM option must be specified with 120V or 277V option only.
- Not available in 2' or 3' model.

- Not available in 4' 70L model or 8' 140L model.
- DALI available up to 80L models only, consult factory for other options.
- EMLED on 8' models illuminates 4' section in emergency mode. EMLED not available on 2' models.
- Specify DIM driver with integral controls options.
- Not available in 8' 110L or 140L models.



## Accessories and options (order separately)



Accessory Catalog Code	Description	FSS strip	FSI industrial	FSW wraparound
FSTH	Sliding hanger bracket (pair)	X	X	X
SV5F12	12" Stem and canopy kit	X	X	X
SV5F18	18" Stem and canopy kit	X	X	X
SV5F24	24" Stem and canopy kit	X	X	X
SV5F36	36" Stem and canopy kit	X	X	X
SV5F48	48" Stem and canopy kit	X	X	X
FKR-126	Chain hanger set (pair)	X	X	X
DACHxx	Adjustable cable hanger kit (single)	X	X	X
DACHxx-1-SC	Adjustable cable hanger kit with white straight 18/3 cord (single)	X	X	X
DACHxx-1-CC	Adjustable cable hanger kit with white coiled 18/3 cord (single)	X	X	X
DACHxx-2-SC	Adjustable cable hanger kit with white straight 18/4 cord (single)	X	X	X
DACHxx-2-CC	Adjustable cable hanger kit with white coiled 18/4 cord (single)	X	X	X
DACHxx-1D-SC	Adjustable cable hanger kit with white straight 18/5 cord with dimming leads (single)	X	X	X
FSWJ	External continuous row joiner (one per joint).			X
LSXR10	Low bay pir motion sensor (120-277v)	X	X	X
LSXR10ADC	Low bay pir motion sensor with photocell and hi/lo trim dimming (120-277v)	X	X	X
FSSWG4	4' Wire guard (order two for 8' models)	X		
FSIWG4	4' Wire guard (order two for 8' models)		X	
FSSD2L	2' Diffuse replacement lens	X		
FSSD3L	3' Diffuse replacement lens	X		
FSSD4L	4' Diffuse replacement lens (order two for 8' models)	X		
FSID4L	4' Diffuse replacement lens (order two for 8' models)		X	
FSWD2L	2' Diffuse replacement lens			X
FSWD4L	4' Diffuse replacement lens (order two for 8' models)			X



