



Project: _____
 Location: _____
 Cat.No: _____
 Type: _____
 Lamps: _____ Qty: _____
 Notes: _____

Ordering Guide

Example: MU5 H

Product Code	MU5	Aluminum Pathlyte
Finish	H	Bronze

Spacing Chart

Specifications

HOUSING:

Die-cast aluminum. Stem is extruded aluminum. Roof has dual stainless steel hinge with stainless steel spring-lock for tool-less entry and relamping. 1/2" NPS male threads to screw onto accessory mounting stake or junction box, sold separately.

FINISH:

Thermoset polyester powdercoat is electrostatically applied after a five-stage conversion cleaning process and bonded by heat fusion thermosetting. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B117 specifications.

OPTICAL ASSEMBLY:

Frosted tempered glass sprinkler shield includes top and bottom silicone gaskets for tight seal. Underside of roof has white reflector, with center ALZAK® reflector for optimal light distribution.

LAMPING:

Lamp is not included. 100W maximum A19 lamp. Lower wattage lamps are acceptable.

ELECTRICAL ASSEMBLY:

4kv rated porcelain mini-can base. Nickel-plated screw shell with center contact. Fixture is pre-wired with 18 AWG black, white, and ground wires.

WARRANTY:

Three-year limited warranty.

CERTIFICATIONS:

ETL listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations. Manufactured to ISO 9001:2008 Standards.

Height : 25" (635mm) **Width:** 9" (229mm) **Max. Weight:** 5.56 lb.

