



Project: _____
 Location: _____
 Cat.No: _____
 Type: _____
 Lamps: _____ Qty: _____
 Notes: _____

Ordering guide

Example 1: DB30 A AO 12L E

Example 2: DB30 A

Product Code	Finish		Optics	Wattage		Voltage
DB30						
DB30 Aluminum Bollard LED	A H	Black Bronze	AO Symmetric	12L	9.5W LED	E 120V
DB30 Aluminum Bollard	A H	Black Bronze				

Specifications

Housing

356 HM high-strength, low-copper, proprietary cast aluminum alloy. Dome roof with die-cast aluminum louvers. Easy access to lamp. 5" dia. extruded aluminum with a wallthickness of 0.125". All non-ferrous fasteners prevent corrosion and ensure longer life.

Finish

Thermoset polyester powdercoat is electrostatically applied after a five-stage conversion cleaning process and bonded by heat fusion thermosetting. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B117 specifications. For larger projects where a custom color is required, contact the factory for more

Optical Assembly

Symmetric. Die-cast aluminum louvers with underside painted with highly reflective white powdercoat. Tempered glass globe.

Lamping

- LED 4Kv medium base porcelain socket A19.
- Incandescent Medium Base A19.

Electrical Assembly

LED is 2700K warm white, delivers 800 lumens, and is dimmable. Lamp life is rated at 25,000 hours. 120 volt only. 4Kv rated medium base porcelain socket. Key-slotted Ballast Assembly is mounted to an aluminum plate, which is mounted inside the base. Quick disconnects for easy installation and removal. 4kv rated medium base porcelain socket. Nickel-plated screw shell with center contact.

Installation & Mounting

Tube is mounted to the base plate with three (3) 5/16-18 flat head allen key stainless steel tamper-resistant screws.

Warranty

Three-year limited warranty.

Certifications

ATL listed to U.S safety standards for wet locations. cETL listed to Canadian safety standards for wet locations. Manufactured to ISO 9001:2008 Standards.

Height

30" (74cm)

Width

6" (15cm)

Bolt Circle

3" (8 cm)

Anchor Rods

Internal (3) 3/8" dia. x 8" long (1 cm x 20cm)

Base Diameter

5" (13cm)

Max. Weight

Powdercoat: 15 lbs

Max. Weight

CraftStone: 19 lbs

