



Project: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Cat.No: \_\_\_\_\_  
 Type: \_\_\_\_\_  
 Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_  
 Notes: \_\_\_\_\_

### Ordering Guide

Example: CUL6 S7 LED2W \_

<b>Product Code</b>	CUL6	Copper Pathlyte	
<b>Mounting</b>	S7	Mounting Stake	*1
<b>LED</b>	LED2W	LED Lamp	
<b>Finish</b>	_	Natural Copper	*2

\*1 Mounting stake option only available with Natural Copper Pathlyte.  
 \*2 When ordering Natural Copper, product code will read as CUL6.

### Specifications

**HOUSING:**

Spun solid copper roof with copper stem. Machined brass threaded adapter for tool-less relamping. 1/2" NPS male threads to screw onto accessory mounting stake or junction box, sold separately.

**FINISH:**

Natural Copper is bright polished, untreated copper. Color will age naturally to a fine dark copper patina.

**OPTICAL ASSEMBLY:**

Reflective white powdercoat on underside of roof. Frosted tempered glass lens.

**LAMPING:**

Philips 12V LED 1.2W Capsule lamp. Up to 88% energy savins when compared to a 10W Capsule halogen lamp. Long lifetime of 15,000 hours (B50,L70). Operating temperature range is between -20C and 35C (ambient). Suitable for use in enclosed luminaires where the case temperature (Tc) remains below Tc MAX. Total Lumens = 105lm Lamp is included with fixture. Lower wattage lamps are acceptable.

**ELECTRICAL ASSEMBLY:**

Bi-pin socket type (G4) with 250° C high temperature teflon coated wire leads. 12 Volt fixture is pre-wired with 3-ft pigtail of 18-2 AWG, 105° C, SPT-1W wire. Low voltage quick connector, catalog #LVC3 included for easy hook-up to the low voltage supply cable, not included. 12 Volt system requires remote transformer, not included.

**WARRANTY:**

5 year extended warranty

**CERTIFICATIONS:**

Manufactured to ISO 9001:2008 Standards. ETL listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations.

# CUL6 Copper Path light

## LED Accent

### Specifications

---

**Height :**  
16 1/4" (413mm)

**Width:**  
6" (152mm)

**Max. Weight:**  
2.75 lb

