

CHLORIDE

by ©signify

Step Lights

MSL Series – Mini Step Light

INSTALLATION INSTRUCTIONS

LED MINI STEP LIGHT

120VAC Input



READ AND FOLLOW ALL SAFETY INSTRUCTIONS

When using electrical, basic safety precautions should always be followed including the following.

1. Disconnect power at fuse or circuit breaker before installing or servicing.
2. Do not mount in hazardous locations, or near gas or electric heaters.
3. Do not let power cords touch hot surface.
4. Equipment should be mounted in locations and at heights where it will not be subjected to tampering by unauthorized personnel.
5. The use of accessory equipment not recommended by the manufacturer may cause an unsafe condition.
6. Do not use this equipment for other than intended use.
7. All servicing should be performed by a qualified personnel only.
8. All electrical connection must be in accordance with local codes, ordinances, and the National Electric Code. If you are unfamiliar with methods of installing electrical wiring, secure the services of a qualified licensed electrician.

SAVE THESE INSTRUCTIONS

Mounting Instructions

1. Unscrew face plate screws by screwdriver then remove face plate (see Fig 1).
2. Connect the fixture wires to J-box wires from building using wire nuts, connect the white wire to neutral, connect the black wire to hot wire (120VAC), connect green wire to ground wire (see Fig 2).
3. Install fixture on J-box by 2 bracket screws provided (see Fig 3).
4. Place face plate on fixture, put 2 pcs washer provided on screw then fixed face plate by 2 screws (see Fig 4).
5. Restore power at circuit breaker or fuse.
6. Finish installation.

Fig 1




Fig 2




Fig 3





Fig 4



Face Plate Styles



Vertical louver face



Horizontal louver face

How To Change Face Plate Direction

If need change face plate direction, please according below instruction.

These instruction also for photocell model.

1. Remove original vertical face plate.
2. Unscrew 2pcs bracket screws.
3. Adjust bracket 90 degree and assemble it on plastic case again, please noted use another 2 screw holes on bracket.
4. Use horizontal face plate instead of vertical face plate.

