

12 Flat  
Flutes

Project: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Cat.No: \_\_\_\_\_  
 Type: \_\_\_\_\_  
 Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_  
 Notes: \_\_\_\_\_

## Order guide

example: 754- 8 ABS B B D

Product Code	Pole Height	Finish	Outlet Location	Outlet Options	Tenon	Photoeye
<b>754</b>						
754	8' 10' 12' 14' 16'	ABS Antique Brass ACP Antique Copper ARD Antique Red ASI Antique Silver BLK Black BRN Brown BRZ Bronze FGN Forest Green GRA Granite IRN Ironstone RBZ Rustic Bronze SRT Shadow Rust VBZ Verde Bronze VCP Verde Copper VGN Verde VTC Vintage Copper WBZ Weathered Bronze WHT White	B 4" from Top of Base T 12" from Top of Pole	D Standard Duplex G GFI Duplex	N/A	B 120V C 208V - 277V

EPA values based on destructive break testing. For AASHTO ratings, contact factory.

## Pole Data

Pole Model	Pole Shape	Pole Type	Shaft Dimension	Pole Fluted	Anchor Base Shape	Bolt Circle	Base Dim (in)
754	Round	Straight	4	Fluted	round	7	17 x 18.75

Pole Family	Catalog Number	Nominal Height (ft)	Tenon Section (in)	Wall Thickness (in)	EPA Rating 80 MPH (sq. ft)	EPA Rating 100 MPH (sq. ft)	EPA Rating 110 MPH (sq. ft)	Anchor Bolts (in)
754	754-8	8	3	0.125	38.53	-	20.07	3/4-15 bs
754	754-10	10	3	0.125	26.48	-	13.55	3/4-15 bs
754	754-12	12	3	0.125	19.68	-	9.74	3/4-15 bs
754	754-14	14	3	0.125	15.7	-	7.61	3/4-15 bs
754	754-16	16	3	0.125	12.35	-	5.55	3/4-15 bs

## Specifications

### CONSTRUCTION:

Cast aluminum anchor base. Cast aluminum removable access door. Flat fluted post welded to base. Tenon secured to post top. Cast aluminum upper base welded to base & post.

### FINISH:

Resilient TGIC thermoset polyester powdercoat paint is electrostatically applied to every fixture. Specially formulated for Signify Outdoor Lighting, it provides UV protection, and the highest temperature rating in the industry. In addition to the standard color choices shown, a spectrum of custom colors is available.

### WARRANTY:


Please visit [www.signify.com/warranties](http://www.signify.com/warranties) for more details on structural and finish warranty.

### OUTLET:

GFI Duplex Outlet has dual-function indicator light, universal metal weatherproof cover. Weatherproof while in use. Heavy-duty all-metal construction. Lockable security cover. Meets NEC 406.9 (B). Weather resistant. Standard Duplex Outlet has universal metal weatherproof cover. Weatherproof while in use. Heavy-duty all-metal construction. Lockable security cover. Meets NEC 406.9 (B). Weather resistant.

# 754 Poles and Brackets

## Straight Round Fluted



The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract.



© 2019 Signify Holding. All rights reserved. This document contains information relating to the product portfolio of Signify which information may be subject to change. No representation or warranty as to the accuracy or completeness of the information included herein is given and any liability for any action in reliance thereon is disclaimed. All trademarks are owned by Signify Holding or their respective owners.

Signify North America Corporation  
200 Franklin Square Drive,  
Somerset, NJ 08873  
Telephone 855-486-2216

Signify Canada Ltd.  
281 Hillmount Road,  
Markham, ON, Canada L6C 2S3  
Telephone 800-668-9008