



The **C4XE Series** is a NEMA 4X Exit Sign. Featuring a reinforced polycarbonate housing, the C4XE series can be wall, ceiling or end mounted.

Project: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Cat.No: \_\_\_\_\_  
 Type: \_\_\_\_\_  
 Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_  
 Notes: \_\_\_\_\_

### Ordering guide

Example: C4XE-R-N-CT-W-1

Family	Letter Color	Battery	Self Diagnostics	Housing	Faces
<b>C4XE</b> NEMA 4X Exit	<b>R</b> Red <b>G</b> Green	<b>Blank</b> AC only <b>N</b> Nicad battery	<b>Blank</b> <b>CT</b> Self diagnostic	<b>W</b> White <b>B</b> Black	<b>1</b> Single <b>2</b> Double

### Specifications

#### Codes and standards

- UL listed to standard 924
- NEMA 4X, IP66 and NSF rated
- NFPA 101 (Life Safety Code)
- UL listed for wet locations (-20° C - 50° C)
- Meets CEC title 20 regulations

#### Power consumption

- All models dual voltage 120/277

#### Construction

- Housing constructed of reinforced polycarbonate
- High impact resistant, UV stabilized polycarbonate clear lens

#### Mounting

- Universal knockout pattern on back provided with gasket for watertight seal for wall mounting
- Polycarbonate mounting canopy included for ceiling or end mounting

#### Battery

- Maintenance-free, 4.8V rechargeable NiCd (NiCad) battery

### Electrical information

Catalog Number	Input Watts		Input Amps	
	120V	277V	120V	277V
<b>C4XE</b>	2.5W	2.5W	0.025A	0.010A

#### Electronics

- Charge rate/power "ON" LED indicator light and magnetic test switch for mandated code compliance testing
- Internal solid-state transfer switch automatically connects the internal battery to the LED board for minimum 90-minutes emergency illumination

#### Options

- Self-diagnostic feature performs monthly, biannual, and annual tests to ensure reliable operation and meet electrical and life safety codes

#### Warranty

- Five year limited warranty on all electronics and housing, battery prorated for 5 years

