

CHLORIDE

by Signify

Exit/Emergency


55 Series

Die cast aluminum exit sign



Project: _____
Location: _____
Cat.No: _____
Type: _____
Lamps: _____ Qty: _____
Notes: _____

Example: ER55L3R



Accessories

PVS2 – Polycarbonate Vandal Shield
WG4 – Wire Guard

Footnotes

¹ Not available in white housing with green letters.

codes and standards

- UL listed to Standard 924
- NFPA 101 (Life Safety Code)
- NFPA 70 (National Electric Code) and OSHA Standards California Energy Commission
- UL listed for damp location

construction and finish

- Available in matte black housing with brushed aluminum face or white with a powder coat paint finish.
- All signs provided with shallow canopy for ceiling or end installations.
- Extra stencil faceplate is provided for converting single face signs to double face signs in the field with ease. All units have concealed directional chevron indicators (knockouts).

installation

- Universal mounting (wall, side, or ceiling).
- Canopy and mounting hardware provided.
- Universal knockouts on backplate allow for wall mounting directly to J-Box.

electronics

- AC Only:
Red = 2.48 Watts, Green = 2.22 Watts
Emergency:
Red = 3.08 Watts, Green = 3.08 Watts
- Surge protection is standard on all models.
- Charging System is complete with low voltage disconnect, AC lockout, and brownout protection.
- 120/277 VAC Selectable Input.

battery

- Maintenance free sealed nickel cadmium has estimated service life of 8 to 10 years.
- Operating temperature range of 10°C to 40°C (50°F to 104°F).
- Provides 90 minutes of emergency illumination.

warranty

- Five full years on electronics and unit.



55 Die cast aluminum LED exit sign

dimensions

