



The **CWC Series** is a wet location Exit Combo. Featuring integrated LED lamps, the CWC series is an attractive combo that can be wall, ceiling or end mounted.

Project: \_\_\_\_\_

Location: \_\_\_\_\_

Cat.No: \_\_\_\_\_

Type: \_\_\_\_\_

Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_

Notes: \_\_\_\_\_

#### Ordering guide

Example: CWC-R-CT-W-1-RC

Family	Letter Color	Self Diagnostics	Housing	Faces	Remote
<b>CWC</b> Wet Location Combo	<b>R</b> Red <b>G</b> Green	<b>Blank</b> <b>CT</b> Self diagnostic	<b>W</b> White <b>B</b> Black	<b>1</b> Single <b>2</b> Double	<b>Blank</b> <b>RC</b> Remote

### Specifications

#### Codes and standards

- UL listed to standard 924
- NFPA 101 (Life Safety Code)
- UL listed for wet locations (0° C - 50° C)
- Meets CEC title 20 regulations

#### Lamps

- High brightness white LEDs
- 3.6W LED lamp heads x 2
- Adjustable lamp heads provide optimal center to center spacing

#### Power consumption

- All models dual voltage 120/277

#### Construction

- Housing constructed of 5VA flame retardant, UV stabilized polycarbonate
- High impact resistant, UV stabilized polycarbonate clear lens
- Corrosion resistant enclosure with engineering grade silicone gasket

#### Mounting

- Die cast aluminum canopy included for ceiling or end mounting
- Universal knock-out pattern on back plate for wall mount
- Knockouts provided for conduit feed applications

#### Battery

- Maintenance-free, 6V rechargeable NiCd (NiCad) battery

#### Electronics

- LED indicator light alerts occupant on battery condition (Green-normal, Red-check battery)
- Internal solid-state transfer switch automatically connects the internal battery to LED board and lampheads for minimum 90-minute emergency illumination

#### Options

- Self-diagnostic feature performs monthly, biannual, and annual tests to ensure reliable operation and meet electrical and life safety codes
- Remote capacity of up to 7.2 watts

#### Warranty

- Five year limited warranty on all electronics and housing, battery prorated for 5 years

