



Find your perfect lighting match

Compare Form Ten Precision and Comfort nominal lumens



Precision				Comfort			
CA20-P/MA20-P (NEW!) CP20-P/MP20-P (NEW!)		CA/MA 17L/22L CP/MP 17L/22L		CA20-C/MA20-C (NEW!) CP20-C/MP20-C (NEW!)		CA/MA 17L/22L CP/MP 17L/22L	
Selection	Nom. Lumens	Selection	Nom. Lumens	Selection	Nom. Lumens	Selection	Nom. Lumens
P01	2,500			C01	2,000	196L-450	2,500
P02	3,500			C02	3,000	196L-650	3,500
P03	5,000			C03	5,000		
P04	6,000	32L-450	6,000	C04	6,500	196L-1150	6,000
P05	8,000			C05	8,000	196L-1675	8,000
P06	10,000	32L-900	10,000	C06	10,000	196L-2100	10,000
P07	12,500	48L-700	12,500	C07	13,000		
P08	15,000	48L-900	16,000	C08	15,000		
P09	16,500			C09	16,000		
P10	18,000			C10	18,000		
P11	20,000	96L-560	21,000				
P12	22,000						
P13	25,000	96L-650	24,000				
P14	27,500						
P15	30,000						
P16	34,000						

Note: Nominal lumens based on 4000K, 70 CRI. See IES files for specific values.

© 2024 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

GENLYTE SOLUTIONS
a signify business

Signify North America Corp.
400 Crossing Blvd, Suite 600
Bridgewater, NJ 08807
Telephone: 800-555-0050

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone: 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.