



## A classic reimagined

The Gardco Form Ten LED family revitalizes a classic design with modern technology to meet the lighting needs of site and area applications.

With several color combinations available, the luminaire can be designed to draw attention or gracefully fade into its surroundings, complementing a variety of building motifs. Regardless of aesthetic preference, the high-performance **precision** or **ComfortEdge light engines** offer energy-saving advantages with low-glare lighting to create a comfortable environment.



### Construction

Cast aluminum housing and mounting elements provide durability and strength, while the spun aluminum roof shape creates a stylish, classic form reminiscent of traditional street lights. Quarter-turn latch provides toolless access to electrical compartment for quick and easy maintenance.

### Flexible Illumination

The perfect blend of classic styling and modern LED technology, Form Ten provides the benefits of ComfortEdge technology, reducing glare and creating a more comfortable environment for visitors. Precision optics available for higher mounting heights or applications requiring wider luminaire spacing and distributions for strict lighting control.

### Controls Solutions

Form Ten integrates the latest in lighting controls to maximize energy savings with Interact. Daylight sensing, motion detection, scheduled dimming, grouping, and remote management help maximize energy savings while providing a consistent experience between indoor and outdoor lighting control.

# Form Ten Arm Mount and Post Top

Cylindrical and semi-spherical series



## Cutting-edge technology, classic design

### Styling Options

- Post top or arm mount
- Cylinder or dome top
- ComfortEdge or precision optics
- Expanded color options
- Accent color optional

### Control Options

- Philips parking sensor for Interact connectivity
- Daylight sensing
- PIR or microwave motion detection
- 0-10V or DALI driver options
- 7-pin receptacle
- Zhaga socket

### Luminaire Specs

- Lumen range 2,500-34,000 lumens
- Efficacy up to 195 LPW with precision optics and 144 LPW with ComfortEdge optics
- Wide selection of CCT/CRI combinations
- Dark Sky Listed 3000K and below
- IP66 rated luminaire
- ANSI vibration rated
- Service Tag standard

### Available in textured finishes

<b>BK</b> Black	<b>BZ</b> Bronze	<b>DG</b> Dark Gray	<b>MG</b> Medium Gray	<b>WH</b> White
<b>BE2TX</b> Midnight Blue	<b>BE6TX</b> Ocean Blue	<b>BE8TX</b> Royal Blue	<b>RD2TX</b> Burgundy	<b>RD4TX</b> Scarlet
<b>GN</b> Green	<b>GN4TX</b> Blue Green	<b>GN6TX</b> Forest Green	<b>GN8TX</b> Dark Forest Green	<b>BG2TX</b> Sandstone



© 2024 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

**GENLYTE**  
**SOLUTIONS**  
a signify business

Signify North America Corp.  
400 Crossing Blvd, Suite 600  
Bridgewater, NJ 08807  
Telephone: 800-555-0050

Signify Canada Ltd.  
281 Hillmount Road,  
Markham, ON, Canada L6C 2S3  
Telephone: 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.