




Find your perfect lighting match

Compare PureForm and 161 nominal lumens



PWS Gen 3 Type 2 (NEW!)		PWS Gen 2 Type 2		161 Type 2	
Selection	Lumen Output	Selection	Lumen Output	Selection	Lumen Output
A01	2,500				
A02	4,000				
A03	6,000	48L-300	6,000		
A04	8,000	48L-400	8,000		
A05	10,000	48L-500	10,000		
A06	12,000	48L-600	12,000	46L-600	11,000
A07	14,000	48L-700	14,000		
A08	16,000	64L-600	16,000	46L-900	15,000
A09	18,000	64L-700	18,000		
A10	20,000	64L-800	20,000		
A11	22,000	64L-900	22,000	92L-600	22,000
A12	26,000				
A13	30,000			92L-800	27,000

Note: Nominal lumens based on 4000K, 70 CRI. See IES files for specific values.