

# Day-Brite CFI

Industrial

HRL High Bay

2x2 12000 to 24000 lm



## Experience Brilliant Illumination with Comfortable Light

This recessed high bay is a high efficiency lay-in style luminaire that provides exceptional light distribution for general areas. Available with high lumen output packages, the HRL is perfect for higher mounting heights or for applications where higher light levels are needed.

# HRL

## 2x2 Recessed high bay

The HRL 2x2 recessed high bay can be used in high ceiling applications like auto showrooms, retail areas, or gathering spaces. Exceptional, high-quality light is provided in a compact solution with two frosted lens options available. The flat lens creates a more traditional look, while the rounded lens creates a more even and aesthetic appeal.



Flat lens

Round lens



### Ordering guide

example: HRL24L840-UNV-DIM-LFA

| Family     | Lumens <sup>1</sup> (nom.)  | CRI/CCT   | Voltage   | Driver                     | Lens  | Options  |
|------------|---|---|---|----------------------------|---|--|
| <b>HRL</b> |   |   | -   | -                          | -   |  |
| HRL        | <b>12L</b> 12,000lm<br><b>18L</b> 18,000lm<br><b>24L</b> 24,000lm | <b>835</b> 80CRI, 3000K<br><b>840</b> 80CRI, 4000K<br><b>850</b> 80CRI, 5000K | <b>UNV</b> Universal, 120-277V<br><b>347</b> 347V | <b>DIM</b> Dimming (0-10V) | <b>LFA</b> Smooth flat frosted acrylic lens<br><b>LRA</b> Smooth rounded frosted acrylic lens | <b>F1</b> 3/8" flex, 3 wire 18 gauge 6'<br><b>F2</b> 3/8" flex, 4 wire 18 gauge 6'<br><b>F2/5W</b> 3/8" single flex, 5 wire 18 gauge 6' for dimmable luminaires<br><b>F2/6W</b> 3/8" single flex, 6 wire 18 gauge 6' for dimmable and emergency luminaires<br><b>BSL10LST<sup>2</sup></b> Factory wired 10W Philips Bodine integral emergency pack, nominal 1400lm to 1700lm |

1. Nominal delivered lumens at 25°C ambient.

2. Not available in 347V.

### Accessories (order separately)

- **FMA22** 2'x2' "F" mounting frame for NEMA "F" ceiling
- **HRL-LFA** 2'x2' Flat replacement lens
- **HRL-LRA** 2'x2' Rounded replacement lens

© 2024 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

**GENLYTE SOLUTIONS**  
a signify business

Signify North America Corp.  
400 Crossing Blvd, Suite 600  
Bridgewater, NJ 08807  
Telephone: 800-555-0050

Signify Canada Ltd.  
281 Hillmount Road,  
Markham, ON, Canada L6C 2S3  
Telephone: 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.