



Floodlighting

DuraForm LED

FLDS/FLDM/FLDL



The simple choice for your diverse needs

We get it... you need it all, versatility, durability, and performance. You must deliver on all levels. Gardco DuraForm floodlight is your solution.

Like all Gardco luminaires, DuraForm gives you peace of mind that you're recommending a quality product that meets all of those requirements. IP66, IK09, and Vibration rated, these floods are rugged enough to function well even in demanding environments, yet sleekly designed with a low profile. As an added bonus, they are backed by our exclusive Service Tag, which includes quick registration, remote monitoring, and spare parts identification, for assistance throughout the life of the product.



FLDS/FLDM/FLDL DuraForm floodlights

Slip Fitter
with external
cord shown



Slip Fitter with
internal wiring
shown



Yoke Mount
shown



Benefits

- Three sizes to provide the right light for your needs
- Three mounting options for a variety of applications
- Rugged construction to stand up to harsh environments
- Low profile design blends in with surroundings
- DLC Standard and DLC Premium configurations available

Features

- Lumen output ranges from 3,100 to 58,900
- Efficacies up to 149 lumens per watt
- Yoke and two Slip Fitter mountings available
- Nine distributions range from tight spot to rectangular medium
- Multiple control options range from simple to advanced
- Three standard finish options, with special finishes available

The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract.



© 2021 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation
200 Franklin Square Drive,
Somerset, NJ 08873
Telephone 855-486-2216

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.