

# KEENE

Site and Area

LytePro Area

LPA



## Your site lighting pro

Delivering on value and performance

**Keene LytePro Area (LPA) pole-mounted LED luminaire is a value-engineered solution with the perfect combination of affordability, quality and performance.**

Available in both make-to-stock and make-to-order options, LytePro is the flexible choice for any project. With its lightweight design and easy-to-install features, it is perfect for contractors and installers who want a hassle-free installation process. Keene LytePro Area is the ideal choice for your area lighting needs.



# LPA LytePro Area

## Product highlights

### Lumens

2,500–28,000lm

### DLC Premium

### Finish

White, medium gray, dark gray, bronze, and black

### Mounting

Integral arm mounts to round or square pole with wide bolt range for retrofits

### Controls

NEMA TLR or button photocell, motion sensor, wattage selector

**Interact ready** with Philips outdoor parking sensor

**Value-engineered solution** in a discreet fixture for a wide variety of outdoor spaces

### CCTs

3000K, 4000K, 5000K

### Distributions

Type 2, 3, 4, 5, internal shielding

### Voltage range

120–277 UNV & 347–480 HVU

**Stock or make-to-order** configurations available

### Energy-efficient fixture

Delivers up to 159 lumens per watt

### 5-year limited warranty

See [signify.com/warranties](https://www.signify.com/warranties) for complete details and exclusions



## Stocked luminaires – Ordering guide

Catalog Number	Description
912300004181	LPA-A06-740-T3-UNV-FAWS-TRPC-BZ
912300004183	LPA-A06-740-T4-UNV-FAWS-TRPC-BZ
912300004185	LPA-A11-740-T3-UNV-FAWS-TRPC-BZ
912300004187	LPA-A11-740-T4-UNV-FAWS-TRPC-BZ



One-board configuration




Two-board configuration

## Optical distributions


### LytePro T2

Type 2 Medium




### LytePro T3

Type 3 Medium




### LytePro T4

Type 4 Medium



### LytePro T5

Type 5 Medium



© 2024 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation  
400 Crossing Blvd, Suite 600  
Bridgewater, NJ 08807  
Telephone: 800-555-0050

Signify Canada Ltd.  
281 Hillmount Road,  
Markham, ON, Canada L6C 2S3  
Telephone: 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.