



## A vision of versatility

**Lumec OmniScape LED Post Top & Arm Mount** luminaires offer a clean and modern aesthetic while providing a foundation to build your vision and enhance any outdoor space. Along with providing uniquely customizable design flexibility and personalization, these luminaires deliver industry leading performance. This new family also allows for the integration of connected ready controls and technology.

### Modularity

#### Custom combinations

- Contemporary style
- Transitional style
- Historical style
- Post top mount
- Arm mount
- Skirt option & finial options
- LEDgine/ComfortEdge™ light engines
- 2700, 3000, 4000K CCT in 70/80 CRI
- Multiple distributions available
- 5-year limited warranty  
(for more info visit [signify.com/warranties](http://signify.com/warranties))

### Performance

#### LEDgine

- Post top: Up to 18,000lm (169 LPW)
- Arm mount: Up to 21,000lm (198 LPW)

#### ComfortEdge™

- Post top: Up to 16,000lm (132 LPW)
- Arm mount: Up to 18,000lm (152 LPW)

### Connectivity

#### Connected ready options & controls

- Zhaga certified driver (zD4i)
- Digitally addressable lighting interface driver (DALI)
- Sensor Ready driver (SR)
- 7-pin receptacle (TRLD7)
- Zhaga socket (TLRSR)
- Outdoor Multi-Sensor (OMS)
- Microwave Motion Sensors (MW)
- Field Adjustable Watt Selector (FAWS)
- Photoelectric Cell controls (PH)

# OSA/OSP OmniScape

## LED Post Top



Contemporary



Transitional



Historical

Mix components to create your own personal style and accentuate any outdoor space. OmniScape is designed to meet a broad range of Contemporary, Transitional or Historical lighting applications in a single family.

### Contemporary

#### Boasting a modern and refined aesthetic

This style incorporates a minimalist design language and soft volume transitions. Luminaire arms create an overall conical form, featuring gentle radii transitions and generous chamfers, adding character, as well as creating a sense of unity. This design is distinctively modern and aimed at contemporary architectural spaces, yet its minimalist appearance makes it suitable for a variety of outdoor areas.

### Transitional

#### Fusion of classic and modern elements

This style offers a stylish open frame design that pays homage to the historic luminaires that once illuminated the most renowned parks in North America. The smooth fitter and curved arms are inspired by the natural beauty of the calla lily, and flow seamlessly from the base to the light source. This design is adaptable and timeless, complementing any architectural style or outdoor setting.

### Historical

#### Past inspirations blended into present

This style features a sleek acorn-shaped body that evokes the classic style of historical luminaires without the need for a globe. The double arched arms connect the fitter to the roof, creating a smooth and elegant classic silhouette. The top section combines dome and cornice forms to add character and familiarity to the design. This design is suitable for both historical and modern settings, as it blends the past and present in a versatile way.



© 2024 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

**GENLYTE SOLUTIONS**  
a signify business

Signify North America Corp.  
400 Crossing Blvd, Suite 600  
Bridgewater, NJ 08807  
Telephone: 800-555-0050

Signify Canada Ltd.  
281 Hillmount Road,  
Markham, ON, Canada L6C 2S3  
Telephone: 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.