

CHLORIDE

by @ignify

Exit/Emergency

Accessories

Mounting plates, wire guards, vandal shields, & mounting shelves



Project: _____

Location: _____

Cat.No: _____

Type: _____













Lamps: _____ Qty: _____

Notes: _____

accessories

- For use with emergency lighting units, exit signs and remote lamp heads.

mounting plates

			<i>Thermoplastic Round Wedge Base / Bi-Pin</i>	<i>Thermoplastic Rectangular Wedge Base</i>	<i>Thermoplastic Round Sealed Beam Par 36</i>	<i>Chrome Plated Steel Sealed Beam Par 36 and M Heads</i>	<i>Heavy Industrial Sealed Beam Par 36</i>
		Chrome Single Head Fits Single Gang Wall Box Double Head Fits Three Gang Wall Box	MP1 MP3	MP1 MP3	MP1 MP3	MP1S MP3S	MP1 MP3
		Cast Aluminum Weatherproof Single Head Fits 3" or 4" round box Double Head Fits 3" or 4" round box	CRMP1 CRMP2	CRMP1 CRMP2	CRMP1 CRMP2	MP1WP MP2WP	CRMP1 CRMP2
		Cast Aluminum Weatherproof Fits Single Gang Box Single Head Double Head	CSMP1 CSMP2	CSMP1 CSMP2	CSMP1 CSMP2	MP1R MP2	CSMP1 CSMP2
		Thermoplastic 5" Diameter Mounts Dir. to Single Gang Wall Box Single Head, Gray Single Head, White Single Head, Black Weatherproof Option	MW1 MBLK1 -WP	MW1 MBLK1 -WP	MW1 MBLK1 -WP		MG1WP included*
		Double Head, Gray Double Head, White Double Head, Black Weatherproof Option	MW2 MBLK2 -WP	MW2 MBLK2 -WP	MW2 MBLK2 -WP		MG2WP included*
		Same As Above With 45° Mounting Holes, Fits 3.5" octagonal box Double Head, Gray Double Head, White Weatherproof Option	MW2S -WP	MW2S -WP	MW2S -WP		MG2SWP included*

* Mounting plates include weatherproof gasket.

Mounting plates, wire guards, vandal shields, & mounting shelves




wire guard and polycarbonate vandal shield

- Wire guards and the polycarbonate vandal shield provide protection from accidental or intentional abuse of emergency lighting equipment.
- Ideal for high traffic areas such as schools, gymnasiums and public buildings.

Cat.#	For Use With:	A	AA	B	BB	C
WG	TMF/TNM Series (200-450 W), ZMF Series (300 & 450 W), Max-Lite Series, Steel-Lite Series, 65X	20.0" (50.8cm)	26.0" (66.0cm)	20.0" (50.8cm)	26.0" (66.0cm)	11.0" (27.9cm)
WG3	SPU Series, CFX Series	10.0" (25.4cm)	12.0" (30.5cm)	10.0" (25.4cm)	12.0" (30.5cm)	5.5" (14.0cm)
WG4	Wall Mount Thermoplastic, Die Cast, & Steel Standard Exits SPU Series (fully recessed), Patron, SL Series	12.5" (31.8cm)	14.5" (36.8cm)	15.0" (38.1cm)	17.0" (43.2cm)	5.5" (14.0cm)
WG5	4X Series, 6M/2M Series, CMF/CNM Series (25-100 W), HZ Series, Steel-Lite Series, Symmetry Series (units), Symmetry Series Combination, TMF/TNM Series, (25-150 W), ZMF Series (100 W)	16.0" (40.6cm)	18.0" (45.7cm)	21.0" (53.3cm)	23.0" (58.4cm)	10.0" (25.4cm)
WG8	CR6/CR12 Series, Top and Back Mount NEMA Standard Exits	12.0" (30.5cm)	14.0" (35.6cm)	12.0" (30.5cm)	14.0" (35.6cm)	13.0" (33.0cm)
WG10	60 Line	8.8" (22.4cm)	N/A	N/A	15.0" (38.1cm)	15.0" (38.1cm)
PCS1	All Standard Exits, 4X Series, 6M/2M Series, CR6/CR12 Series, 30V, CCHX Combo, CTX Units (All Wall Mount)	19.4" (W) X 12.3" (H) X 9.0" (D) Outside 19.2" (W) X 12.1" (H) X 8.9" (D) Inside				
PVS2	VE, CXX, 55 Line Contemporary, SL Series (All Wall Mount)	13.3" (W) X 9.2" (H) X 2.75" (D) Inside				
PVS3	CCAX	15" (W) X 22" (H) X 8" (D) Inside				



PCS1



C = depth



PVS2



PVS3

mounting shelves

Cat.#	For Use With:	A	AA	B
SSMP	CMF/CNM Series (25-50 W) TMF/TNM Series (25-50 W)	13.0" (33.02cm)	8.0" (20.32cm)	2.75" (6.98cm)
SMMP	CMF/CNM Series (75-100 W), TMF/TNM Series (75-150 W), ZMF Series (100 W)	15.25" (38.73cm)	9.0" (22.86cm)	6.0" (15.24cm)
SLMP	TMF/TNM Series (200-450 W) ZMF Series (300 W, 450 W)	19.0" (48.26cm)	11.0" (27.94cm)	7.5" (19.05cm)

