



Gardco OptiForm site and area luminaires are available in three sizes: small, medium and large. Featuring the latest in LED technology, OptiForm achieves up to 192 lumens per watt. Eleven optical distributions are available, suitable for a range of outdoor lighting applications. OptForm features a unique mounting system with a two-piece housing for hassle-free installation. Mounting options include a standard arm, mast arm, and wall mount bracket. Service Tag is a standard feature with every OptiForm luminaire, providing maintenance or upgrade assistance throughout the life of the product.

OPF-L Area Optic Lumen values

| Performance Package | System Watts | Distribution Type | 70 CRI | | | 70 CRI | | | 70 CRI | | | 70 CRI | | | 80 CRI | | | 80 CRI | | |
|---------------------|--------------|-------------------|--------------|------------|----------------|--------------|------------|----------------|--------------|------------|----------------|--------------|------------|----------------|--------------|------------|----------------|--------------|------------|----------------|
| | | | 2700K | | | 3000K | | | 4000K | | | 5000K | | | 3000K | | | 4000K | | |
| | | | Lumen Output | BUG Rating | Efficacy (LPW) | Lumen Output | BUG Rating | Efficacy (LPW) | Lumen Output | BUG Rating | Efficacy (LPW) | Lumen Output | BUG Rating | Efficacy (LPW) | Lumen Output | BUG Rating | Efficacy (LPW) | Lumen Output | BUG Rating | Efficacy (LPW) |
| A16 | 195 | T2M | 28516 | B4-U0-G4 | 147 | 34055 | B4-U0-G4 | 175 | 36004 | B4-U0-G4 | 185 | 36004 | B4-U0-G4 | 185 | 30157 | B4-U0-G4 | 155 | 32106 | B4-U0-G4 | 165 |
| | | T3M | 28288 | B3-U0-G4 | 145 | 33783 | B4-U0-G4 | 174 | 35716 | B4-U0-G4 | 184 | 35716 | B4-U0-G4 | 184 | 29916 | B3-U0-G4 | 154 | 31850 | B3-U0-G4 | 164 |
| | | T4M | 28669 | B3-U0-G4 | 147 | 34238 | B3-U0-G4 | 176 | 36197 | B3-U0-G4 | 186 | 36197 | B3-U0-G4 | 186 | 30319 | B3-U0-G4 | 156 | 32278 | B3-U0-G4 | 166 |
| | | T5M | 29550 | B5-U0-G3 | 152 | 35290 | B5-U0-G3 | 181 | 37309 | B5-U0-G3 | 192 | 37309 | B5-U0-G3 | 192 | 31251 | B5-U0-G3 | 161 | 33270 | B5-U0-G3 | 171 |
| | | AFR | 29535 | B4-U0-G4 | 152 | 35272 | B4-U0-G4 | 181 | 37290 | B4-U0-G4 | 192 | 37290 | B4-U0-G4 | 192 | 31235 | B4-U0-G4 | 160 | 33253 | B4-U0-G4 | 171 |
| | | T4W | 27296 | B3-U0-G4 | 140 | 32598 | B3-U0-G5 | 167 | 34464 | B3-U0-G5 | 177 | 34464 | B3-U0-G5 | 177 | 28867 | B3-U0-G4 | 148 | 30733 | B3-U0-G4 | 158 |
| | | T5N | 29342 | B5-U0-G3 | 151 | 35041 | B5-U0-G3 | 180 | 37047 | B5-U0-G3 | 190 | 37047 | B5-U0-G3 | 190 | 31031 | B5-U0-G3 | 159 | 33036 | B5-U0-G3 | 170 |
| | | T5W | 28251 | B5-U0-G4 | 145 | 33739 | B5-U0-G4 | 173 | 35669 | B5-U0-G4 | 183 | 35669 | B5-U0-G4 | 183 | 29877 | B5-U0-G4 | 154 | 31808 | B5-U0-G4 | 163 |
| | | LCL | 15515 | B2-U0-G2 | 80 | 18529 | B2-U0-G3 | 95 | 19589 | B2-U0-G3 | 101 | 19589 | B2-U0-G3 | 101 | 16408 | B2-U0-G2 | 84 | 17468 | B2-U0-G2 | 90 |
| | | LCR | 15515 | B2-U0-G2 | 80 | 18529 | B2-U0-G3 | 95 | 19589 | B2-U0-G3 | 101 | 19589 | B2-U0-G3 | 101 | 16408 | B2-U0-G2 | 84 | 17468 | B2-U0-G2 | 90 |
| A17 | 210 | BLC | 19883 | B1-U0-G3 | 102 | 23745 | B1-U0-G4 | 122 | 25104 | B1-U0-G4 | 129 | 25104 | B1-U0-G4 | 129 | 21027 | B1-U0-G3 | 108 | 22386 | B1-U0-G3 | 115 |
| | | T2M | 30041 | B4-U0-G4 | 143 | 35876 | B4-U0-G4 | 171 | 37929 | B4-U0-G4 | 180 | 37929 | B4-U0-G4 | 180 | 31770 | B4-U0-G4 | 151 | 33823 | B4-U0-G4 | 161 |
| | | T3M | 29801 | B3-U0-G4 | 142 | 35590 | B4-U0-G4 | 169 | 37626 | B4-U0-G4 | 179 | 37626 | B4-U0-G4 | 179 | 31516 | B4-U0-G4 | 150 | 33553 | B4-U0-G4 | 160 |
| | | T4M | 30202 | B3-U0-G4 | 144 | 36068 | B3-U0-G4 | 171 | 38133 | B3-U0-G4 | 181 | 38133 | B3-U0-G4 | 181 | 31940 | B3-U0-G4 | 152 | 34004 | B3-U0-G4 | 162 |
| | | T5M | 31130 | B5-U0-G3 | 148 | 37177 | B5-U0-G3 | 177 | 39305 | B5-U0-G4 | 187 | 39305 | B5-U0-G4 | 187 | 32922 | B5-U0-G3 | 157 | 35049 | B5-U0-G3 | 167 |
| | | AFR | 31114 | B4-U0-G4 | 148 | 37158 | B4-U0-G4 | 177 | 39284 | B4-U0-G4 | 187 | 39284 | B4-U0-G4 | 187 | 32905 | B4-U0-G4 | 156 | 35031 | B4-U0-G4 | 167 |
| | | T4W | 28756 | B3-U0-G4 | 137 | 34342 | B3-U0-G5 | 163 | 36307 | B3-U0-G5 | 173 | 36307 | B3-U0-G5 | 173 | 30411 | B3-U0-G5 | 145 | 32376 | B3-U0-G5 | 154 |
| | | T5N | 30911 | B5-U0-G3 | 147 | 36915 | B5-U0-G3 | 176 | 39028 | B5-U0-G3 | 186 | 39028 | B5-U0-G3 | 186 | 32690 | B5-U0-G3 | 155 | 34803 | B5-U0-G3 | 165 |
| | | T5W | 29762 | B5-U0-G4 | 141 | 35543 | B5-U0-G4 | 169 | 37577 | B5-U0-G4 | 179 | 37577 | B5-U0-G4 | 179 | 31475 | B5-U0-G4 | 150 | 33509 | B5-U0-G4 | 159 |
| | | LCL | 16345 | B2-U0-G2 | 78 | 19519 | B2-U0-G3 | 93 | 20637 | B2-U0-G3 | 98 | 20637 | B2-U0-G3 | 98 | 17285 | B2-U0-G3 | 82 | 18402 | B2-U0-G3 | 87 |
| LCR | 16345 | B2-U0-G2 | 78 | 19519 | B2-U0-G3 | 93 | 20637 | B2-U0-G3 | 98 | 20637 | B2-U0-G3 | 98 | 17285 | B2-U0-G3 | 82 | 18402 | B2-U0-G3 | 87 | | |
| BLC | 20946 | B1-U0-G3 | 100 | 25015 | B1-U0-G4 | 119 | 26446 | B1-U0-G4 | 126 | 26446 | B1-U0-G4 | 126 | 22151 | B1-U0-G3 | 105 | 23583 | B1-U0-G4 | 112 | | |

OPF-L Lumen specifications

Site & area luminaire

OPF-L Area Optic Lumen values (cont'd)

| Performance Package | System Watts | Distribution Type | 70 CRI | | | 70 CRI | | | 70 CRI | | | 70 CRI | | | 80 CRI | | | 80 CRI | | |
|---------------------|--------------|-------------------|--------------|------------|----------------|--------------|------------|----------------|--------------|------------|----------------|--------------|------------|----------------|--------------|------------|----------------|--------------|------------|----------------|
| | | | 2700K | | | 3000K | | | 4000K | | | 5000K | | | 3000K | | | 4000K | | |
| | | | Lumen Output | BUG Rating | Efficacy (LPW) | Lumen Output | BUG Rating | Efficacy (LPW) | Lumen Output | BUG Rating | Efficacy (LPW) | Lumen Output | BUG Rating | Efficacy (LPW) | Lumen Output | BUG Rating | Efficacy (LPW) | Lumen Output | BUG Rating | Efficacy (LPW) |
| A18 | 223 | T2M | 31804 | B4-U0-G4 | 142 | 37982 | B4-U0-G4 | 170 | 40155 | B4-U0-G4 | 180 | 40155 | B4-U0-G4 | 180 | 33634 | B4-U0-G4 | 151 | 35808 | B4-U0-G4 | 160 |
| | | T3M | 31550 | B4-U0-G4 | 141 | 37679 | B4-U0-G4 | 169 | 39835 | B4-U0-G4 | 178 | 39835 | B4-U0-G4 | 178 | 33366 | B4-U0-G4 | 149 | 35522 | B4-U0-G4 | 159 |
| | | T4M | 31975 | B3-U0-G4 | 143 | 38185 | B3-U0-G5 | 171 | 40371 | B3-U0-G5 | 181 | 40371 | B3-U0-G5 | 181 | 33815 | B3-U0-G4 | 151 | 36000 | B3-U0-G4 | 161 |
| | | T5M | 32957 | B5-U0-G3 | 148 | 39359 | B5-U0-G4 | 176 | 41612 | B5-U0-G4 | 186 | 41612 | B5-U0-G4 | 186 | 34854 | B5-U0-G3 | 156 | 37107 | B5-U0-G3 | 166 |
| | | AFR | 32940 | B4-U0-G4 | 148 | 39339 | B4-U0-G4 | 176 | 41590 | B4-U0-G4 | 186 | 41590 | B4-U0-G4 | 186 | 34836 | B4-U0-G4 | 156 | 37087 | B4-U0-G4 | 166 |
| | | T4W | 30444 | B3-U0-G4 | 136 | 36357 | B3-U0-G5 | 163 | 38438 | B3-U0-G5 | 172 | 38438 | B3-U0-G5 | 172 | 32196 | B3-U0-G5 | 144 | 34277 | B3-U0-G5 | 154 |
| | | T5N | 32725 | B5-U0-G3 | 147 | 39082 | B5-U0-G3 | 175 | 41319 | B5-U0-G3 | 185 | 41319 | B5-U0-G3 | 185 | 34609 | B5-U0-G3 | 155 | 36845 | B5-U0-G3 | 165 |
| | | T5W | 31509 | B5-U0-G4 | 141 | 37629 | B5-U0-G4 | 169 | 39782 | B5-U0-G4 | 178 | 39782 | B5-U0-G4 | 178 | 33322 | B5-U0-G4 | 149 | 35476 | B5-U0-G4 | 159 |
| | | LCL | 17304 | B2-U0-G3 | 78 | 20665 | B2-U0-G3 | 93 | 21848 | B3-U0-G3 | 98 | 21848 | B3-U0-G3 | 98 | 18300 | B2-U0-G3 | 82 | 19482 | B2-U0-G3 | 87 |
| A19 | 235 | LCR | 17304 | B2-U0-G3 | 78 | 20665 | B2-U0-G3 | 93 | 21848 | B2-U0-G3 | 98 | 21848 | B2-U0-G3 | 98 | 18300 | B2-U0-G3 | 82 | 19482 | B2-U0-G3 | 87 |
| | | BLC | 22175 | B1-U0-G3 | 99 | 26483 | B1-U0-G4 | 119 | 27998 | B1-U0-G4 | 125 | 27998 | B1-U0-G4 | 125 | 23452 | B1-U0-G4 | 105 | 24967 | B1-U0-G4 | 112 |
| | | T2M | 33320 | B4-U0-G4 | 142 | 39792 | B4-U0-G4 | 169 | 42069 | B4-U0-G4 | 179 | 42069 | B4-U0-G4 | 179 | 35237 | B4-U0-G4 | 150 | 37515 | B4-U0-G4 | 160 |
| | | T3M | 33054 | B4-U0-G4 | 141 | 39474 | B4-U0-G4 | 168 | 41733 | B4-U0-G4 | 177 | 41733 | B4-U0-G4 | 177 | 34956 | B4-U0-G4 | 149 | 37215 | B4-U0-G4 | 158 |
| | | T4M | 33499 | B3-U0-G4 | 142 | 40005 | B3-U0-G5 | 170 | 42295 | B3-U0-G5 | 180 | 42295 | B3-U0-G5 | 180 | 35426 | B3-U0-G4 | 151 | 37716 | B3-U0-G4 | 160 |
| | | T5M | 34528 | B5-U0-G3 | 147 | 41235 | B5-U0-G4 | 175 | 43595 | B5-U0-G4 | 185 | 43595 | B5-U0-G4 | 185 | 36515 | B5-U0-G3 | 155 | 38875 | B5-U0-G3 | 165 |
| | | AFR | 34510 | B4-U0-G4 | 147 | 41214 | B4-U0-G4 | 175 | 43572 | B4-U0-G4 | 185 | 43572 | B4-U0-G4 | 185 | 36496 | B4-U0-G4 | 155 | 38855 | B4-U0-G4 | 165 |
| | | T4W | 31895 | B3-U0-G5 | 136 | 38090 | B3-U0-G5 | 162 | 40270 | B3-U0-G5 | 171 | 40270 | B3-U0-G5 | 171 | 33730 | B3-U0-G5 | 143 | 35910 | B3-U0-G5 | 153 |
| | | T5N | 34285 | B5-U0-G3 | 146 | 40945 | B5-U0-G4 | 174 | 43288 | B5-U0-G4 | 184 | 43288 | B5-U0-G4 | 184 | 36258 | B5-U0-G3 | 154 | 38601 | B5-U0-G3 | 164 |
| A20 | 247 | T5W | 33010 | B5-U0-G4 | 140 | 39422 | B5-U0-G4 | 168 | 41679 | B5-U0-G4 | 177 | 41679 | B5-U0-G4 | 177 | 34910 | B5-U0-G4 | 148 | 37166 | B5-U0-G4 | 158 |
| | | LCL | 18129 | B2-U0-G3 | 77 | 21650 | B3-U0-G3 | 92 | 22889 | B3-U0-G3 | 97 | 22889 | B3-U0-G3 | 97 | 19172 | B2-U0-G3 | 82 | 20411 | B2-U0-G3 | 87 |
| | | LCR | 18129 | B2-U0-G3 | 77 | 21650 | B2-U0-G3 | 92 | 22889 | B2-U0-G3 | 97 | 22889 | B2-U0-G3 | 97 | 19172 | B2-U0-G3 | 82 | 20411 | B2-U0-G3 | 87 |
| | | BLC | 23232 | B1-U0-G4 | 99 | 27745 | B1-U0-G4 | 118 | 29333 | B1-U0-G4 | 125 | 29333 | B1-U0-G4 | 125 | 24569 | B1-U0-G4 | 104 | 26157 | B1-U0-G4 | 111 |
| | | T2M | 34900 | B4-U0-G4 | 141 | 41679 | B4-U0-G4 | 168 | 44064 | B4-U0-G4 | 178 | 44064 | B4-U0-G4 | 178 | 36909 | B4-U0-G4 | 149 | 39294 | B4-U0-G4 | 159 |
| | | T3M | 34622 | B4-U0-G4 | 140 | 41347 | B4-U0-G4 | 167 | 43713 | B4-U0-G4 | 177 | 43713 | B4-U0-G4 | 177 | 36614 | B4-U0-G4 | 148 | 38980 | B4-U0-G4 | 158 |
| | | T4M | 35087 | B3-U0-G4 | 142 | 41903 | B3-U0-G5 | 169 | 44301 | B3-U0-G5 | 179 | 44301 | B3-U0-G5 | 179 | 37107 | B3-U0-G5 | 150 | 39505 | B3-U0-G5 | 160 |
| | | T5M | 36166 | B5-U0-G3 | 146 | 43191 | B5-U0-G4 | 175 | 45662 | B5-U0-G4 | 185 | 45662 | B5-U0-G4 | 185 | 38247 | B5-U0-G4 | 155 | 40719 | B5-U0-G4 | 165 |
| | | AFR | 36147 | B4-U0-G4 | 146 | 43169 | B4-U0-G4 | 174 | 45639 | B4-U0-G4 | 184 | 45639 | B4-U0-G4 | 184 | 38228 | B4-U0-G4 | 154 | 40698 | B4-U0-G4 | 164 |
| A20 | 247 | T4W | 33408 | B3-U0-G5 | 135 | 39897 | B4-U0-G5 | 161 | 42180 | B4-U0-G5 | 170 | 42180 | B4-U0-G5 | 170 | 35330 | B3-U0-G5 | 143 | 37614 | B3-U0-G5 | 152 |
| | | T5N | 35911 | B5-U0-G3 | 145 | 42887 | B5-U0-G4 | 173 | 45341 | B5-U0-G4 | 183 | 45341 | B5-U0-G4 | 183 | 37978 | B5-U0-G3 | 153 | 40432 | B5-U0-G3 | 163 |
| | | T5W | 34576 | B5-U0-G4 | 140 | 41292 | B5-U0-G4 | 167 | 43655 | B5-U0-G4 | 176 | 43655 | B5-U0-G4 | 176 | 36566 | B5-U0-G4 | 148 | 38929 | B5-U0-G4 | 157 |
| | | LCL | 18988 | B2-U0-G3 | 77 | 22677 | B3-U0-G3 | 92 | 23975 | B3-U0-G3 | 97 | 23975 | B3-U0-G3 | 97 | 20081 | B3-U0-G3 | 81 | 21379 | B3-U0-G3 | 86 |
| | | LCR | 18988 | B2-U0-G3 | 77 | 22677 | B2-U0-G3 | 92 | 23975 | B2-U0-G3 | 97 | 23975 | B2-U0-G3 | 97 | 20081 | B2-U0-G3 | 81 | 21379 | B2-U0-G3 | 86 |
| | | BLC | 24334 | B1-U0-G4 | 98 | 29061 | B1-U0-G4 | 117 | 30724 | B1-U0-G4 | 124 | 30724 | B1-U0-G4 | 124 | 25735 | B1-U0-G4 | 104 | 27398 | B1-U0-G4 | 111 |

OPF-L Lumen specifications

Site & area luminaire

OPF-L Area Optic Lumen values (cont'd)

| Performance Package | System Watts | Distribution Type | 70 CRI | | | 70 CRI | | | 70 CRI | | | 70 CRI | | | 80 CRI | | | 80 CRI | | |
|---------------------|--------------|-------------------|--------------|------------|----------------|--------------|------------|----------------|--------------|------------|----------------|--------------|------------|----------------|--------------|------------|----------------|--------------|------------|----------------|
| | | | 2700K | | | 3000K | | | 4000K | | | 5000K | | | 3000K | | | 4000K | | |
| | | | Lumen Output | BUG Rating | Efficacy (LPW) | Lumen Output | BUG Rating | Efficacy (LPW) | Lumen Output | BUG Rating | Efficacy (LPW) | Lumen Output | BUG Rating | Efficacy (LPW) | Lumen Output | BUG Rating | Efficacy (LPW) | Lumen Output | BUG Rating | Efficacy (LPW) |
| A21 | 260 | T2M | 36426 | B4-U0-G4 | 140 | 43501 | B4-U0-G4 | 167 | 45991 | B4-U0-G4 | 177 | 45991 | B4-U0-G4 | 177 | 38522 | B4-U0-G4 | 148 | 41012 | B4-U0-G4 | 158 |
| | | T3M | 36135 | B4-U0-G4 | 139 | 43154 | B4-U0-G5 | 166 | 45624 | B4-U0-G5 | 176 | 45624 | B4-U0-G5 | 176 | 38215 | B4-U0-G4 | 147 | 40685 | B4-U0-G4 | 157 |
| | | T4M | 36621 | B3-U0-G5 | 141 | 43735 | B3-U0-G5 | 168 | 46238 | B3-U0-G5 | 178 | 46238 | B3-U0-G5 | 178 | 38729 | B3-U0-G5 | 149 | 41232 | B3-U0-G5 | 159 |
| | | T5M | 37747 | B5-U0-G4 | 145 | 45079 | B5-U0-G4 | 174 | 47659 | B5-U0-G4 | 183 | 47659 | B5-U0-G4 | 183 | 39919 | B5-U0-G4 | 154 | 42499 | B5-U0-G4 | 164 |
| | | AFR | 37727 | B4-U0-G4 | 145 | 45056 | B4-U0-G4 | 173 | 47634 | B4-U0-G4 | 183 | 47634 | B4-U0-G4 | 183 | 39899 | B4-U0-G4 | 154 | 42477 | B4-U0-G4 | 164 |
| | | T4W | 34868 | B3-U0-G5 | 134 | 41641 | B4-U0-G5 | 160 | 44024 | B4-U0-G5 | 169 | 44024 | B4-U0-G5 | 169 | 36875 | B3-U0-G5 | 142 | 39258 | B3-U0-G5 | 151 |
| | | T5N | 37481 | B5-U0-G3 | 144 | 44762 | B5-U0-G4 | 172 | 47323 | B5-U0-G4 | 182 | 47323 | B5-U0-G4 | 182 | 39638 | B5-U0-G4 | 153 | 42200 | B5-U0-G4 | 162 |
| | | T5W | 36088 | B5-U0-G4 | 139 | 43097 | B5-U0-G4 | 166 | 45564 | B5-U0-G4 | 175 | 45564 | B5-U0-G4 | 175 | 38165 | B5-U0-G4 | 147 | 40631 | B5-U0-G4 | 156 |
| | | LCL | 19819 | B2-U0-G3 | 76 | 23668 | B3-U0-G3 | 91 | 25023 | B3-U0-G3 | 96 | 25023 | B3-U0-G3 | 96 | 20959 | B3-U0-G3 | 81 | 22314 | B3-U0-G3 | 86 |
| | | LCR | 19819 | B2-U0-G3 | 76 | 23668 | B2-U0-G3 | 91 | 25023 | B2-U0-G3 | 96 | 25023 | B2-U0-G3 | 96 | 20959 | B2-U0-G3 | 81 | 22314 | B2-U0-G3 | 86 |
| BLC | 25398 | B1-U0-G4 | 98 | 30331 | B1-U0-G4 | 117 | 32067 | B1-U0-G4 | 123 | 32067 | B1-U0-G4 | 123 | 26860 | B1-U0-G4 | 103 | 28595 | B1-U0-G4 | 110 | | |
| A22 | 273 | T2M | 38047 | B4-U0-G4 | 140 | 45438 | B4-U0-G4 | 167 | 48038 | B4-U0-G4 | 176 | 48038 | B4-U0-G4 | 176 | 40237 | B4-U0-G4 | 148 | 42838 | B4-U0-G4 | 157 |
| | | T3M | 37744 | B4-U0-G4 | 138 | 45075 | B4-U0-G5 | 165 | 47655 | B4-U0-G5 | 175 | 47655 | B4-U0-G5 | 175 | 39916 | B4-U0-G4 | 146 | 42496 | B4-U0-G4 | 156 |
| | | T4M | 38252 | B3-U0-G5 | 140 | 45682 | B3-U0-G5 | 168 | 48296 | B3-U0-G5 | 177 | 48296 | B3-U0-G5 | 177 | 40453 | B3-U0-G5 | 148 | 43068 | B3-U0-G5 | 158 |
| | | T5M | 39427 | B5-U0-G4 | 145 | 47086 | B5-U0-G4 | 173 | 49781 | B5-U0-G4 | 183 | 49781 | B5-U0-G4 | 183 | 41697 | B5-U0-G4 | 153 | 44391 | B5-U0-G4 | 163 |
| | | AFR | 39407 | B4-U0-G4 | 145 | 47062 | B4-U0-G4 | 173 | 49755 | B4-U0-G4 | 183 | 49755 | B4-U0-G4 | 183 | 41675 | B4-U0-G4 | 153 | 44368 | B4-U0-G4 | 163 |
| | | T4W | 36420 | B3-U0-G5 | 134 | 43495 | B4-U0-G5 | 160 | 45984 | B4-U0-G5 | 169 | 45984 | B4-U0-G5 | 169 | 38517 | B3-U0-G5 | 141 | 41006 | B4-U0-G5 | 150 |
| | | T5N | 39150 | B5-U0-G4 | 144 | 46754 | B5-U0-G4 | 172 | 49430 | B5-U0-G4 | 181 | 49430 | B5-U0-G4 | 181 | 41403 | B5-U0-G4 | 152 | 44079 | B5-U0-G4 | 162 |
| | | T5W | 37694 | B5-U0-G4 | 138 | 45016 | B5-U0-G5 | 165 | 47592 | B5-U0-G5 | 175 | 47592 | B5-U0-G5 | 175 | 39864 | B5-U0-G4 | 146 | 42440 | B5-U0-G4 | 156 |
| | | LCL | 20701 | B3-U0-G3 | 76 | 24722 | B3-U0-G3 | 91 | 26137 | B3-U0-G3 | 96 | 26137 | B3-U0-G3 | 96 | 21892 | B3-U0-G3 | 80 | 23307 | B3-U0-G3 | 85 |
| | | LCR | 20701 | B2-U0-G3 | 76 | 24722 | B2-U0-G3 | 91 | 26137 | B2-U0-G3 | 96 | 26137 | B2-U0-G3 | 96 | 21892 | B2-U0-G3 | 80 | 23307 | B2-U0-G3 | 85 |
| BLC | 26529 | B1-U0-G4 | 97 | 31682 | B1-U0-G4 | 116 | 33495 | B1-U0-G4 | 123 | 33495 | B1-U0-G4 | 123 | 28055 | B1-U0-G4 | 103 | 29869 | B1-U0-G4 | 110 | | |
| A23 | 286 | T2M | 39766 | B4-U0-G4 | 139 | 47490 | B4-U0-G4 | 166 | 50208 | B4-U0-G4 | 176 | 50208 | B4-U0-G4 | 176 | 42055 | B4-U0-G4 | 147 | 44772 | B4-U0-G4 | 157 |
| | | T3M | 39449 | B4-U0-G4 | 138 | 47111 | B4-U0-G5 | 165 | 49808 | B4-U0-G5 | 174 | 49808 | B4-U0-G5 | 174 | 41719 | B4-U0-G5 | 146 | 44415 | B4-U0-G5 | 155 |
| | | T4M | 39979 | B3-U0-G5 | 140 | 47745 | B4-U0-G5 | 167 | 50478 | B4-U0-G5 | 177 | 50478 | B4-U0-G5 | 177 | 42280 | B3-U0-G5 | 148 | 45013 | B3-U0-G5 | 157 |
| | | T5M | 41208 | B5-U0-G4 | 144 | 49213 | B5-U0-G4 | 172 | 52029 | B5-U0-G4 | 182 | 52029 | B5-U0-G4 | 182 | 43580 | B5-U0-G4 | 152 | 46396 | B5-U0-G4 | 162 |
| | | AFR | 41187 | B4-U0-G4 | 144 | 49187 | B4-U0-G4 | 172 | 52002 | B4-U0-G4 | 182 | 52002 | B4-U0-G4 | 182 | 43557 | B4-U0-G4 | 152 | 46372 | B4-U0-G4 | 162 |
| | | T4W | 38065 | B3-U0-G5 | 133 | 45459 | B4-U0-G5 | 159 | 48061 | B4-U0-G5 | 168 | 48061 | B4-U0-G5 | 168 | 40256 | B4-U0-G5 | 141 | 42858 | B4-U0-G5 | 150 |
| | | T5N | 40918 | B5-U0-G4 | 143 | 48866 | B5-U0-G4 | 171 | 51663 | B5-U0-G4 | 181 | 51663 | B5-U0-G4 | 181 | 43273 | B5-U0-G4 | 151 | 46070 | B5-U0-G4 | 161 |
| | | T5W | 39397 | B5-U0-G4 | 138 | 47049 | B5-U0-G5 | 165 | 49742 | B5-U0-G5 | 174 | 49742 | B5-U0-G5 | 174 | 41664 | B5-U0-G4 | 146 | 44357 | B5-U0-G4 | 155 |
| | | LCL | 21636 | B3-U0-G3 | 76 | 25839 | B3-U0-G4 | 90 | 27317 | B3-U0-G4 | 96 | 27317 | B3-U0-G4 | 96 | 22881 | B3-U0-G3 | 80 | 24360 | B3-U0-G3 | 85 |
| | | LCR | 21636 | B2-U0-G3 | 76 | 25839 | B3-U0-G4 | 90 | 27317 | B3-U0-G4 | 96 | 27317 | B3-U0-G4 | 96 | 22881 | B2-U0-G3 | 80 | 24360 | B2-U0-G3 | 85 |
| BLC | 27727 | B1-U0-G4 | 97 | 33113 | B1-U0-G4 | 116 | 35008 | B1-U0-G4 | 122 | 35008 | B1-U0-G4 | 122 | 29323 | B1-U0-G4 | 103 | 31218 | B1-U0-G4 | 109 | | |

OPF-L Lumen specifications

Site & area luminaire

OPF-L Area Optic Lumen values (cont'd)

| Performance Package | System Watts | Distribution Type | 70 CRI | | | 70 CRI | | | 70 CRI | | | 70 CRI | | | 80 CRI | | | 80 CRI | | |
|---------------------|--------------|-------------------|--------------|------------|----------------|--------------|------------|----------------|--------------|------------|----------------|--------------|------------|----------------|--------------|------------|----------------|--------------|------------|----------------|
| | | | 2700K | | | 3000K | | | 4000K | | | 5000K | | | 3000K | | | 4000K | | |
| | | | Lumen Output | BUG Rating | Efficacy (LPW) | Lumen Output | BUG Rating | Efficacy (LPW) | Lumen Output | BUG Rating | Efficacy (LPW) | Lumen Output | BUG Rating | Efficacy (LPW) | Lumen Output | BUG Rating | Efficacy (LPW) | Lumen Output | BUG Rating | Efficacy (LPW) |
| A24 | 298 | T2M | 41212 | B4-U0-G4 | 138 | 49218 | B4-U0-G4 | 165 | 52034 | B4-U0-G4 | 175 | 52034 | B4-U0-G4 | 175 | 43584 | B4-U0-G4 | 146 | 46401 | B4-U0-G4 | 156 |
| | | T3M | 40884 | B4-U0-G4 | 137 | 48825 | B4-U0-G5 | 164 | 51619 | B4-U0-G5 | 173 | 51619 | B4-U0-G5 | 173 | 43237 | B4-U0-G5 | 145 | 46031 | B4-U0-G5 | 154 |
| | | T4M | 41434 | B3-U0-G5 | 139 | 49482 | B4-U0-G5 | 166 | 52313 | B4-U0-G5 | 175 | 52313 | B4-U0-G5 | 175 | 43818 | B3-U0-G5 | 147 | 46650 | B3-U0-G5 | 156 |
| | | T5M | 42707 | B5-U0-G4 | 143 | 51003 | B5-U0-G4 | 171 | 53921 | B5-U0-G4 | 181 | 53921 | B5-U0-G4 | 181 | 45165 | B5-U0-G4 | 151 | 48084 | B5-U0-G4 | 161 |
| | | AFR | 42685 | B4-U0-G4 | 143 | 50976 | B5-U0-G4 | 171 | 53894 | B5-U0-G4 | 181 | 53894 | B5-U0-G4 | 181 | 45142 | B4-U0-G4 | 151 | 48059 | B4-U0-G4 | 161 |
| | | T4W | 39450 | B4-U0-G5 | 132 | 47113 | B4-U0-G5 | 158 | 49809 | B4-U0-G5 | 167 | 49809 | B4-U0-G5 | 167 | 41720 | B4-U0-G5 | 140 | 44417 | B4-U0-G5 | 149 |
| | | T5N | 42406 | B5-U0-G4 | 142 | 50644 | B5-U0-G4 | 170 | 53542 | B5-U0-G4 | 180 | 53542 | B5-U0-G4 | 180 | 44847 | B5-U0-G4 | 150 | 47745 | B5-U0-G4 | 160 |
| | | T5W | 40830 | B5-U0-G4 | 137 | 48761 | B5-U0-G5 | 164 | 51551 | B5-U0-G5 | 173 | 51551 | B5-U0-G5 | 173 | 43180 | B5-U0-G4 | 145 | 45970 | B5-U0-G4 | 154 |
| | | LCL | 22423 | B3-U0-G3 | 75 | 26778 | B3-U0-G4 | 90 | 28311 | B3-U0-G4 | 95 | 28311 | B3-U0-G4 | 95 | 23713 | B3-U0-G3 | 80 | 25246 | B3-U0-G3 | 85 |
| LCR | 22423 | B2-U0-G3 | 75 | 26778 | B3-U0-G4 | 90 | 28311 | B3-U0-G4 | 95 | 28311 | B3-U0-G4 | 95 | 23713 | B2-U0-G3 | 80 | 25246 | B2-U0-G3 | 85 | | |
| BLC | 28735 | B1-U0-G4 | 96 | 34317 | B1-U0-G4 | 115 | 36281 | B2-U0-G4 | 122 | 36281 | B2-U0-G4 | 122 | 30389 | B1-U0-G4 | 102 | 32353 | B1-U0-G4 | 109 | | |
| A25 | 311 | T2M | 42706 | B4-U0-G4 | 137 | 51001 | B5-U0-G4 | 164 | 53920 | B5-U0-G4 | 173 | 53920 | B5-U0-G4 | 173 | 45164 | B4-U0-G4 | 145 | 48082 | B4-U0-G4 | 154 |
| | | T3M | 42365 | B4-U0-G5 | 136 | 50594 | B4-U0-G5 | 163 | 53490 | B4-U0-G5 | 172 | 53490 | B4-U0-G5 | 172 | 44803 | B4-U0-G5 | 144 | 47699 | B4-U0-G5 | 153 |
| | | T4M | 42935 | B3-U0-G5 | 138 | 51275 | B4-U0-G5 | 165 | 54209 | B4-U0-G5 | 174 | 54209 | B4-U0-G5 | 174 | 45406 | B3-U0-G5 | 146 | 48340 | B4-U0-G5 | 155 |
| | | T5M | 44255 | B5-U0-G4 | 142 | 52851 | B5-U0-G4 | 170 | 55875 | B5-U0-G4 | 180 | 55875 | B5-U0-G4 | 180 | 46802 | B5-U0-G4 | 150 | 49826 | B5-U0-G4 | 160 |
| | | AFR | 44232 | B4-U0-G4 | 142 | 52824 | B5-U0-G4 | 170 | 55847 | B5-U0-G4 | 179 | 55847 | B5-U0-G4 | 179 | 46777 | B4-U0-G4 | 150 | 49801 | B4-U0-G4 | 160 |
| | | T4W | 40880 | B4-U0-G5 | 131 | 48820 | B4-U0-G5 | 157 | 51614 | B4-U0-G5 | 166 | 51614 | B4-U0-G5 | 166 | 43232 | B4-U0-G5 | 139 | 46026 | B4-U0-G5 | 148 |
| | | T5N | 43943 | B5-U0-G4 | 141 | 52479 | B5-U0-G4 | 169 | 55482 | B5-U0-G4 | 178 | 55482 | B5-U0-G4 | 178 | 46472 | B5-U0-G4 | 149 | 49475 | B5-U0-G4 | 159 |
| | | T5W | 42309 | B5-U0-G4 | 136 | 50528 | B5-U0-G5 | 162 | 53419 | B5-U0-G5 | 172 | 53419 | B5-U0-G5 | 172 | 44744 | B5-U0-G5 | 144 | 47636 | B5-U0-G5 | 153 |
| | | LCL | 23235 | B3-U0-G3 | 75 | 27749 | B3-U0-G4 | 89 | 29337 | B3-U0-G4 | 94 | 29337 | B3-U0-G4 | 94 | 24573 | B3-U0-G3 | 79 | 26161 | B3-U0-G3 | 84 |
| LCR | 23235 | B2-U0-G3 | 75 | 27749 | B3-U0-G4 | 89 | 29337 | B3-U0-G4 | 94 | 29337 | B3-U0-G4 | 94 | 24573 | B3-U0-G3 | 79 | 26161 | B3-U0-G4 | 84 | | |
| BLC | 29777 | B1-U0-G4 | 96 | 35561 | B2-U0-G4 | 114 | 37596 | B2-U0-G5 | 121 | 37596 | B2-U0-G5 | 121 | 31490 | B1-U0-G4 | 101 | 33526 | B1-U0-G4 | 108 | | |
| A26 | 324 | T2M | 44224 | B4-U0-G4 | 136 | 52814 | B5-U0-G4 | 163 | 55837 | B5-U0-G4 | 172 | 55837 | B5-U0-G4 | 172 | 46769 | B4-U0-G4 | 144 | 49792 | B4-U0-G4 | 153 |
| | | T3M | 43871 | B4-U0-G5 | 135 | 52393 | B4-U0-G5 | 162 | 55391 | B4-U0-G5 | 171 | 55391 | B4-U0-G5 | 171 | 46396 | B4-U0-G5 | 143 | 49395 | B4-U0-G5 | 152 |
| | | T4M | 44461 | B3-U0-G5 | 137 | 53098 | B4-U0-G5 | 164 | 56136 | B4-U0-G5 | 173 | 56136 | B4-U0-G5 | 173 | 47020 | B4-U0-G5 | 145 | 50059 | B4-U0-G5 | 154 |
| | | T5M | 45828 | B5-U0-G4 | 141 | 54730 | B5-U0-G4 | 169 | 57862 | B5-U0-G4 | 178 | 57862 | B5-U0-G4 | 178 | 48465 | B5-U0-G4 | 149 | 51598 | B5-U0-G4 | 159 |
| | | AFR | 45804 | B4-U0-G4 | 141 | 54702 | B5-U0-G4 | 169 | 57832 | B5-U0-G5 | 178 | 57832 | B5-U0-G5 | 178 | 48440 | B4-U0-G4 | 149 | 51571 | B4-U0-G4 | 159 |
| | | T4W | 42333 | B4-U0-G5 | 130 | 50556 | B4-U0-G5 | 156 | 53449 | B4-U0-G5 | 165 | 53449 | B4-U0-G5 | 165 | 44769 | B4-U0-G5 | 138 | 47663 | B4-U0-G5 | 147 |
| | | T5N | 45505 | B5-U0-G4 | 140 | 54344 | B5-U0-G4 | 168 | 57455 | B5-U0-G4 | 177 | 57455 | B5-U0-G4 | 177 | 48124 | B5-U0-G4 | 148 | 51234 | B5-U0-G4 | 158 |
| | | T5W | 43813 | B5-U0-G5 | 135 | 52324 | B5-U0-G5 | 161 | 55318 | B5-U0-G5 | 171 | 55318 | B5-U0-G5 | 171 | 46335 | B5-U0-G5 | 143 | 49330 | B5-U0-G5 | 152 |
| | | LCL | 24062 | B3-U0-G3 | 74 | 28735 | B3-U0-G4 | 89 | 30380 | B3-U0-G4 | 94 | 30380 | B3-U0-G4 | 94 | 25446 | B3-U0-G4 | 78 | 27091 | B3-U0-G4 | 84 |
| LCR | 24062 | B2-U0-G3 | 74 | 28735 | B3-U0-G4 | 89 | 30380 | B3-U0-G4 | 94 | 30380 | B3-U0-G4 | 94 | 25446 | B3-U0-G4 | 78 | 27091 | B3-U0-G4 | 84 | | |
| BLC | 30835 | B1-U0-G4 | 95 | 36825 | B2-U0-G5 | 114 | 38932 | B2-U0-G5 | 120 | 38932 | B2-U0-G5 | 120 | 32610 | B1-U0-G4 | 101 | 34717 | B1-U0-G4 | 107 | | |

OPF-L Lumen specifications

Site & area luminaire

OPF-L Area Optic Lumen values (cont'd)

| Performance Package | System Watts | Distribution Type | 70 CRI | | | 70 CRI | | | 70 CRI | | | 70 CRI | | | 80 CRI | | | 80 CRI | | |
|---------------------|--------------|-------------------|--------------|------------|----------------|--------------|------------|----------------|--------------|------------|----------------|--------------|------------|----------------|--------------|------------|----------------|--------------|------------|----------------|
| | | | 2700K | | | 3000K | | | 4000K | | | 5000K | | | 3000K | | | 4000K | | |
| | | | Lumen Output | BUG Rating | Efficacy (LPW) | Lumen Output | BUG Rating | Efficacy (LPW) | Lumen Output | BUG Rating | Efficacy (LPW) | Lumen Output | BUG Rating | Efficacy (LPW) | Lumen Output | BUG Rating | Efficacy (LPW) | Lumen Output | BUG Rating | Efficacy (LPW) |
| A27 | 337 | T2M | 45754 | B4-U0-G4 | 136 | 54641 | B5-U0-G4 | 162 | 57768 | B5-U0-G5 | 171 | 57768 | B5-U0-G5 | 171 | 48387 | B4-U0-G4 | 143 | 51514 | B4-U0-G4 | 153 |
| | | T3M | 45389 | B4-U0-G5 | 135 | 54205 | B4-U0-G5 | 161 | 57308 | B4-U0-G5 | 170 | 57308 | B4-U0-G5 | 170 | 48001 | B4-U0-G5 | 142 | 51103 | B4-U0-G5 | 151 |
| | | T4M | 45999 | B4-U0-G5 | 136 | 54935 | B4-U0-G5 | 163 | 58078 | B4-U0-G5 | 172 | 58078 | B4-U0-G5 | 172 | 48647 | B4-U0-G5 | 144 | 51791 | B4-U0-G5 | 154 |
| | | T5M | 47413 | B5-U0-G4 | 141 | 56623 | B5-U0-G4 | 168 | 59864 | B5-U0-G4 | 177 | 59864 | B5-U0-G4 | 177 | 50142 | B5-U0-G4 | 149 | 53383 | B5-U0-G4 | 158 |
| | | AFR | 47389 | B4-U0-G4 | 140 | 56594 | B5-U0-G5 | 168 | 59833 | B5-U0-G5 | 177 | 59833 | B5-U0-G5 | 177 | 50116 | B5-U0-G4 | 149 | 53355 | B5-U0-G4 | 158 |
| | | T4W | 43797 | B4-U0-G5 | 130 | 52305 | B4-U0-G5 | 155 | 55298 | B4-U0-G5 | 164 | 55298 | B4-U0-G5 | 164 | 46318 | B4-U0-G5 | 137 | 49311 | B4-U0-G5 | 146 |
| | | T5N | 47080 | B5-U0-G4 | 140 | 56224 | B5-U0-G4 | 167 | 59442 | B5-U0-G4 | 176 | 59442 | B5-U0-G4 | 176 | 49789 | B5-U0-G4 | 148 | 53007 | B5-U0-G4 | 157 |
| | | T5W | 45329 | B5-U0-G5 | 134 | 54134 | B5-U0-G5 | 160 | 57232 | B5-U0-G5 | 170 | 57232 | B5-U0-G5 | 170 | 47938 | B5-U0-G5 | 142 | 51036 | B5-U0-G5 | 151 |
| | | LCL | 24894 | B3-U0-G4 | 74 | 29729 | B3-U0-G4 | 88 | 31431 | B3-U0-G4 | 93 | 31431 | B3-U0-G4 | 93 | 26327 | B3-U0-G4 | 78 | 28028 | B3-U0-G4 | 83 |
| | | LCR | 24894 | B3-U0-G4 | 74 | 29729 | B3-U0-G4 | 88 | 31431 | B3-U0-G4 | 93 | 31431 | B3-U0-G4 | 93 | 26327 | B3-U0-G4 | 78 | 28028 | B3-U0-G4 | 83 |
| | | BLC | 31902 | B1-U0-G4 | 95 | 38099 | B2-U0-G5 | 113 | 40279 | B2-U0-G5 | 119 | 40279 | B2-U0-G5 | 119 | 33738 | B2-U0-G4 | 100 | 35918 | B2-U0-G4 | 106 |
| A28 | 350 | T2M | 47178 | B4-U0-G4 | 135 | 56342 | B5-U0-G5 | 161 | 59566 | B5-U0-G5 | 170 | 59566 | B5-U0-G5 | 170 | 49893 | B5-U0-G4 | 142 | 53117 | B5-U0-G4 | 152 |
| | | T3M | 46801 | B4-U0-G5 | 134 | 55892 | B4-U0-G5 | 160 | 59091 | B4-U0-G5 | 169 | 59091 | B4-U0-G5 | 169 | 49495 | B4-U0-G5 | 141 | 52694 | B4-U0-G5 | 150 |
| | | T4M | 47431 | B4-U0-G5 | 135 | 56644 | B4-U0-G5 | 162 | 59886 | B4-U0-G5 | 171 | 59886 | B4-U0-G5 | 171 | 50161 | B4-U0-G5 | 143 | 53403 | B4-U0-G5 | 152 |
| | | T5M | 48889 | B5-U0-G4 | 140 | 58385 | B5-U0-G4 | 167 | 61727 | B5-U0-G4 | 176 | 61727 | B5-U0-G4 | 176 | 51703 | B5-U0-G4 | 148 | 55044 | B5-U0-G4 | 157 |
| | | AFR | 48864 | B5-U0-G4 | 139 | 58355 | B5-U0-G5 | 167 | 61695 | B5-U0-G5 | 176 | 61695 | B5-U0-G5 | 176 | 51676 | B5-U0-G4 | 148 | 55016 | B5-U0-G4 | 157 |
| | | T4W | 45160 | B4-U0-G5 | 129 | 53933 | B4-U0-G5 | 154 | 57019 | B4-U0-G5 | 163 | 57019 | B4-U0-G5 | 163 | 47760 | B4-U0-G5 | 136 | 50846 | B4-U0-G5 | 145 |
| | | T5N | 48545 | B5-U0-G4 | 139 | 57974 | B5-U0-G4 | 165 | 61292 | B5-U0-G4 | 175 | 61292 | B5-U0-G4 | 175 | 51339 | B5-U0-G4 | 147 | 54656 | B5-U0-G4 | 156 |
| | | T5W | 46740 | B5-U0-G5 | 133 | 55819 | B5-U0-G5 | 159 | 59013 | B5-U0-G5 | 168 | 59013 | B5-U0-G5 | 168 | 49430 | B5-U0-G5 | 141 | 52624 | B5-U0-G5 | 150 |
| | | LCL | 25669 | B3-U0-G4 | 73 | 30655 | B3-U0-G4 | 88 | 32409 | B3-U0-G4 | 93 | 32409 | B3-U0-G4 | 93 | 27146 | B3-U0-G4 | 77 | 28900 | B3-U0-G4 | 82 |
| | | LCR | 25669 | B3-U0-G4 | 73 | 30655 | B3-U0-G4 | 88 | 32409 | B3-U0-G4 | 93 | 32409 | B3-U0-G4 | 93 | 27146 | B3-U0-G4 | 77 | 28900 | B3-U0-G4 | 82 |
| | | BLC | 32895 | B1-U0-G4 | 94 | 39284 | B2-U0-G5 | 112 | 41533 | B2-U0-G5 | 119 | 41533 | B2-U0-G5 | 119 | 34788 | B2-U0-G4 | 99 | 37036 | B2-U0-G4 | 106 |
| A29 | 378 | T2M | 50152 | B5-U0-G4 | 133 | 59894 | B5-U0-G5 | 159 | 63322 | B5-U0-G5 | 168 | 63322 | B5-U0-G5 | 168 | 53039 | B5-U0-G4 | 140 | 56467 | B5-U0-G4 | 150 |
| | | T3M | 49752 | B4-U0-G5 | 132 | 59416 | B4-U0-G5 | 157 | 62817 | B4-U0-G5 | 166 | 62817 | B4-U0-G5 | 166 | 52616 | B4-U0-G5 | 139 | 56016 | B4-U0-G5 | 148 |
| | | T4M | 50422 | B4-U0-G5 | 134 | 60216 | B4-U0-G5 | 159 | 63662 | B4-U0-G5 | 169 | 63662 | B4-U0-G5 | 169 | 53324 | B4-U0-G5 | 141 | 56770 | B4-U0-G5 | 150 |
| | | T5M | 51971 | B5-U0-G4 | 138 | 62066 | B5-U0-G5 | 164 | 65618 | B5-U0-G5 | 174 | 65618 | B5-U0-G5 | 174 | 54962 | B5-U0-G4 | 146 | 58514 | B5-U0-G4 | 155 |
| | | AFR | 51945 | B5-U0-G4 | 138 | 62034 | B5-U0-G5 | 164 | 65585 | B5-U0-G5 | 174 | 65585 | B5-U0-G5 | 174 | 54934 | B5-U0-G5 | 145 | 58484 | B5-U0-G5 | 155 |
| | | T4W | 48008 | B4-U0-G5 | 127 | 57333 | B4-U0-G5 | 152 | 60614 | B4-U0-G5 | 161 | 60614 | B4-U0-G5 | 161 | 50771 | B4-U0-G5 | 134 | 54052 | B4-U0-G5 | 143 |
| | | T5N | 51605 | B5-U0-G4 | 137 | 61629 | B5-U0-G4 | 163 | 65156 | B5-U0-G4 | 173 | 65156 | B5-U0-G4 | 173 | 54576 | B5-U0-G4 | 145 | 58103 | B5-U0-G4 | 154 |
| | | T5W | 49687 | B5-U0-G5 | 132 | 59338 | B5-U0-G5 | 157 | 62734 | B5-U0-G5 | 166 | 62734 | B5-U0-G5 | 166 | 52547 | B5-U0-G5 | 139 | 55942 | B5-U0-G5 | 148 |
| | | LCL | 27287 | B3-U0-G4 | 72 | 32587 | B3-U0-G4 | 86 | 34452 | B3-U0-G4 | 91 | 34452 | B3-U0-G4 | 91 | 28858 | B3-U0-G4 | 76 | 30722 | B3-U0-G4 | 81 |
| | | LCR | 27287 | B3-U0-G4 | 72 | 32587 | B3-U0-G4 | 86 | 34452 | B3-U0-G4 | 91 | 34452 | B3-U0-G4 | 91 | 28858 | B3-U0-G4 | 76 | 30722 | B3-U0-G4 | 81 |
| | | BLC | 34969 | B2-U0-G4 | 93 | 41761 | B2-U0-G5 | 111 | 44151 | B2-U0-G5 | 117 | 44151 | B2-U0-G5 | 117 | 36981 | B2-U0-G5 | 98 | 39371 | B2-U0-G5 | 104 |

OPF-L Lumen specifications

Site & area luminaire

OPF-L Area Optic Lumen values (cont'd)

| Performance Package | System Watts | Distribution Type | 70 CRI | | | 70 CRI | | | 70 CRI | | | 70 CRI | | | 80 CRI | | | 80 CRI | | |
|---------------------|--------------|-------------------|--------------|------------|----------------|--------------|------------|----------------|--------------|------------|----------------|--------------|------------|----------------|--------------|------------|----------------|--------------|------------|----------------|
| | | | 2700K | | | 3000K | | | 4000K | | | 5000K | | | 3000K | | | 4000K | | |
| | | | Lumen Output | BUG Rating | Efficacy (LPW) | Lumen Output | BUG Rating | Efficacy (LPW) | Lumen Output | BUG Rating | Efficacy (LPW) | Lumen Output | BUG Rating | Efficacy (LPW) | Lumen Output | BUG Rating | Efficacy (LPW) | Lumen Output | BUG Rating | Efficacy (LPW) |
| A30 | 393 | T2M | 51694 | B5-U0-G4 | 132 | 61735 | B5-U0-G5 | 157 | 65268 | B5-U0-G5 | 166 | 65268 | B5-U0-G5 | 166 | 54669 | B5-U0-G5 | 139 | 58202 | B5-U0-G5 | 148 |
| | | T3M | 51281 | B4-U0-G5 | 131 | 61243 | B4-U0-G5 | 156 | 64747 | B4-U0-G5 | 165 | 64747 | B4-U0-G5 | 165 | 54233 | B4-U0-G5 | 138 | 57738 | B4-U0-G5 | 147 |
| | | T4M | 51971 | B4-U0-G5 | 132 | 62066 | B4-U0-G5 | 158 | 65618 | B4-U0-G5 | 167 | 65618 | B4-U0-G5 | 167 | 54962 | B4-U0-G5 | 140 | 58514 | B4-U0-G5 | 149 |
| | | T5M | 53569 | B5-U0-G4 | 136 | 63974 | B5-U0-G5 | 163 | 67635 | B5-U0-G5 | 172 | 67635 | B5-U0-G5 | 172 | 56652 | B5-U0-G4 | 144 | 60313 | B5-U0-G4 | 154 |
| | | AFR | 53541 | B5-U0-G4 | 136 | 63941 | B5-U0-G5 | 163 | 67600 | B5-U0-G5 | 172 | 67600 | B5-U0-G5 | 172 | 56623 | B5-U0-G5 | 144 | 60282 | B5-U0-G5 | 153 |
| | | T4W | 49483 | B4-U0-G5 | 126 | 59095 | B4-U0-G5 | 150 | 62477 | B4-U0-G5 | 159 | 62477 | B4-U0-G5 | 159 | 52331 | B4-U0-G5 | 133 | 55713 | B4-U0-G5 | 142 |
| | | T5N | 53192 | B5-U0-G4 | 135 | 63524 | B5-U0-G5 | 162 | 67159 | B5-U0-G5 | 171 | 67159 | B5-U0-G5 | 171 | 56253 | B5-U0-G4 | 143 | 59888 | B5-U0-G4 | 152 |
| | | T5W | 51214 | B5-U0-G5 | 130 | 61162 | B5-U0-G5 | 156 | 64662 | B5-U0-G5 | 165 | 64662 | B5-U0-G5 | 165 | 54162 | B5-U0-G5 | 138 | 57662 | B5-U0-G5 | 147 |
| | | LCL | 28126 | B3-U0-G4 | 72 | 33589 | B3-U0-G4 | 85 | 35511 | B3-U0-G4 | 90 | 35511 | B3-U0-G4 | 90 | 29744 | B3-U0-G4 | 76 | 31667 | B3-U0-G4 | 81 |
| LCR | 28126 | B3-U0-G4 | 72 | 33589 | B3-U0-G4 | 85 | 35511 | B3-U0-G4 | 90 | 35511 | B3-U0-G4 | 90 | 29744 | B3-U0-G4 | 76 | 31667 | B3-U0-G4 | 81 | | |
| BLC | 36044 | B2-U0-G5 | 92 | 43045 | B2-U0-G5 | 110 | 45508 | B2-U0-G5 | 116 | 45508 | B2-U0-G5 | 116 | 38118 | B2-U0-G5 | 97 | 40581 | B2-U0-G5 | 103 | | |



© 2023 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation
400 Crossing Blvd, Suite 600
Bridgewater, NJ 08807
Telephone: 800-555-0050

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone: 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.