


Project: _____
Location: _____
Cat.No: _____
Type: _____
Lamps: _____ Qty: _____
Notes: _____



Ordering Guide

Example: WAB2100 4 A

Product Code	WAB2100	2100 Series Wraparound Base
Pole Diameter	4	4"
	5	5"
	6	6"
	7	7"
Finish	A	Black
	B	White
	G	Verde
	H	Bronze
	J	Green

Specifications

HOUSING:

356 HM high-strength, low-copper, proprietary cast aluminum alloy .

FINISH:

Thermoset polyester powdercoat is electrostatically applied after a five-stage conversion cleaning process and bonded by heat fusion thermosetting. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B117 specifications. For larger projects where a custom color is required, contact the factory for more information.

WARRANTY:

Three-year limited warranty.

Height :

25"

Base Diameter:

20"

Inside Diameter:

18 11/16"

