

Lumec features a range of aluminum poles suited for multiple outdoor applications, all designed and manufactured for superior quality.

	Good	Good	Good	Good	Better	Better	Better	Better	Better	Better	Better	Better	Better	Better	Better	Better	Better	Better	Best	Best	Best	Best	Best	Best	Best		
	APR4	APR5	ATR74	ATR85	ATR-C1/ATR-C2	AM6/AM8	SAM8	AMT8	RA61	RAS61	TM6	R80/R80A	RA804	RA805	RA856	RTA800	RTA61	P135A	RA40	RTA40	RTA500	RTA608	RAF805	RTAF800	RTA906	RTA928	
Pole Style	Round Straight	Round Straight	Round Tapered	Round Tapered	Round Tapered Curved	Round Straight	Round Straight	Round Tapered	Round Straight	Round Straight	Round Tapered	Round Straight	Round Straight	Round Straight	Round Straight	Round Tapered	12-Flute Round Tapered	12-Flute Round Straight	12-Flute Round Straight	12-Flute Round Tapered	12-Flute Round Tapered	12-Flute Round Tapered	12-Flute Round Straight	12-Flute Round Tapered	12-Flute Round Tapered	12-Flute Round Tapered	
Base Style	Optional Base Covers	Optional Base Covers	Bolt Covers	Bolt Covers	Bolt Covers	Bottleneck	Bottleneck	Bottleneck	Bottleneck	Bottleneck	Bottleneck	Fluted Bottleneck & Bolt Covers or Optional Base Covers	Fluted Bottleneck	Fluted Bottleneck	Fluted Bottleneck	Fluted Bottleneck	Bottleneck	Optional Covers	Fluted Decorative	Fluted Decorative	Fluted Decorative	Fluted Decorative	Fluted Bottleneck	Fluted Bottleneck	Fluted Bottleneck	Fluted Bottleneck	
Height	8', 10', 12', 14', 15', 16', 18', 20'	12', 14', 15', 16', 18', 20'	20', 21', 22', 23', 24', 25'	25', 26', 27', 28', 29', 30', 31', 32', 33', 34'	16', 18', 20', 22', 24', 26', 28', 30'	8', 10', 12', 13', 14', 15', 16', 18', 20'	12', 13', 14', 15', 16', 18', 20', 22', 23'	8', 10', 12', 14', 16', 18', 20'	8', 10', 12', 13', 14', 15', 16', 18', 20'	12', 13', 14', 15', 16', 18', 20', 22', 23'	8', 10', 12', 14', 16', 18', 20'	8', 10', 12', 14', 15', 16', 18', 20'	8', 10', 12', 13', 14', 15', 16', 18', 20'	12' - 20'	8', 10', 12', 14', 16', 18', 20', 22'	8', 10', 12', 14', 16', 18', 20'	10', 11', 12', 13', 14', 15'	8', 10', 12', 14', 15', 16', 18', 20'	8', 10', 12', 14', 16', 18', 20'	10', 11', 12', 13', 14'	12', 14', 16', 18'	22', 24', 26', 28'	8', 10', 12', 14', 15', 16', 18', 20'	12', 14', 16', 18'	10', 12', 14', 16', 18', 20'	12', 14', 16', 18', 20', 22', 24', 26', 28'	
Diameter	4"	5"	7-4" Tapered	8-5" Tapered	6-4", 7-4", 8-5" Tapered	4"	5-9/16"	6-4" Tapered	4"	5-9/16"	6-4" Tapered	4"	4"	5"	5-9/16"	6-4" Tapered	5"	5"	5"	5"	6"	8"	5"	6-4" Tapered	6-4" Tapered	8-4" Tapered	
Thickness	0.125", 0.226", 0.318"	0.17", 0.219", 0.247"	0.156", 0.188"	0.156", 0.188", 0.250"	0.156", 0.188", 0.250"	0.125", 0.226", 0.318"	0.258"	0.125", 0.250"	0.125", 0.226", 0.318"	0.258"	0.125", 0.188", 0.250"	0.125", 0.167", 0.226"	0.125", 0.226", 0.318"	0.170", 0.219", 0.247"	0.258"	0.125", 0.188", 0.250"	0.125", 0.250"	0.208"	0.208"	0.125", 0.188", 0.250"	0.125", 0.250"	0.188", 0.250"	0.208"	0.125", 0.250"	0.125", 0.250"	0.125", 0.156", 0.250"	
Base	10" Square	12-1/2" Square	11-1/4" Square	12" Square	12", 14", 16" Square	16", 18" Round	15" Round	18" Round	18" Round	18" Round	16" Round	15-1/2" Round	16-1/2" Round	16-1/2" Round	16-1/2" Round	16-1/2" Round	18" Round	11-1/2" Square	17" Round	17" Round	20" Round	24" Round	16-1/2" Round	16-1/2" Round	17-1/4" Round	23" Round	
Bolt Circle	8-1/2"	12-1/2"	10-1/2"	11-1/2"	10-1/2", 12-1/2", 14-1/2"	10-1/2", 12-1/2"	12-1/2"	12-1/2"	12-1/2"	12-1/2"	9-1/2"	12-1/2"	8-1/2"	12-1/2"	12-1/2"	9-1/2"	12-1/2"	12-1/2"	10-1/2"	10-1/2"	9-1/2"	11-1/2"	12-1/2"	9-1/2"	12-1/2"	12-1/2"	
Optional Base Covers	LBC1, LBC2, LBC3, LBC4C	LBC1, B105, B50	-	-	-	-	-	TBC1, TBC2	-	-	-	TBC1, TBC2	-	-	-	-	-	LBC1, B105, B50	-	-	-	LBC1, B105, B50	-	-	-	-	
EPA @ 90 MPH	3.27-18.64	5.86-21.72	9.65-18.30	8.87-25.65	N/A	5.32-30.00	14.78-30.00	9.97-30.00	6.70-30.00	14.78-30.00	7.23-30.00	3.82-29.69	3.27-18.64	5.86-21.72	11.44-30.00	7.95-30.00	11.14-30.00	7.40-27.56	8.75-30.00	10.33-30.00	9.59-30.00	14.61-30.00	7.40-27.56	9.77-30.00	14.11-30.00	12.49-30.00	
EPA @ 110 MPH	1.36-12.35	3.41-14.46	5.84-12.03	5.49-17.21	N/A	2.94-20.59	9.71-28.46	6.31-30.00	3.71-20.59	9.71-28.46	4.35-25.98	1.80-20.17	1.36-12.35	3.41-14.46	7.39-30.00	4.56-26.88	6.99-27.99	4.03-18.40	5.02-22.78	6.43-22.60	5.49-24.27	8.31-20.88	4.03-18.40	5.55-24.26	9.01-30.00	7.34-30.00	
EPA @ 120 MPH	1.19-10.28	2.72-12.13	4.77-10.06	4.38-14.40	N/A	2.21-17.35	8.07-23.89	5.20-30.00	2.80-17.35	8.07-23.89	3.50-21.93	1.22-16.98	1.19-10.28	2.72-12.13	6.08-30.00	3.62-22.63	5.69-23.57	2.97-15.40	3.85-19.15	5.18-18.97	4.20-20.20	6.34-17.04	2.97-15.40	4.29-20.20	7.37-30.00	5.67-25.24	
EPA @ 150 MPH	1.16-6.53	1.45-7.66	2.74-6.25	2.21-8.87	N/A	1.22-11.20	4.94-15.14	3.11-24.24	1.53-11.20	4.94-15.14	1.98-14.11	1.16-10.94	1.16-6.53	1.45-7.66	1.98-25.12	1.99-14.48	3.24-15.02	1.02-9.61	1.65-12.11	2.89-11.96	1.90-12.43	2.60-9.67	1.02-9.61	1.98-12.47	4.20-19.26	2.45-15.95	
Options	Buried Pole, Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Hinged Base, Banner Arm, Plant Support, Mid-Pole Luminaire, Optional Base Covers	Buried Pole, Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Hinged Base, Banner Arm, Plant Support, Mid-Pole Luminaire, Optional Base Covers	Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Mid-Pole Luminaire	Buried Pole, Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Hinged Base (AM6), Banner Arm, Plant Support, Mid-Pole Luminaire	Buried Pole, Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Buried Pole, Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Buried Pole, Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Buried Pole, Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Buried Pole, Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire
Finish	Refer to Finishes below																Refer to Finishes below										
Link																											

Available in Textured and Smooth finishes

WHTX White	GY3TX Medium Grey	BKTX Black	BE8TX Royal Blue	BE6TX Ocean Blue	BE2TX Midnight Blue	RD4TX Scarlet	RD2TX Burgundy	GNTX Green	GN4TX Blue Green	GN6TX Forest Green	GN8TX Dark Forest Green	BG2TX Sandstone	BRTX Bronze

Available in a variety of standard colors and finishes to suit your needs

These colors are available in smooth finishes (to order remove TX from code). Due to the porous nature of castings, a smooth finish may present minor imperfections. Textured finishes conceal pores and provide a more uniform finish.

Textured only Smooth only

TS Hammerstone Silver	TG Hammerstone Gold	NP Natural Aluminum

Special colors

SCLSpecial Color (liquid)  
SCPSpecial Color (powder)  
It is now possible to order smaller quantities of powder paint for a premium. Your representative can advise you if a powder coat paint can be developed for your project.

Custom colors

We support custom color options to the ultimate in color matching opportunities with your site lighting needs.