


Project: _____
 Location: _____
 Cat.No: _____
 Type: _____
 Lamps: _____ Qty: _____
 Notes: _____



Ordering Guide

Example: 197 3 V ABS A B WHT 12

Product Code	197	Street Sign
Fitter Size	3	3" Round
	4	4" Round
	5	5" Round
Lettering	V	Vinyl
Finish	ABS	Antique Brass
	ACP	Antique Copper
	ARD	Antique Red
	ASI	Antique Silver
	BLK	Black
	BRN	Brown
	BRZ	Bronze
	FGN	Forest Green
	GRA	Granite
	IRN	Ironstone
	RBZ	Rustic Bronze
	SRT	Shadow Rust
	VBZ	Verde Bronze
	VCP	Verde Copper
	VGN	Verde
	VTC	Vintage Copper
	WBZ	Weathered Bronze
	WHT	White
Print	A	Single Sided
	B	Double Sided
	N	None
Vinyl Lettering Style	B	Block *1
Letter Color	WHT	White
Wording	12	Spaces (12)

*1 Vinyl Lettering Style Only

Specifications

CONSTRUCTION:

Turned aluminum knob. Stamped aluminum 24" x 6" sign attached to arm with cast aluminum clamp-on brackets. (Sign has 23" x 4" lettering area on both sides.) Solid cast aluminum ladder rest. Engineer grade reflective green vinyl both sides. Vinyl number and/or letter both sides.

FINISH:

Resilient TGIC thermoset polyester powdercoat paint is electrostatically applied to every fixture. Specially formulated for Philips Outdoor Lighting, it provides UV protection, and the highest temperature rating in the industry. In addition to the standard color choices shown, a spectrum of custom colors is available.

MOUNTING:

Clamps onto a 3", 4", or 5" dia. post. (Post must be ordered separately.)

197 Accessories

Street sign

Specifications

WARRANTY:

Three-year limited warranty.

Height:

8"

Width:

32 1/2"

