


Frame-in Kit



Reflector Trim

Project: _____
 Location: _____
 Cat.No: _____
 Type: _____
 Lamps: _____ Qty: _____
 Notes: _____

Complete Fixture consists of Reflector Trim & Frame-In Kit. Select each separately.

2003R	Frame-In Kit								Reflector Trims — See Individual Reflector Trim Specification Sheets			
	Open Downlight				Pinhole	Open Wall Washer	Open Wet Location	Enclosed Diffuser				
Specular Reflector	Specular Cone		Satin Cone	Baffles					2011	2095 2096 2096CD	2084CD 2084WH	2090
	2045 2046 2046CD	2012 2012NM 2013 2013NM 2013WH	2013BK 2013BKNM 2013CD 2013CDNM	2008 2008NM 2010 2010NM	2005 2005BNM 2005WH 2005NM							

Features

- Mounting Ring:** .032 (#22 ga.) galvanized steel. Accommodates existing ceilings up to 2" thick. Attaches securely to any type of ceiling material without tools using (3) mounting straps provided. Push-in/twist-out clips hold reflector flush to ceiling. Includes adhesive backed aperture template.
- Junction Box:** 2 1/2" X 2 1/2" X 3 1/2" (21 cu. in.) .032 (#22 ga.) galvanized steel. U.L.listed for 90° C supply wire. Integral cable clamps permit attachment of non-metallic (#12 or #14 ga.) Romex® cable without tools or additional connectors. Attaches to mounting ring without tools.
- Socket Housing:** Impact extruded aluminum or galvanized steel.

- Socket:** Porcelain medium base; nickel plated screw shell. Pre-wired with #18 ga. SF1 (300 VOLT 200° C) leads to junction box.
- Thermal Protector:** Meets NEC and U.L. requirements. Do not install insulation within 3 inches of fixture sides or wiring compartment nor above fixture in such a manner as to entrap heat.

Options & Accessories

Replacement Clips (Set of 3): **1997**

Labels

UL (Suitable for Damp Locations)

Romex® is a registered trademark of General Cable Industries Inc.

