

Project: _____


Location: _____

Cat.No: _____

Type: _____

Lamps: _____ Qty: _____

Notes: _____



Ordering Guide

Example: 39DBL-3 ABS 18

Product Code	39DBL-3	Banner Arms
Finish	ABS	Antique Brass
	ACP	Antique Copper
	ARD	Antique Red
	ASI	Antique Silver
	BLK	Black
	BRN	Brown
	BRZ	Bronze
	FGN	Forest Green
	GRA	Granite
	IRN	Ironstone
	RBZ	Rustic Bronze
	SRT	Shadow Rust
	VBZ	Verde Bronze
	VCP	Verde Copper
	VGN	Verde
VTC	Vintage Copper	
WBZ	Weathered Bronze	
WHT	White	
Length	18	18"
	24	24"
	30	30"
	36	36"

Specifications

CONSTRUCTION:

Two cast aluminum brackets. Turned aluminum knobs. 24 1/2" long 7/8" dia. heavy wall pipes threaded and welded to cast aluminum brackets. 3" dia. post order separately.

FINISH:

Resilient TGIC thermoset polyester powdercoat paint is electrostatically applied to every fixture. Specially formulated for Philips Outdoor Lighting, it provides UV protection, and the highest temperature rating in the industry. In addition to the standard color choices shown, a spectrum of custom colors is available.

Height:

2 1/4"

Width:

55 1/2"

