



Project: _____
 Location: _____
 Cat.No: _____
 Type: _____
 Lamps: _____ Qty: _____
 Notes: _____

Ordering Guide

Example: B4 A

Product Code	B4	Incandescent Aluminum Bullyte
Finish	A H G	Black Bronze Verde

*1 US and CAN: 150 Watt PAR 38 Incandescent without lens and shroud (Cannot use HID in open fixture).
 *2 US: 100 Watt PAR 38 INC/HID with shroud / CAN: 70 Watt PAR 38 INC/HID with shroud.

Specifications

HOUSING:

Fully rotatable shroud, gasketed, cast aluminum. Die-cast aluminum. Fully-adjustable swivel arm with vibration-proof locking teeth. Gasketing is silicone. Fasteners are 300 series stainless steel. Shroud is optional. 1/2" NPS male threads to screw onto accessory mounting stake or junction box, sold separately.

FINISH:

Thermoset polyester powdercoat is electrostatically applied after a five-stage conversion cleaning process and bonded by heat fusion thermosetting.

OPTICAL ASSEMBLY:

Clear Tempered flat glass lens (glass comes with shroud)

LAMPING:

100W maximum PAR30/R30 or PAR38/R40 medium base lamp. 100W maximum MH medium base: E17 100W maximum MH medium base: PAR38 Lamp is not included. Lower wattage lamps are acceptable. HID PAR30 MH or MV acceptable with remote ballast (not included).

ELECTRICAL ASSEMBLY:

4kv rated porcelain mini-can base. Nickel-plated screw shell with center contact.

BALLAST:

Must order inground (IBH) or above ground (ABH) ballast housing separately.

CERTIFICATIONS:

Manufactured to ISO 9001:2008 Standards. ETL listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations.

WARRANTY:

Three-year limited warranty.

Width:

6 1/4" (159mm)

Length:

8-9/16" 218mm, (S)10-3/16" 259mm,(L)16-1/2" 419mm

Max. Weight:

2.2 lb., (S) 4.5 lb., (L) 8.15 lb.

