

# P150


## Light-Leveler Photocontrols

### Features

- Highly durable polycarbonate housing with field adjustable 1/2" threaded swivel base.
- Supplied complete with adjustable slider bar to vary turn-on level.
- 6" #14 AWG wire leads rated at 105°C.
- Fail mode ON, contacts normally closed.



### Dimensions



Catalogue No.	Volts	Max. Watts Incandescent	Max. Watts HID	
			HPF	NPF
P150A	120	1800	1000	400
P150B	208/240/277	1800	1000	400
P150W	347	1800	1000	400

### Job Information

### Type:

**Job Name:**

**Cat. No.:**

**Lamp(s):**

**Notes:**