







Real convenience for your operation's success. Tough and dependable luminaires designed for ease of handling and flexibility.

★	High
★	Medium
★	Low
-	NA

				
		Budget-grade	Value-grade	Specification-grade
		Best	Best	Best
		SofTrace LED	ClearAppeal LED	FormFlex LED
Applications	Description	Fully luminous aperture luminaire providing modern appeal to architectural spaces.	Reliable performance, elegant aesthetics, and affordability.	Fully luminous aperture offering a diffuse, perforated, opaque, or linear prism center channel accent for unique aesthetic flexibility.
	Education	★	★	★
	Office	★	★	★
	Healthcare	★	★	★
	Retail	★	★	★
Features	Sizes	1x4, 2x2, 2x4	1x4, 2x2, 2x4	1x4, 2x2, 2x4
	Depth	3-15/16"	3-15/16"	3-15/16"
	Ceiling Types	NEMA G & NFG	NEMA G & NFG	NEMA G & NFG
	Air Function	Downlight, Baffle, Adj. Accent, Gimbal, Pinhole, Wall Wash, & Shower Light	Downlight & Wall Wash	Downlight, Lensed Wall Wash, & Shower Light
	Reflector	Return, Chicago Plenum	Return, Chicago Plenum	Return, Chicago Plenum
	Finish	Antimicrobial	Antimicrobial	Antimicrobial
	Lens	Diffuse (smooth & ribbed)	Diffuse (smooth)	Diffuse (smooth, perforated, opaque, & linear prism)
	Installation	Flex Wiring, Install from Below & Wet Location	Flex Wiring, Install from Below & Wet Location	Flex Wiring, Install from Below & Wet Location
	DLC	Standard & Premium	Standard & Premium	Standard & Premium
	Lumens (Max)	3800, 4300, 4800, 5400, 7400	3800, 4300, 4800, 5400, 7400	3800, 4300, 4800, 5400, 7400
	Color Render Index	80 CRI	80 CRI	80 CRI & 90 CRI (Accurender)
Color Temperature	3000K, 3500K, 4000K, & 5000K	3000K, 3500K, 4000K, & 5000K	3000K, 3500K, 4000K, & 5000K	
Efficacy	up to 130lm/W	up to 130lm/W	up to 130lm/W	
Emergency	Self testing Battery Pack, UL924 Generator Transfer, Factory installed with drivers & sensors	Self testing Battery Pack, UL924 Generator Transfer, Factory installed with drivers & sensors	Self testing Battery Pack, UL924 Generator Transfer, Factory installed with drivers & sensors	
Voltage	120/277V & 347V	120/277V & 347V	120/277V & 347V	
Lifespan	5 year warranty @ 60,000hrs	5 year warranty @ 60,000hrs	5 year warranty @ 60,000hrs	
Sensors/Controls	SpaceWise	Yes	Yes	Yes
	Interact Ready	Interact Wireless & Interact Office POE	Interact Wireless & Interact Office POE	Interact Wireless & Interact Office POE
	Dimming	Lutron 0-10v to 5%, Step Dim to 40%, DALI, & Mark X phase dimming	Lutron 0-10v to 5%, Step Dim to 40%, DALI, & Mark X phase dimming	Lutron 0-10v to 5%, Step Dim to 40%, DALI, & Mark X phase dimming
	Link	 1x4	 2x2	 2x4