






Real convenience for your operation's success. Tough and dependable luminaires designed for ease of handling and flexibility.

						
Applicability	★ High	Budget-grade	Value-grade	Value-grade	Value-grade	Specification-grade
	★ Medium	Good	Better	Better	Better	Best
	★ Low	VTS Sealed Strip LED	Fluxstream LED Sealed Strip	DW Vaporlume LED	V2 Vaporlume LED	V3W Vaporlume LED
– NA						
Applications	Sports/Rec.	★	★	★	★	★
	Warehouse	★	★	★	★	★
	Manufacturing	★	★	★	★	★
	Cold Storage	★	★	★	★	★
	Complex Areas	★	★	★	★	★
Features	Sizes	2', 4', 8'	4', 8'	2', 4', 8'	2', 4', 8'	2', 4'
	Installation	Stainless steel latches, Wet location (IP66)	Wet location (IP6 optional)	Wet location (IP65/IP67/NSF)	Wet location (IP65/IP67/NSF) Stainless steel latches, Top & End hubs	Wet location (IP65/IP67/NEMA 4X/NSF)
	DLC	Standard	Standard	Standard	Standard	Standard & Premium
Performance	Lumens (Max)	2500, 2800, 5000, 5600, 10000, & 13000	4000, 6000, 8000, & 12000	2700, 3500, 4300, 5100, 7000, 10200, & 14000	7000, 10200, & 14000	2700, 3500, 4300, 5100, 7000, 8000, & 10000
	Color Render Index	80 CRI	80 CRI	80 CRI	80 CRI	80 CRI
	Color Temperature	3500K, 4000K, & 5000K	3000K, 3500K, 4000K, & 5000K	3000K, 3500K, 4000K, & 5000K	3000K, 3500K, 4000K, & 5000K	3000K, 3500K, 4000K, & 5000K
	Efficacy	up to 104lm/W	up to 122lm/W	up to 121lm/W	up to 122lm/W	up to 147lm/W
	Ambient Temp.	-30 to +40°C	-20 to +40°C	-20 to +40°C	-20 to +40°C	-20 to +40°C
	Emergency	Yes (field installed)	Yes	Yes	Yes	Yes
	Voltage	120-277V, 120/277V & 347V	120-277V, 120/277V & 347V	120-277V, 120/277V & 347V	120-277V, 120/277V & 347V	120-277V, 120/277V & 347V
	Lifespan	5 year warranty @ (L70) 50,000hrs	5 year warranty @ (L70) 100,000hrs	5 year warranty @ (L70) 100,000hrs	5 year warranty @ (L70) 100,000hrs	5 year warranty @ (L70) 100,000hrs
Sensors/Controls	Sensor	Occupancy (field installed)	Occupancy (field installed)	Occupancy (factory or field installed)	Occupancy (factory or field installed)	Occupancy (factory or field installed)
	SpaceWise	–	Yes	Yes	Yes	Yes
	Interact Ready	–	Yes	Yes	Yes	Yes
	Dimming	0-10V	0-10V	0-10V	0-10V	0-10V
	Link	