


Real convenience for your operation's success. Tough and dependable luminaires designed for ease of handling and flexibility.



★ High
★ Medium
★ Low
- NA

	Budget-grade	Budget-grade	Value-grade	Specification-grade	
	Good	Good	Better	Best	
	NWL LED Wraparound	Fluxstream EZ LED Wraparound	OWL LED Wraparound	Fluxstream LED Wraparound	
Applications	Education	★	★	★	
	Office	★	★	★	
	Healthcare	★	★	★	
	Retail	★	★	★	
	Industrial	-	★	-	★
	Residential	★	★	★	★
Features	Sizes	2', 4', 8'	4'	2', 4', 8'	4'
	Modular Wiring	Electro-Connect (see product spec sheet for details)	Electro-Connect (see product spec sheet for details)	Electro-Connect (see product spec sheet for details)	Electro-Connect (see product spec sheet for details)
	DLC	Standard	-	Standard	Standard
Performance	Lumens (Max)	4000	4000	3000, 4000, 5000, 7000	2000, 3000, 4000, 5500, 6000, 8000, 11000, 14000
	Lumens Field Selectable	1500, 2000, 2500, 3000, 4000, 5000, 6000, 8000, 10000	-	-	-
	Color Render Index	80 CRI	80 CRI	80 CRI	80 CRI
	Color Temperature	3500K, 4000K, & 5000K (color selectable)	3000K, 3500K, & 4000K	3000K, 3500K, 4000K, & 5000K	3000K, 3500K, 4000K, & 5000K
	Efficacy	-	up to 104lm/W	up to 106lm/W	up to 122lm/W
	Ambient Temp.	-10 to +35°C	-20 to +25°C	-20 to +25°C	-20 to +25°C
	Emergency	-	Yes	Yes	Yes
	Voltage	120/277V & 347V	120/277V & 347V	120/277V & 347V	120/277V & 347V
Sensors/Controls	Lifespan	5 year warranty	5 year warranty @ (L70) 50,000hrs	5 year warranty @ (L70) 50,000hrs	5 year warranty @ (L70) 100,000hrs
	Sensor	Occupancy	Occupancy	-	Occupancy
	SpaceWise	-	-	-	Yes
	Interact Ready	-	-	-	Yes
	Dimming	0-10V	-	0-10V	0-10V
	Link				