



	Best	Best	Best	Best
	PureForm Post Top LED Comfort	PureForm Post Top LED Precision	Form Ten Round Comfort	Form Ten Round Comfort
Prefix	PPT-C	PPT-P	S-CP20/MP20-C	S-CP20/MP20-P
Lumen Output Range	1,500-16,114	2,500-17,315	1,500-15,400	2,000-30,000
Efficacy	95-147	127-186	93-125	129-168
Distribution	Type 2, 3, 4, 5	Type 2, 3, 4, 5, back light control	Types 2, 3, 4, 5	Types 2, 3, 3W, 4, 4FT, 5
Color Temperature	2700, 3000, 3500, 4000, 5000	2700, 3000, 4000, 5000	2700*, 3000, 3500*, 4000, 5000*	2700, 3000, 4000, 5000
Mounting Height Range	10'-25'	10'-25'	15'-20'	15'-30'
0 Uplight	✓	✓	✓	✓
Auto Profile Dimming	✓	✓	✓	✓
Motion Response	✓	✓	✓	✓
Interact Controls	✓	✓	✓	✓
SR Drive with Zhaga Socket	✓	✓	✓	✓
Service Tag Standard	✓	✓	✓	✓
Additional Luminaire Options	Emergency Battery Backup (cold weather and standard), Field Adjustable Wattage Selector (FAWS)	Emergency Battery Backup (cold weather and standard), Field Adjustable Wattage Selector (FAWS)	Shielding, Fusing, Increased Surge Protection (20 kA)	Shielding, Fusing, Increased Surge Protection (20 kA)
Mounting	T3, T2	T3, T2	Square or 3"-4.5" Round pole	Square or 3"-4.5" Round pole
Finish	Bronze, Black, White, Medium Grey, Dark Grey	Bronze, Black, White, Medium Grey, Dark Grey	14 primary and accent finishes available	14 primary and accent finishes available
IP Rating	IP66	IP66	IP66	IP66
Vibration	Level 2 (3G)	Level 2 (3G)	Level 1 - Normal Applications	Level 1 - Normal Applications
DLC Listing	Premium/Standard	Premium/Standard	Standard and Premium	Standard and Premium
Certifications	UL/cUL	UL/cUL	UL/cUL	UL/cUL
Lifetime	L70>100,000h	L70>100,000h	L70>100,000h	L70>100,000h
Limited Warranty	5 years	5 years	5 years	5 years
Link			Coming soon	Coming soon