

KEENE

Outdoor

Wall Mount

Product Selection Guide

Keene features a variety of wall packs to suit a range of building types. Stonco wall mount luminaires are readily available and easy to install, making them a great choice for any project.



	Good	Good	Good	Better	Better	Better
	Wall Pack Dual Select	Adjustable Slim Wall Pack	Residential Wall Pack	LytePro Wall Small	LytePro Wall Medium	LytePro Wall Large
Prefix	WP	ASW	RWP	LPW7	LPW16	LPW32
Lumen Output Range	3860-12800	1800-9000	2600-4100	1050	2065-4629	6472-9637
Efficacy	128-145	120+	120	108	87-104	95-114
Distribution	-	-	-	Type 2	Type 3, 4	Type 3, 4
Color Temperature	3000K, 4000K, 5000K	3000K, 4000K, 5000K	3000K, 4000K, 5000K	3000K, 4000K	3000K, 4000K	3000K, 4000K
Mounting Height	10-25	-	7-10	7-10	10-15	15-25
0 Uplight	-	-	-	✓	✓	✓
Emergency (0°C to 40°C)	-	-	-	-	-	✓
Field Adjustable Wattage Selector (FAWS)	✓	✓	✓	-	-	✓
Motion Response	-	-	-	-	-	✓
Photocell	✓	✓	Button	Button	Button	Button
Finish	Bronze, White	Bronze	Bronze	Black, Bright, Bronze, Dark Grey, Medium Grey	Black, Bright, Bronze, Dark Grey, Medium Grey	Black, White, Bronze, Dark Grey, Medium Grey
IP Rating	IP65	IP65	IP65	IP65	IP65	IP65
DLC Listing	Standard	DLC 5.1 Premium	DLC 5.1 Premium	Standard	Standard	Standard
Certifications	cULus	cULus	cULus	cETLus	cETLus	cETLus
Lifetime	L70-54000h	L70-54,000h	L70	L70-60,000h	L70-54,000h	L70-54000h
Limited Warranty	5 years	5 years	5 years	5 years	5 years	5 years
Link						