

Gardco and Stonco garage and canopy luminaires provide a high quality solution specifically designed to meet the unique challenges of these applications. Whether you are seeking energy savings or require an enhanced sense of security and optimal light levels, our portfolio has you covered.



Stonco



Stonco



Stonco



GARDCO



GARDCO



GARDCO



GARDCO

	Good	Good	Better	Better	Best	Best	Best
	Garage and Canopy Dual Select	Garage and Canopy Round Dual Select	LytePro Garage and Canopy	G3	SoftView	SlenderForm Canopy	SlenderForm Canopy Recessed
Prefix	GC	GCR	LPGC	G3	SVPG	SFC	SFCR
Lumen Output Range	4,100-12,850	3,870-13,310	1843-10124	2,751-13,239	1,884-18,054	4,630-14,700	4,630-12,028
Efficacy	125-150	120-140	154-179	104-148	84-135	91-125	95-125
Distribution	Type 5 Symmetric	Type 5 Symmetric	Type 5 Square, Type 5 Concentrated Downlight	Type 5 Square, Concentrated Downlight, Type 1R, Type 3	Type 5, Concentrated Downlight, Type 1R, Type 3	Type 5 Wide, Type 5 Rectangular, Concentrated Downlight, Type 3	Type 5 Wide, Type 5 Rectangular, Concentrated Downlight, Type 3
Color Temperature	3000, 4000, 5000K (Field Selectable)	3000, 4000, 5000K (Field Selectable)	3000K, 4000K	3000, 4000, 5000	3000, 4000, 5000	3000, 4000, 5000	3000, 4000, 5000
Uplight	-	-	✓	-	✓	-	-
Motion Response	✓	✓	✓	✓	(Bluetooth programmable or microwave)	✓	-
Interact ready	-	-	✓	-	✓	-	-
Photocell	✓	✓	-	Button	-	Button	-
Additional Options	-	-	LPES Shield, Bird Spikes, J-box with 4 side conduit entries, Remote controls	Bird Guard, Balanced offset J-box for pendant	Shielding, various Bird Guards, Wire Guard	Glass lens, Diffuse lens, Bird Guard, J-box for pendant	Glass lens, Diffuse lens, Bird Guard
Mounting	Surface Mount	Surface Mount	Surface Mount, Pendant Mount	Surface Mount	Surface Mount, Pendant Mount, Trunnion Mount, Wall Mount	Surface Mount	Recessed
Vibration	-	-	Bridge/Overpass	Bridge/Overpass option	Normal or Bridge/Overpass	-	-
Finish	Bronze	Bronze	Medium Gray (opaque), Luminous White (translucent)	Bronze, White, Black, Medium Grey	Bronze, White, Medium Grey	Medium Grey	Medium Grey
IP Rating	IP65	IP65	IP66	IP66	IP66	IP65 luminaire with IP66 LED modules	IP65 luminaire with IP66 LED modules
IK Rating	-	-	IK10	-	IK10	-	-
Surge Protection	-	-	10kV/10kA	10kV/10kA	10kV/10kA standard, 20kV/10kA option	10kV/10kA	10kV/10kA
DLC Listing	Standard	Standard	Premium	Standard and Premium	Standard and Premium	Standard	Standard
Certifications	cULus	cULus	cULus	cULus	cULus	cULus	cULus
Lifetime	L70->60,000h	L70->60,000h	L70->100,000h	L70->100,000h	L70->100,000h	L70->100,000h	L70->100,000h
Luminaire Useful Life	-	-	100,000+ hours accounting for LED life, driver life, etc. - see specification sheet for details				
Limited Warranty	5 years	5 years	5 years	5 years	5 years	5 years	5 years
Link							