

Gardco and Stonco site and area luminaires blend excellent performance with award winning aesthetics. Multiple styles are available for a range of different mounting heights and applications.



Brand	Stonco	GARDCO	GARDCO	GARDCO	GARDCO	GARDCO	GARDCO	GARDCO	GARDCO	GARDCO	GARDCO	GARDCO	GARDCO	GARDCO	GARDCO	
Rating	Better	Better	Better	Better	Better	Better	Better	Better	Better	Best	Best	Best	Best	Best	Best	Best
Product	LytePro Area	OptiForm Area Small	OptiForm Area Medium	OptiForm Area Large	EcoForm Area Small	EcoForm Area Large	PowerForm Site and Area	Gullwing Large LED	Form Ten Round Comfort	Form Ten Round Precision	Site and Area Small Round Comfort	Site and Area Small Square Comfort	Site and Area Small Round Precision	Site and Area Small Square Precision	PureForm Area P26	
Prefix	LPA	OPF-S	OPF-M	OPF-L	ECF-S	ECF-L	PFAS	GL18	S-CA20/MA20-C	S-CA20/MA20-P	P20-C	P15-C	P20-P	P15-P	P26	
Lumen Output Range (4000K, 70CRI)	2,500-28,000	7,000-22,000	13,500-34,000	34,000-67,000	5713-27,526	29,299-50,641	34,640-103,975	5,710-29,497	1,690-17,700	2,600-34,8100	1,500-16,500	2,200-10,800	2,400-19,000	1,700-16,500	12,000-62,000	
Efficacy (4000K, 70CRI)	142-187	140-183	150-190	150-190	113-133	112-128	87-119	87-124	102-144	146-195	92-150	103-126	163-205	109-160	187-150	
Distributions	Type 2, 3, 4, 5	Type 2, 3, 4, 4W 5, 5N, 5W, AFR, BLC, LEED Corner	Type 2, 3, 4, 4W 5, 5N, 5W, AFR, BLC, LEED Corner	Type 2, 3, 4, 4W 5, 5N, 5W, AFR, BLC, LEED Corner	Type 2, 3, 4, 5, 5W, AFR	Type 2, 3, 4, 5, 5W, AFR	Type 2, 3, 4, 5W, AFR	Type 2, 3, 4, 5	Types 2, 3, 4, 5	Types 2, 3, 3W, 4, 4FT, 5	Type 2, 3, 4, 5	T1S, T2S, T4S, 4CD, T5S	Type 2, 3, 4, 4W 5, 5N, 5W, AFR, BLC, LEED Corner	T2M, T3M, T4S, T5S, BLC	Type 2, 3, 4, 4W 5, 5N, 5W, AFR, BLC, LEED Corner	
Color Temperatures (K)	3000, 4000, 5000	2700, 3000, 4000, 5000	2700, 3000, 4000, 5000	2700, 3000, 4000, 5000	3000, 4000, 5000	3000, 4000, 5000	3000, 4000	3000, 4000, 5700	2700*, 3000, 3500*, 4000, 5000*	2700, 3000, 4000, 5000	2700*, 3000, 3500*, 4000, 5000*	2700*, 3000, 3500*, 4000, 5000*	2700*, 3000, 4000, 5000	2700*, 3000, 3500*, 4000, 5000*	2700, 3000, 4000, 5000	
Mounting Height Range	8'-30'	8'-20'	20'-30'	25'-50'	8-40'	8-40'	8-40'	8-40'	15' - 20'	15' - 30'	10'-25'	10'-25'	10'-25'	10'-25'	20-40'	
0 Uplight	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
Field Adjustable Wattage Selector (FAWS)	✓	✓	✓	✓	✓	✓	-	-	✓	✓	✓	✓	✓	✓	✓	✓
Dual Circuit Control	-	-	-	-	✓	✓	✓	✓	-	-	-	-	✓	-	✓	✓
Auto Profile Dimming	-	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
Motion Response	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
Microwave Hidden Motion Response	-	-	-	-	-	-	-	-	✓	✓	✓	✓	-	-	-	-
Interact Outdoor	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	-	-	✓	✓	✓
SR Driver with Zhaga Socket	✓	✓	✓	✓	✓	✓	-	-	✓	✓	✓	✓	✓	✓	✓	✓
Service Tag Standard	✓	✓	✓	✓	✓	✓	✓	-	✓	✓	-	-	-	✓	✓	✓
Photocell	Button, TLRD7	Button, TLRD5, TLRD7	Button, TLRD5, TLRD7	Button, TLRD5, TLRD7	Button, TLRD5,TLRD7,TLRPC	Button, TLRD5,TLRD7,TLRPC	Button, TLRD5,TLRD7,TLRPC	Button, TLRD7	Button, TLRD7	Button, TLRD7	Button, TLRD5, TLRD7	Button, TLRD5, TLRD7	Button, TLRD5, TLRD7	Button, TLRD5, TLRD7	Button, TLRD7	
Additional Options	Shielding	Shielding, Fusing, Increased Surge Protection (20 kA)	Shielding, Fusing, Increased Surge Protection (20 kA)	Shielding, Fusing, Increased Surge Protection (20 kA)	Increased Surge Protection (20 kA)	Increased Surge Protection (20 kA)	Increased Surge Protection (20 kA)	-	Shielding, Fusing, Increased Surge Protection (20 kA)	Shielding, Fusing, Increased Surge Protection (20 kA)	Increased Surge Protection (20 kA)	Increased Surge Protection (20 kA)	Increased Surge Protection (20 kA)	Increased Surge Protection (20 kA)	Increased Surge Protection (20 kA)	Shielding, Fusing, Increased Surge Protection (20 kA)
Mounting	Standard Retrofit Arm	Standard Retrofit Arm, Mast Arm, Wall Mount	Standard Retrofit Arm, Mast Arm, Wall Mount	Standard Retrofit Arm, Mast Arm, Wall Mount	Standard Arm, Adjustable Slipfitter, Wall Mount, Retrofit Arm Mount	Standard Arm, Adjustable Slipfitter, Wall Mount, Retrofit Arm Mount	Arm Mount, Slip Fitter Mount	Pole Mounted	Square or 3"-4.5" Round pole	Square or 3"-4.5" Round pole	Standard Arm, Wall Mount, Retrofit Arm Mount	Standard Arm, Wall Mount, Retrofit Arm Mount	Standard Arm, Wall Mount, Retrofit Arm Mount	Standard Arm, Wall Mount, Retrofit Arm Mount	Standard Arm, Adjustable Slipfitter, Wall Mount, Retrofit Arm Mount	
Finish	Bronze, Black, White, Medium Grey, Dark Grey	Bronze, Black, White, Medium Grey, Dark Grey	Bronze, Black, White, Medium Grey, Dark Grey	Bronze, Black, White, Medium Grey, Dark Grey	Bronze, Black, White, Medium Grey, Dark Grey	Bronze, Black, White, Medium Grey, Dark Grey	Bronze, Black, White, Medium Grey, Dark Grey	Bronze, Black, White, Natural Aluminium	14 primary and accent finishes available	14 primary and accent finishes available	Bronze, Black, White, Medium Grey, Dark Grey	Bronze, Black, White, Medium Grey, Dark Grey	Bronze, Black, White, Medium Grey, Dark Grey	Bronze, Black, White, Medium Grey, Dark Grey	Bronze, Black, White, Medium Gray, Dark Gray	
IP Rating	IP66 Light Engine, UL Wet Location Luminaire	IP65 Luminaire, IP66 Light Engine	IP65 Luminaire, IP66 Light Engine	IP65 Luminaire, IP66 Light Engine	IP66	IP66	IP66	IP66	IP66	IP66	IP66	IP65	IP65	IP65	IP66	
Vibration	Level 1 (1.5G)	3G/Level 2 Bridge and Overpass Rated	3G/Level 2 Bridge and Overpass Rated	3G/Level 2 Bridge and Overpass Rated	3G	3G	1.5G	-	Level 1 - Normal Applications	Level 1 - Normal Applications	Level 2	Level 2	Level 2	Level 2	Level 2 - Bridge & Overpass	
DLC Listing	Premium	Premium	Premium	Premium	Premium	Premium	Standard	Standard	Standard and Premium	Standard and Premium	Standard & Premium	Standard & Premium	Standard & Premium	Standard & Premium	Premium	
Certifications	UL/cUL	UL/cUL	UL/cUL	UL/cUL	UL/cUL	UL/cUL	cULus	UL/cUL	UL/cUL	UL/cUL	UL/cUL	UL/cUL	UL/cUL	UL/cUL	UL/cUL	
Lifetime	L70 >100,000h	L70 >100,000h	L70 >100,000h	L70 >100,000h	L70 >100,000h	L70 >100,000h	L70 >100,000h	L70 >100,000h	L70 >100,000h	L70 >100,000h	L70 >100,000h	L70 >100,000h	L70 >100,000h	L70 >100,000h	L70 >100,000h	
Limited Warranty	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	
Link									Coming soon	Coming soon						