LIGHTOLIER

by (s) ignify

3D printed lighting

Decorative High Bay

IHB Series



Lightolier 3D Printed Decorative High Bay, IHB series, takes a classic form redesigned in a intergrated modern modular decorative form. Its not often that a traditional High Bay gets a complete redesign makeover! Light-weight yet durable polycarbonate construction reduces weight that helps ease handling during installation. Unleash your inner creator and select from a variety of color options to help tailor your design.

Project:			
Location	n:		
Cat.No:			
Туре:			
Qty:			
Notes:			

All product specializations, dimensions and styles are preliminarily and are subject to change.

Medium fixture

example: 3DP I HB M CL LF WHGL LF 10/14/20L 940

	Shape	Size M	Lower Shade		Upper Shade			
Series 3DP I HB			Color	Texture	Color	Texture	Lumens 10/14/20L	CRI/CCT
3D Printed E Intergrated High Bay L	BL Bell	M Medium (17.5"/444.5 mm)	CL Clear WHTL Trans. White GYSM Smokey Grey	LF Layered Fine TC Tufted Coarse (Transparent)	WHST White GNMT Enamel Green Fine 10,0	10/14/20 10,000/ 14,000/	935 90 CRI / 3500 K CCT	
	LA Layers	M Medium (21"/534mm)	CL Clear WHTL Trans. White GYSM Smokey Grey	LF Layered Fine TC Tufted Coarse (Transparent)	DGYS Dark Grey SIST Silver GDST Gold BZST Bronze BKMT Black BLMT Steel Blue Matallic colors	LF Layered Fine	20,000 lm (Switchable)	940 90 CRI / 4000 K CCT
	BN Barn	M Medium (15.67"/398 mm)	- None	- None	PKME Rose Gold (Pink) PUME Purple BLME Blue GNME Green	LF Layered Fine FC Facets		

 $\textbf{Note:} \ \textbf{Different colors, textures and custom logo options are available upon request, but will take a longer lead time to produce. . \\$

Large fixture

example: 3DP I HB L CL LF WHGL LF 24/28/31L 940

			Lower Shade		Upper Shade			
Series 3DP I HB	Shape	Size	Color	Texture	Color	Texture	Lumens 25/30/33L	CRI/CCT
3DP I HB 3D Printed Intergrated High Bay	BL Bell	L Large (19.5"/495.3 mm)	CL Clear WHTL Trans. White GYSM Smokey Grey	LF Layered Fine TC Tufted Coarse (Transparent)	Satin colors WHST White GNMT Enamel Green GYST Grey BRMT Stone Brown	LF Layered Fine	25/30/33 25,000 / 30,000 / 33,000 lm (Switchable)	935 90 CRI / 3500 K CCT 940 90 CRI / 4000 K CCT
	LA Layers	L Large (23"/584mm)	CL Clear WHTL Trans. White GYSM Smokey Grey	LF Layered Fine TC Tufted Coarse (Transparent)	DGYS Dark Grey SIST Silver GDST Gold BZST Bronze BKMT Black (9004) BLMT Steel Blue Matallic colors	LF Layered Fine		
	BN Barn	L Large (18.15"/461mm)	- None	- None	PKME Rose Gold (Pink) PUME Purple BLME Blue GNME Green	LF Layered Fine FC Facets		

Note: Different colors, textures and custom logo options are available upon request, but will take a longer lead time to produce. .









