

Day-Brite



by Signify

IES INDOOR REPORT PHOTOMETRIC FILENAME : RBX20L835-A22R.IES

DESCRIPTION INFORMATION (From Photometric File)

IESNA:LM-63-2002
[TEST] FO36346.PSO
[TESTLAB] DAY-BRITE PHOTOMETRIC LABORATORY
[ISSUEDATE] 4/29/16
[MANUFAC] SIGNIFY DAY-BRITE - CFI
[LUMCAT] RBX20L835-UNV-WT-A22R
[LUMINAIRE] RBX 22"
[MORE] ALUMINUM OPEN HIGHBAY 4-DLS3 2015 3500K BOARDS 2-95W DRIVERS 2.94K RESISTORS
[LAMP] LED. LUMINAIRE OUTPUT = 16105 LUMENS
[TESTDATE] 4/29/16
[_LM79] Absolute Photometry tested in accordance with IES procedure LM79-08

CHARACTERISTICS

Lumens Per Lamp	N.A. (absolute)
Total Lamp Lumens	N.A. (absolute)
Luminaire Lumens	16105
Total Luminaire Efficiency	N.A.
Luminaire Efficacy Rating (LER)	102
Total Luminaire Watts	158.2
Ballast Factor	1.00
CIE Type	Direct
Spacing Criterion (0-180)	1.02
Spacing Criterion (90-270)	1.02
Spacing Criterion (Diagonal)	1.02
Basic Luminous Shape	Circular w/ Sides
Luminous Length (0-180)	1.83 ft (Diameter)
Luminous Width (90-270)	1.83 ft (Diameter)
Luminous Height	1.17 ft



LUMINANCE DATA (cd/sq.m)

Angle In Degrees	Average 0-Deg	Average 45-Deg	Average 90-Deg
45	7388	7388	7388
55	2061	2061	2061
65	1064	1064	1064
75	469	469	469
85	83	83	83

IES INDOOR REPORT
PHOTOMETRIC FILENAME : RBX20L835-A22R.IES

CANDELA TABULATION

	<u>0.0</u>	<u>22.5</u>	<u>45.0</u>	<u>67.5</u>	<u>90.0</u>	<u>112.5</u>	<u>135.0</u>	<u>157.5</u>	<u>180.0</u>	<u>202.5</u>
0.0	13457.2	13457.2	13457.2	13457.2	13457.2	13457.2	13457.2	13457.2	13457.2	13457.2
2.5	13439.0	13439.0	13439.0	13439.0	13439.0	13439.0	13439.0	13439.0	13439.0	13439.0
5.0	13373.5	13373.5	13373.5	13373.5	13373.5	13373.5	13373.5	13373.5	13373.5	13373.5
7.5	13245.8	13245.8	13245.8	13245.8	13245.8	13245.8	13245.8	13245.8	13245.8	13245.8
10.0	13039.4	13039.4	13039.4	13039.4	13039.4	13039.4	13039.4	13039.4	13039.4	13039.4
12.5	12733.3	12733.3	12733.3	12733.3	12733.3	12733.3	12733.3	12733.3	12733.3	12733.3
15.0	12325.1	12325.1	12325.1	12325.1	12325.1	12325.1	12325.1	12325.1	12325.1	12325.1
17.5	11808.9	11808.9	11808.9	11808.9	11808.9	11808.9	11808.9	11808.9	11808.9	11808.9
20.0	11192.2	11192.2	11192.2	11192.2	11192.2	11192.2	11192.2	11192.2	11192.2	11192.2
22.5	10519.0	10519.0	10519.0	10519.0	10519.0	10519.0	10519.0	10519.0	10519.0	10519.0
25.0	9839.3	9839.3	9839.3	9839.3	9839.3	9839.3	9839.3	9839.3	9839.3	9839.3
27.5	9201.7	9201.7	9201.7	9201.7	9201.7	9201.7	9201.7	9201.7	9201.7	9201.7
30.0	8525.1	8525.1	8525.1	8525.1	8525.1	8525.1	8525.1	8525.1	8525.1	8525.1
32.5	7612.7	7612.7	7612.7	7612.7	7612.7	7612.7	7612.7	7612.7	7612.7	7612.7
35.0	6501.8	6501.8	6501.8	6501.8	6501.8	6501.8	6501.8	6501.8	6501.8	6501.8
37.5	5337.5	5337.5	5337.5	5337.5	5337.5	5337.5	5337.5	5337.5	5337.5	5337.5
40.0	4246.8	4246.8	4246.8	4246.8	4246.8	4246.8	4246.8	4246.8	4246.8	4246.8
42.5	3220.1	3220.1	3220.1	3220.1	3220.1	3220.1	3220.1	3220.1	3220.1	3220.1
45.0	2317.8	2317.8	2317.8	2317.8	2317.8	2317.8	2317.8	2317.8	2317.8	2317.8
47.5	1487.5	1487.5	1487.5	1487.5	1487.5	1487.5	1487.5	1487.5	1487.5	1487.5
50.0	950.7	950.7	950.7	950.7	950.7	950.7	950.7	950.7	950.7	950.7
52.5	740.5	740.5	740.5	740.5	740.5	740.5	740.5	740.5	740.5	740.5
55.0	625.2	625.2	625.2	625.2	625.2	625.2	625.2	625.2	625.2	625.2
57.5	525.8	525.8	525.8	525.8	525.8	525.8	525.8	525.8	525.8	525.8
60.0	440.1	440.1	440.1	440.1	440.1	440.1	440.1	440.1	440.1	440.1
62.5	366.0	366.0	366.0	366.0	366.0	366.0	366.0	366.0	366.0	366.0
65.0	302.0	302.0	302.0	302.0	302.0	302.0	302.0	302.0	302.0	302.0
67.5	246.3	246.3	246.3	246.3	246.3	246.3	246.3	246.3	246.3	246.3
70.0	197.9	197.9	197.9	197.9	197.9	197.9	197.9	197.9	197.9	197.9
72.5	156.0	156.0	156.0	156.0	156.0	156.0	156.0	156.0	156.0	156.0
75.0	119.8	119.8	119.8	119.8	119.8	119.8	119.8	119.8	119.8	119.8
77.5	88.4	88.4	88.4	88.4	88.4	88.4	88.4	88.4	88.4	88.4
80.0	61.3	61.3	61.3	61.3	61.3	61.3	61.3	61.3	61.3	61.3
82.5	38.1	38.1	38.1	38.1	38.1	38.1	38.1	38.1	38.1	38.1
85.0	18.3	18.3	18.3	18.3	18.3	18.3	18.3	18.3	18.3	18.3
87.5	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9
90.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
112.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

IES INDOOR REPORT
PHOTOMETRIC FILENAME : RBX20L835-A22R.IES

CANDELA TABULATION - (Cont.)

135.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155.0	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
157.5	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3
160.0	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8
162.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
165.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
167.5	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
170.0	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9
172.5	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2
175.0	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6
177.5	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8
180.0	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9

Vert. Angles **Horizontal Angles**

	<u>225.0</u>	<u>247.5</u>	<u>270.0</u>	<u>292.5</u>	<u>315.0</u>	<u>337.5</u>	<u>360.0</u>
0.0	13457.2	13457.2	13457.2	13457.2	13457.2	13457.2	13457.2
2.5	13439.0	13439.0	13439.0	13439.0	13439.0	13439.0	13439.0
5.0	13373.5	13373.5	13373.5	13373.5	13373.5	13373.5	13373.5
7.5	13245.8	13245.8	13245.8	13245.8	13245.8	13245.8	13245.8
10.0	13039.4	13039.4	13039.4	13039.4	13039.4	13039.4	13039.4
12.5	12733.3	12733.3	12733.3	12733.3	12733.3	12733.3	12733.3
15.0	12325.1	12325.1	12325.1	12325.1	12325.1	12325.1	12325.1
17.5	11808.9	11808.9	11808.9	11808.9	11808.9	11808.9	11808.9
20.0	11192.2	11192.2	11192.2	11192.2	11192.2	11192.2	11192.2
22.5	10519.0	10519.0	10519.0	10519.0	10519.0	10519.0	10519.0
25.0	9839.3	9839.3	9839.3	9839.3	9839.3	9839.3	9839.3
27.5	9201.7	9201.7	9201.7	9201.7	9201.7	9201.7	9201.7
30.0	8525.1	8525.1	8525.1	8525.1	8525.1	8525.1	8525.1
32.5	7612.7	7612.7	7612.7	7612.7	7612.7	7612.7	7612.7
35.0	6501.8	6501.8	6501.8	6501.8	6501.8	6501.8	6501.8
37.5	5337.5	5337.5	5337.5	5337.5	5337.5	5337.5	5337.5
40.0	4246.8	4246.8	4246.8	4246.8	4246.8	4246.8	4246.8
42.5	3220.1	3220.1	3220.1	3220.1	3220.1	3220.1	3220.1
45.0	2317.8	2317.8	2317.8	2317.8	2317.8	2317.8	2317.8
47.5	1487.5	1487.5	1487.5	1487.5	1487.5	1487.5	1487.5
50.0	950.7	950.7	950.7	950.7	950.7	950.7	950.7
52.5	740.5	740.5	740.5	740.5	740.5	740.5	740.5
55.0	625.2	625.2	625.2	625.2	625.2	625.2	625.2
57.5	525.8	525.8	525.8	525.8	525.8	525.8	525.8
60.0	440.1	440.1	440.1	440.1	440.1	440.1	440.1
62.5	366.0	366.0	366.0	366.0	366.0	366.0	366.0
65.0	302.0	302.0	302.0	302.0	302.0	302.0	302.0
67.5	246.3	246.3	246.3	246.3	246.3	246.3	246.3
70.0	197.9	197.9	197.9	197.9	197.9	197.9	197.9
72.5	156.0	156.0	156.0	156.0	156.0	156.0	156.0
75.0	119.8	119.8	119.8	119.8	119.8	119.8	119.8
77.5	88.4	88.4	88.4	88.4	88.4	88.4	88.4
80.0	61.3	61.3	61.3	61.3	61.3	61.3	61.3

IES INDOOR REPORT
PHOTOMETRIC FILENAME : RBX20L835-A22R.IES

CANDELA TABULATION - (Cont.)

82.5	38.1	38.1	38.1	38.1	38.1	38.1	38.1
85.0	18.3	18.3	18.3	18.3	18.3	18.3	18.3
87.5	2.9	2.9	2.9	2.9	2.9	2.9	2.9
90.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
112.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155.0	0.7	0.7	0.7	0.7	0.7	0.7	0.7
157.5	1.3	1.3	1.3	1.3	1.3	1.3	1.3
160.0	1.8	1.8	1.8	1.8	1.8	1.8	1.8
162.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
165.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
167.5	3.4	3.4	3.4	3.4	3.4	3.4	3.4
170.0	3.9	3.9	3.9	3.9	3.9	3.9	3.9
172.5	4.2	4.2	4.2	4.2	4.2	4.2	4.2
175.0	4.6	4.6	4.6	4.6	4.6	4.6	4.6
177.5	4.8	4.8	4.8	4.8	4.8	4.8	4.8
180.0	4.9	4.9	4.9	4.9	4.9	4.9	4.9

IES INDOOR REPORT
PHOTOMETRIC FILENAME : RBX20L835-A22R.IES

ZONAL LUMEN SUMMARY

Zone	Lumens	%Lamp	%Fixt
0-20	4710.69	N.A.	29.30
0-30	9236.12	N.A.	57.40
0-40	13240.28	N.A.	82.20
0-60	15644.14	N.A.	97.10
0-80	16078.73	N.A.	99.80
0-90	16103.18	N.A.	100.00
10-90	14837.11	N.A.	92.10
20-40	8529.59	N.A.	53.00
20-50	10357.35	N.A.	64.30
40-70	2708.38	N.A.	16.80
60-80	434.59	N.A.	2.70
70-80	130.07	N.A.	0.80
80-90	24.45	N.A.	0.20
90-110	0.00	N.A.	0.00
90-120	0.00	N.A.	0.00
90-130	0.00	N.A.	0.00
90-150	0.00	N.A.	0.00
90-180	1.52	N.A.	0.00
110-180	1.52	N.A.	0.00
0-180	16104.7	N.A.	100.00

Total Luminaire Efficiency = N.A. %

ZONAL LUMEN SUMMARY

Zone	Lumens
0-10	1266.08
10-20	3444.61
20-30	4525.43
30-40	4004.16
40-50	1827.75
50-60	576.10
60-70	304.52
70-80	130.07
80-90	24.45
90-100	0.00
100-110	0.00
110-120	0.00
120-130	0.00
130-140	0.00
140-150	0.00
150-160	0.31
160-170	0.80
170-180	0.41


IES INDOOR REPORT
PHOTOMETRIC FILENAME : RBX20L835-A22R.IES

COEFFICIENTS OF UTILIZATION - ZONAL CAVITY METHOD

Effective Floor Cavity Reflectance 0.20

RC	80				70				50			30			10			0
	RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	104	110	107	105	103	103	101	99	100	98	96	96	95	94	92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	87	85	84
3	100	93	87	83	98	91	86	82	89	84	80	86	82	79	84	81	78	76
4	94	86	79	74	92	84	79	74	82	77	73	80	76	72	78	74	71	70
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64
6	83	73	67	62	82	73	66	62	71	65	61	70	65	61	68	64	60	59
7	79	68	62	57	77	68	61	57	66	61	56	65	60	56	64	59	56	54
8	74	64	57	53	73	63	57	53	62	56	52	61	56	52	60	55	52	50
9	70	60	53	49	69	59	53	49	58	53	49	57	52	48	56	52	48	47
10	67	56	50	45	66	56	49	45	55	49	45	54	49	45	53	48	45	44

POLAR GRAPH



Maximum Candela = 13457.2 Located At Horizontal Angle = 0, Vertical Angle = 0
1 - Vertical Plane Through Horizontal Angles (0 - 180) (Through Max. Cd.)