

PureStyle Intelligent Color Powercore, RGBA

Premium concealed interior linear LED luminaire with intelligent color light

Date: _____
 Type: _____
 Firm Name: _____
 Project: _____

Innovative PureStyle Powercore luminaires bring lighting professionals high output in a compact, easily concealed luminaire. PureStyle delivers exceptionally high-quality light for a wide range of interior applications from cove to wall-washing to backlighting and beyond. Here are just some of the powerful advantages that PureStyle brings to lighting professionals and their clients.

- Unbeatable Performance—Major innovations, including a unique optical cluster, enable PureStyle to deliver up to 800 lumens – all with superior beam quality that delivers bright, smooth light.
- Simple - Directly processes 100 to 277 VAC input, all in one slim housing, eliminating the need for bulky external low voltage power supplies and related cabling limitations, allowing for greater installation flexibility and a lean installation.
Optional On-Off or DMX-512 control allows for dimming and dynamic control with industry standard protocols, allowing for easy setup and 3rd party system integration.
- White and Color Light — PureStyle combines tunable white and dynamic color light in one innovative, high-performance luminaire that's easy to install and control.



[Product page](#)

Beam Angle	10° x 60°, 30° x 60°, 100° x 100°
Lumens per foot*	481 to 549
LED Channels	Red/Green/Blue/Amber

Input Voltage	100 to 277 VAC, auto-ranging, 50/60 Hz
Weight	0.5 kg (1.1 lb) 305 mm 1.8 kg (4.2 lb) 1219 mm
Housing Material	Extruded anodized aluminium, white powder-coated finish
Approbations	UL/cUL, FCC Class B, CE, PSE, CQC, RCM
Environment	Dry/Damp Location, IP20
Applications	Cove Lighting, Wall Grazing, Wall Washing

Specification Sheets

PDF Download	Beam Angle	Lumens*	Efficacy	Power	Weight	Item Number	12 NC
10° x 60°, 305 mm (12 in), Narrow Beam Angle	10° x 60°	549	42	13 W	0.5 kg (1.1 lb)	123-000026-02	912400133456
10° x 60°, 1219 mm (48 in), Narrow Beam Angle	10° x 60°	2,196	42	52 W	1.8 kg (4.2 lb)	123-000026-05	912400133459
30° x 60°, 305 mm (12 in), Medium Beam Angle	30° x 60°	481	39	13 W	0.5 kg (1.1 lb)	123-000026-01	912400133455
30° x 60°, 1219 mm (48 in), Medium Beam Angle	30° x 60°	1,924	39	52 W	1.8 kg (4.2 lb)	123-000026-04	912400133458

Specification Sheets (cont.)

PDF Download	Beam Angle	Lumens*	Efficacy	Power	Weight	Item Number	I2 NC
100° x 100°, 305 mm (12 in), Wide Beam Angle	100° x 100°	528	41	13 W	0.5 kg (1.1 lb)	123-000026-00	912400133454
100° x 100°, 1219 mm (48 in), Wide Beam Angle	100° x 100°	2,112	41	52 W	1.8 kg (4.2 lb)	123-000026-03	912400133457

* Lumen output measurements comply with IES LM-79-08 testing procedures.



© 2019 Signify Holding. All rights reserved. Specifications are subject to change without notice. No representation or warranty as to the accuracy or completeness of the information included herein is given and any liability for any action in reliance thereon is disclaimed.

Color Kinetics
www.colorkinetics.com/ls/rgb/PureStyle/