

Day-Brite



by Signify

Linear

FluxStream EZ LED wraparound

4', 4000 lumens



Day-Brite / CFI FluxStream EZ LED wraparound is a high performing luminaire delivering smooth diffused light ideal for light industrial, commercial and residential applications with unparalleled energy efficiency.

Project: _____

Location: _____

Cat.No: _____

Type: _____

Lumens: _____ Qty: _____

Notes: _____

Ordering guide

Example: FSWEZ440L840-UNV

Series	Length (nominal)	Lumens ¹ (nominal)	Color temp. (K)	Voltage	Options
FSWEZ	4	40L	–	UNV –	
FSWEZ FluxStream wraparound EZ	4 4' length	40L 4000 lumens	830 80 CRI, 3000K 835 80 CRI, 3500K 840 80 CRI, 4000K	UNV Universal voltage 120-277	EMLED Factory wired Bodine BSL310LP integral emergency pack. Nominal 1100 lm LSXR10 120-347V motion sensor, factory installed on end cap BAC ² Meets the requirements of the Buy American Act of 1933 (BAA)

Footnotes

- Nominal delivered lumens at 25°C ambient.
- Failure to properly select the "BAC" suffix could result in you receiving product that is not BAA compliant product with no recourse for an RMA or refund. This BAC designation hereunder does not address (i) the applicability of, or availability of a waiver under, the Trade Agreements Act, or (ii) the "Buy America" domestic content requirements imposed on states, localities, and other non-federal entities as a condition of receiving funds administered by the Department of Transportation or other federal agencies.
- Consult Signify to confirm whether specific accessories are BAA-compliant.

Accessories³ (order separately)

- FSWD4L - FluxStream Wraparound 4' diffuse replacement lens
- LSXR10 - Low bay PIR motion sensor, 120-277V
- FSTH - Sliding hanger bracket (set of 2)
- FSWJ - Continuous row joiner (one per joint required)
- (See last page for details and more options)

General notes

Many luminaire components, such as reflectors, refractors, lenses, sockets, lampholders, and LEDs are made from various types of plastics which can be adversely affected by airborne contaminants. If sulfur based chemicals, petroleum based products, cleaning solutions, or other contaminants are expected in the intended area of use, consult factory for compatibility.



FSWEZ FluxStream EZ LED wraparound

4', 4000 lumens

Features

- Compact design for installation in tight spaces
- Frosted acrylic diffuser provides wide light distribution and superior glare control
- Injection molded lens retainer provides positive diffuser retention and easy tool-free access to LED boards and driver
- Convenient nominal 4' length accommodates many field applications
- Up to 50,000 hour predicted L70 LED lumen maintenance provides long service life to reduce maintenance costs
- Can be surface mounted on ceilings or walls, or suspended via chain, pendants or cables
- Wall mountable – ADA compliant
- Ideal for cold applications (-20°C to 25°C)
- FSWJ accessory required for continuous row mounting, one FSWJ at each joint

- 7/8" knock out provided at each end and on base of luminaire. Note: Center knockout is covered and not useable in 4' version with EMLED option.
- Enclosed lens minimizes penetration of dust, insects, and other debris into the lamp compartment
- 5 year manufacturer's limited warranty. Visit www.philips.com/warranties for complete warranty information

Finish

- Baked white acrylic matte high reflectance paint finish

Shielding

- Contoured frosted acrylic lens

Electrical

- LED boards and drivers are RoHS (Restriction of Hazardous Substances) compliant. Total system life rated at 50,000 hours. Predicted L70 lifetime based on LED manufacturer's supplied LM-80 data and in-situ laboratory testing. (<http://www.designlights.org/QPL>)



Materials

- Heavy gauge cold rolled steel housing and LED pan. Polycarbonate injection molded end caps

Labels

- cETLus listed
- Suitable for damp locations

Dimensions



FSWEZ FluxStream EZ LED wraparound

4', 4000 lumens

Photometry

4' FluxStream EZ wraparound LED, 4000 nominal delivered lumens

LER - 104

<p>Catalog No. FSWEZ440L840-UNV Test No. 37443 S/MH 1.3 Lamp Type LED Lumens 3325 Input Watts 32</p> <p>Comparative yearly lighting energy cost per 1000 lumens – \$2.31 based on 3000 hrs. and \$.08 pwr KWH.</p> <p>The photometric results were obtained in the Day-Brite laboratory which is NVLAP accredited by the National Institute of Standards and Technology.</p> <p>Photometric values based on test performed in compliance with LM-79.</p>	<p style="text-align: center;">Candlepower</p> <table border="1"> <thead> <tr> <th>Angle</th> <th>End</th> <th>45</th> <th>Cross</th> <th>Back-45</th> </tr> </thead> <tbody> <tr><td>0</td><td>906</td><td>906</td><td>906</td><td>906</td></tr> <tr><td>5</td><td>892</td><td>903</td><td>909</td><td>903</td></tr> <tr><td>15</td><td>862</td><td>883</td><td>895</td><td>883</td></tr> <tr><td>25</td><td>799</td><td>833</td><td>852</td><td>833</td></tr> <tr><td>35</td><td>707</td><td>756</td><td>780</td><td>756</td></tr> <tr><td>45</td><td>593</td><td>661</td><td>689</td><td>661</td></tr> <tr><td>55</td><td>429</td><td>543</td><td>577</td><td>543</td></tr> <tr><td>65</td><td>291</td><td>386</td><td>439</td><td>386</td></tr> <tr><td>75</td><td>153</td><td>261</td><td>303</td><td>261</td></tr> <tr><td>85</td><td>36</td><td>147</td><td>198</td><td>147</td></tr> </tbody> </table>	Angle	End	45	Cross	Back-45	0	906	906	906	906	5	892	903	909	903	15	862	883	895	883	25	799	833	852	833	35	707	756	780	756	45	593	661	689	661	55	429	543	577	543	65	291	386	439	386	75	153	261	303	261	85	36	147	198	147	<p>Light Distribution</p> <table border="1"> <thead> <tr> <th>Degrees</th> <th>Lumens</th> <th>% Luminaire</th> </tr> </thead> <tbody> <tr><td>0-30</td><td>718</td><td>21.5</td></tr> <tr><td>0-40</td><td>1189</td><td>35.7</td></tr> <tr><td>0-60</td><td>2165</td><td>64.9</td></tr> <tr><td>0-90</td><td>2956</td><td>88.7</td></tr> <tr><td>0-180</td><td>3333</td><td>100</td></tr> </tbody> </table> <p>Average Luminance</p> <table border="1"> <thead> <tr> <th>Zone</th> <th>End</th> <th>45°</th> <th>Cross</th> </tr> </thead> <tbody> <tr><td>45</td><td>16190</td><td>746.4</td><td>6347</td></tr> <tr><td>55</td><td>13966</td><td>597.0</td><td>5063</td></tr> <tr><td>65</td><td>12209</td><td>426.1</td><td>3785</td></tr> <tr><td>75</td><td>9391</td><td>298.9</td><td>2649</td></tr> <tr><td>85</td><td>4390</td><td>180.0</td><td>1808</td></tr> </tbody> </table> <p>Coefficients of Utilization</p> <p>EFFECTIVE FLOOR CAVITY REFLECTANCE 20 PER (pfc=0.20)</p> <table border="1"> <thead> <tr> <th>pfc =</th> <th colspan="2">20</th> <th colspan="2"></th> <th colspan="2"></th> <th colspan="2"></th> </tr> <tr> <th>Ceiling</th> <th colspan="2">80</th> <th colspan="2">70</th> <th colspan="2">50</th> <th colspan="2"></th> </tr> <tr> <th>Wall</th> <th>70</th> <th>50</th> <th>30</th> <th>70</th> <th>50</th> <th>30</th> <th>50</th> <th>30</th> </tr> <tr> <th>RCR</th> <th colspan="2"></th> <th colspan="2"></th> <th colspan="2"></th> <th colspan="2"></th> </tr> </thead> <tbody> <tr><td>0</td><td>115</td><td>115</td><td>115</td><td>112</td><td>112</td><td>112</td><td>105</td><td>105</td></tr> <tr><td>1</td><td>105</td><td>98</td><td>94</td><td>101</td><td>95</td><td>92</td><td>90</td><td>85</td></tr> <tr><td>2</td><td>94</td><td>85</td><td>79</td><td>91</td><td>82</td><td>76</td><td>78</td><td>71</td></tr> <tr><td>3</td><td>85</td><td>75</td><td>66</td><td>81</td><td>71</td><td>65</td><td>68</td><td>60</td></tr> <tr><td>4</td><td>78</td><td>66</td><td>56</td><td>75</td><td>64</td><td>56</td><td>59</td><td>53</td></tr> <tr><td>5</td><td>71</td><td>58</td><td>50</td><td>68</td><td>56</td><td>47</td><td>54</td><td>46</td></tr> <tr><td>6</td><td>66</td><td>53</td><td>44</td><td>64</td><td>51</td><td>42</td><td>47</td><td>40</td></tr> <tr><td>7</td><td>60</td><td>47</td><td>39</td><td>58</td><td>46</td><td>38</td><td>44</td><td>35</td></tr> <tr><td>8</td><td>56</td><td>42</td><td>34</td><td>55</td><td>41</td><td>34</td><td>40</td><td>33</td></tr> <tr><td>9</td><td>53</td><td>40</td><td>30</td><td>51</td><td>39</td><td>30</td><td>36</td><td>29</td></tr> <tr><td>10</td><td>50</td><td>36</td><td>28</td><td>47</td><td>35</td><td>28</td><td>34</td><td>27</td></tr> </tbody> </table>	Degrees	Lumens	% Luminaire	0-30	718	21.5	0-40	1189	35.7	0-60	2165	64.9	0-90	2956	88.7	0-180	3333	100	Zone	End	45°	Cross	45	16190	746.4	6347	55	13966	597.0	5063	65	12209	426.1	3785	75	9391	298.9	2649	85	4390	180.0	1808	pfc =	20								Ceiling	80		70		50				Wall	70	50	30	70	50	30	50	30	RCR									0	115	115	115	112	112	112	105	105	1	105	98	94	101	95	92	90	85	2	94	85	79	91	82	76	78	71	3	85	75	66	81	71	65	68	60	4	78	66	56	75	64	56	59	53	5	71	58	50	68	56	47	54	46	6	66	53	44	64	51	42	47	40	7	60	47	39	58	46	38	44	35	8	56	42	34	55	41	34	40	33	9	53	40	30	51	39	30	36	29	10	50	36	28	47	35	28	34	27
Angle	End	45	Cross	Back-45																																																																																																																																																																																																																																						
0	906	906	906	906																																																																																																																																																																																																																																						
5	892	903	909	903																																																																																																																																																																																																																																						
15	862	883	895	883																																																																																																																																																																																																																																						
25	799	833	852	833																																																																																																																																																																																																																																						
35	707	756	780	756																																																																																																																																																																																																																																						
45	593	661	689	661																																																																																																																																																																																																																																						
55	429	543	577	543																																																																																																																																																																																																																																						
65	291	386	439	386																																																																																																																																																																																																																																						
75	153	261	303	261																																																																																																																																																																																																																																						
85	36	147	198	147																																																																																																																																																																																																																																						
Degrees	Lumens	% Luminaire																																																																																																																																																																																																																																								
0-30	718	21.5																																																																																																																																																																																																																																								
0-40	1189	35.7																																																																																																																																																																																																																																								
0-60	2165	64.9																																																																																																																																																																																																																																								
0-90	2956	88.7																																																																																																																																																																																																																																								
0-180	3333	100																																																																																																																																																																																																																																								
Zone	End	45°	Cross																																																																																																																																																																																																																																							
45	16190	746.4	6347																																																																																																																																																																																																																																							
55	13966	597.0	5063																																																																																																																																																																																																																																							
65	12209	426.1	3785																																																																																																																																																																																																																																							
75	9391	298.9	2649																																																																																																																																																																																																																																							
85	4390	180.0	1808																																																																																																																																																																																																																																							
pfc =	20																																																																																																																																																																																																																																									
Ceiling	80		70		50																																																																																																																																																																																																																																					
Wall	70	50	30	70	50	30	50	30																																																																																																																																																																																																																																		
RCR																																																																																																																																																																																																																																										
0	115	115	115	112	112	112	105	105																																																																																																																																																																																																																																		
1	105	98	94	101	95	92	90	85																																																																																																																																																																																																																																		
2	94	85	79	91	82	76	78	71																																																																																																																																																																																																																																		
3	85	75	66	81	71	65	68	60																																																																																																																																																																																																																																		
4	78	66	56	75	64	56	59	53																																																																																																																																																																																																																																		
5	71	58	50	68	56	47	54	46																																																																																																																																																																																																																																		
6	66	53	44	64	51	42	47	40																																																																																																																																																																																																																																		
7	60	47	39	58	46	38	44	35																																																																																																																																																																																																																																		
8	56	42	34	55	41	34	40	33																																																																																																																																																																																																																																		
9	53	40	30	51	39	30	36	29																																																																																																																																																																																																																																		
10	50	36	28	47	35	28	34	27																																																																																																																																																																																																																																		

Accessories³



Accessory Catalog Code	Description	
FSTH	Sliding hanger bracket (pair)	
SV5F12	12" Stem and canopy kit	White stem and canopy kit, 1/4" trade size (1/2" O.D.) locknuts included. Works with 9/16" k.O. on base of housing.
SV5F18	18" Stem and canopy kit	
SV5F24	24" Stem and canopy kit	
SV5F36	36" Stem and canopy kit	
SV5F48	48" Stem and canopy kit	
FKR-126	Chain hanger set (pair)	Includes two 5' heavy duty link chains with "V" hooks. Attaches to base of housing.
DACHxx	Adjustable cable hanger kit (single)	Works with 1/4" hole on base of housing or FSTH hanger bracket. xx=cable length in inches, enter 48" to 180" lengths in 12" increments
DACHxx-1-SC	Adjustable cable hanger kit with white straight 18/3 cord (single)	
DACHxx-1-CC	Adjustable cable hanger kit with white coiled 18/3 cord (single)	
DACHxx-2-SC	Adjustable cable hanger kit with white straight 18/4 cord (single)	
DACHxx-2-CC	Adjustable cable hanger kit with white coiled 18/4 cord (single)	
DACHxx-1D-SC	Adjustable cable hanger kit with white straight 18/5 cord with dimming leads (single)	
FSWJ	External continuous row joiner (one per joint).	FSWJ accessory required for continuous row mounting
LSXR10	Low bay pir motion sensor (120-277v)	
LSXR10ADC	Low bay pir motion sensor with photocell and hi/lo trim dimming (120-277v)	
FSWD4L	4' Diffuse replacement lens	

3 Consult Signify to confirm whether specific accessories are BAA-compliant.



© 2021 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation
 200 Franklin Square Drive,
 Somerset, NJ 08873
 Telephone 855-486-2216

Signify Canada Ltd.
 281 Hillmount Road,
 Markham, ON, Canada L6C 2S3
 Telephone 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.