



Project: _____
 Location: _____
 Cat.No: _____
 Type: _____
 Lamps: _____ Qty: _____
 Notes: _____

The Hadco Baltimore LED post top consists of a traditional stately form that has created an industry standard. It offers the style of traditional lanterns with today's cutting edge LEDgene technology. For historic areas and new street-scapes Baltimore is available in sizes that are in proportion to most applications including residential streets, city streets, campuses and parking lots.


Ordering guide

Example: VX651-16-G3-A-C-2S-N-N-730-A-5-N-SP1

Series	LED Count	Gen	Finish	Panel	Distribution	Photo Control Receptacle	Future-Proof Control Receptacle	CRI/CCT	Voltage	Drive Current	Driver Option	Surge Protection	
VX651	16 16 LEDs	G3 Gen 3	A Black B White G Verde H Bronze J Green	C Clear F Frosted V Vertical Ribbed	2S Type 2 Short shield 2SH Type 2 Short House-side shield 3S Type 3 Short shield 3SH Type 3 Short House-side shield 3W Type 3 Wide House-side shield 3WH Type 3 Wide House-side shield 5 Type 5	N None E 120 VAC button eye H 208/240/277 VAC button eye R 3-Pin Twist Lock Receptacle	N None R7 7-pin receptacle in cage	730 70CRI/3000K 740 70 CRI/4000K 827 80 CRI/2700K	A 120-277 B 347-480	16 LEDs 5 530mA 7 700mA 9 900mA 1 1050mA 32 LEDs 5 530mA 7 700mA 8 800mA 1 1050mA 48 LEDs 5 530mA 7 700mA	Dynadimmer DA ² 4 Hrs, 25% reduction DB ² 4 Hrs, 50% reduction DC ² 4 Hrs, 75% reduction DD ² 6 Hrs, 25% reduction DE ² 6 Hrs, 50% reduction DF ² 6 Hrs, 75% reduction DG ² 8 Hrs, 25% reduction DH ² 8 Hrs, 50% reduction DJ ² 8 Hrs, 75% reduction	N None DL ² DALI S FAWS Field adj watt selector SRD ² Sensor ready driver (standard configuration) SRD1 ² Sensor ready driver (alternate configuration)	SP1 10kV/10kA Surge Protector SP2 20kV/20kA Surge Protector

1. Not available with Type 4 optics.
2. Only available in (A) 120-277V

Dimensions



VX651
 Height: 39" (99cm)
 Width: 16" (41cm)
 Max. EPA: 1.65 sq. ft.
 Max. Weight 28 lbs.



VX651 Baltimore

Post top

LED Wattage and Lumen Values for 3000K fixtures

Ordering Code: (3000K)	LED QTY	System Current (mA)	Color Temp	Average System Watts (W)	Type 2S			Type 3S			Type 3W			Type 5		
					Lumen Output	BUG Rating	Efficacy (Lm/W)	Lumen Output	BUG Rating	Efficacy (Lm/W)	Lumen Output	BUG Rating	Efficacy (Lm/W)	Lumen Output	BUG Rating	Efficacy (Lm/W)
Clear Panels																
VX651-16-G3-C-5-x-730	16	530	3000	29	2857	B1-U2-G1	99	3039	B1-U2-G1	105	3029	B1-U2-G1	105	3194	B1-U2-G1	111
VX651-16-G3-C-7-x-730	16	700	3000	38	3613	B1-U2-G1	95	3844	B1-U3-G1	101	3831	B1-U3-G1	101	4040	B1-U3-G1	106
VX651-16-G3-C-9-x-730	16	900	3000	49	4434	B1-U3-G1	91	4718	B1-U3-G1	96	4702	B1-U3-G2	96	4957	B1-U3-G1	101
VX651-16-G3-C-1-x-730	16	1050	3000	57	4998	B1-U2-G1	88	5316	B1-U3-G1	93	5300	B1-U3-G1	93	5587	B1-U3-G1	98
VX651-32-G3-C-5-x-730	32	530	3000	53	5562	B1-U3-G1	104	5822	B1-U3-G1	109	5875	B2-U3-G2	110	6123	B1-U3-G2	115
VX651-32-G3-C-7-x-730	32	700	3000	70	7023	B2-U3-G2	100	7351	B2-U3-G2	105	7417	B2-U3-G2	106	7730	B1-U3-G2	110
VX651-32-G3-C-8-x-730	32	800	3000	80	7816	B1-U3-G1	97	8183	B1-U3-G1	102	8256	B1-U3-G2	103	8604	B1-U3-G2	107
VX651-32-G3-C-1-x-730	32	1050	3000	108	9817	B2-U3-G2	91	10275	B2-U3-G2	95	10368	B2-U3-G2	96	10805	B1-U3-G2	100
VX651-48-G3-C-5-x-730	48	530	3000	80.8	8480	B2-U3-G2	105	8877	B1-U3-G2	110	8957	B2-U3-G2	111	9335	B1-U3-G2	116
VX651-48-G3-C-7-x-730	48	700	3000	105	10646	B2-U3-G2	102	11144	B2-U3-G2	106	11244	B2-U3-G2	107	11719	B2-U3-G2	112
Frosted Panels																
VX651-16-G3-F-5-x-730	16	530	3000	29	2621	B1-U2-G1	91	2788	B1-U2-G1	96	2779	B1-U2-G1	96	2930	B1-U2-G1	101
VX651-16-G3-F-7-x-730	16	700	3000	38	3315	B1-U2-G1	87	3527	B1-U3-G1	93	3515	B1-U3-G1	92	3706	B1-U3-G1	97
VX651-16-G3-F-9-x-730	16	900	3000	49	4068	B1-U3-G1	83	4328	B1-U3-G1	89	4314	B1-U3-G2	88	4548	B1-U3-G1	93
VX651-16-G3-F-1-x-730	16	1050	3000	57	4585	B1-U2-G1	81	4877	B1-U3-G1	86	4862	B1-U3-G1	85	5126	B1-U3-G1	90
VX651-32-G3-F-5-x-730	32	530	3000	53	5103	B1-U3-G1	96	5341	B1-U3-G1	100	5390	B2-U3-G2	101	5617	B1-U3-G2	105
VX651-32-G3-F-7-x-730	32	700	3000	70	6443	B2-U3-G2	92	6744	B2-U3-G2	96	6805	B2-U3-G2	97	7092	B1-U3-G2	101
VX651-32-G3-F-8-x-730	32	800	3000	80	7171	B1-U3-G1	89	7507	B1-U3-G1	93	7574	B1-U3-G2	94	7894	B1-U3-G2	98
VX651-32-G3-F-1-x-730	32	1050	3000	108	9006	B2-U3-G2	83	9427	B2-U3-G2	87	9512	B2-U3-G2	88	9913	B1-U3-G2	91
VX651-48-G3-F-5-x-730	48	530	3000	80.8	7780	B2-U3-G2	96	8144	B1-U3-G2	101	8217	B2-U3-G2	102	8564	B1-U3-G2	106
VX651-48-G3-F-7-x-730	48	700	3000	105	9767	B2-U3-G2	93	10224	B2-U3-G2	98	10316	B2-U3-G2	98	10751	B2-U3-G2	103
Vertical Ribbed Panels																
VX651-16-G3-V-5-x-730	16	530	3000	29	2750	B1-U2-G1	95	2940	B1-U2-G1	102	2920	B1-U3-G1	101	3096	B2-U3-G1	107
VX651-16-G3-V-7-x-730	16	700	3000	38	3479	B1-U2-G1	91	3719	B1-U2-G1	98	3694	B1-U3-G1	97	3916	B2-U3-G1	103
VX651-16-G3-V-9-x-730	16	900	3000	49	4269	B1-U3-G1	87	4563	B1-U3-G1	93	4532	B1-U3-G2	93	4806	B3-U3-G1	98
VX651-16-G3-V-1-x-730	16	1050	3000	57	4811	B1-U3-G1	85	5143	B1-U3-G1	90	5108	B1-U3-G1	90	5416	B3-U3-G1	95
VX651-32-G3-V-5-x-730	32	530	3000	53	5379	B1-U3-G1	101	5601	B1-U3-G1	105	5610	B1-U3-G1	105	5883	B3-U3-G2	110
VX651-32-G3-V-7-x-730	32	700	3000	70	6792	B2-U3-G2	97	7072	B1-U3-G2	101	7083	B1-U3-G2	101	7428	B3-U3-G2	106
VX651-32-G3-V-8-x-730	32	800	3000	80	7560	B2-U3-G2	94	7871	B1-U3-G2	98	7884	B2-U3-G2	98	8268	B3-U3-G2	103
VX651-32-G3-V-1-x-730	32	1050	3000	108	9494	B2-U3-G2	88	9885	B2-U3-G2	91	9901	B2-U3-G2	91	10383	B4-U3-G2	96
VX651-48-G3-V-5-x-730	48	530	3000	80.8	8202	B2-U3-G2	102	8540	B2-U3-G2	106	8553	B2-U3-G2	106	8970	B4-U3-G2	111
VX651-48-G3-V-7-x-730	48	700	3000	105	10297	B2-U3-G2	98	10721	B2-U3-G2	102	10738	B2-U3-G2	102	11261	B4-U3-G2	107

Actual performance may vary due to installation variables including optics, mounting/ceiling height, dirt depreciation, light loss factor, etc.; highly recommended to confirm performance with a layout - contact Applications at outdoorlighting.applications@signify.com.
Note: Some data may be scaled based on tests of similar. But not identical luminaires.

VX651 Baltimore

Post top

LED Wattage and Lumen Values for 4000K fixtures

Ordering Code: (3000K)	Total LEDs	System current (mA)	Color Temp	Average System Watts ¹	Type 2S			Type 3S			Type 3W			Type 5		
					Lumen Output ²	BUG Rating	Efficacy (LPW)	Lumen Output ²	BUG Rating	Efficacy (LPW)	Lumen Output ²	BUG Rating	Efficacy (LPW)	Lumen Output ²	BUG Rating	Efficacy (LPW)
Clear Panels																
VX651-16-G3-C-5-x-740	16	530	4000	29	3141	B1-U2-G1	107	3341	B1-U2-G1	114	3330	B1-U2-G1	114	3511	B1-U2-G1	120
VX651-16-G3-C-7-x-740	16	700	4000	39	3973	B1-U2-G1	103	4226	B1-U3-G1	110	4213	B1-U3-G1	109	4442	B1-U3-G1	115
VX651-16-G3-C-9-x-740	16	900	4000	49	4876	B1-U3-G1	99	5186	B1-U3-G1	105	5170	B1-U3-G2	105	5450	B1-U3-G1	110
VX651-16-G3-C-1-x-740	16	1050	4000	58	5495	B1-U2-G1	96	5846	B1-U3-G1	102	5826	B1-U3-G1	101	6143	B1-U3-G1	107
VX651-32-G3-C-5-x-740	32	530	4000	54	6115	B1-U3-G1	113	6402	B1-U3-G1	119	6459	B2-U3-G2	120	6731	B1-U3-G2	125
VX651-32-G3-C-7-x-740	32	700	4000	71	7722	B2-U3-G2	109	8082	B2-U3-G2	114	8155	B2-U3-G2	115	8499	B1-U3-G2	120
VX651-32-G3-C-8-x-740	32	800	4000	81	8595	B1-U3-G1	106	8996	B1-U3-G1	111	9078	B1-U3-G2	112	9460	B1-U3-G2	116
VX651-32-G3-C-1-x-740	32	1050	4000	110	10793	B2-U3-G2	98	11298	B2-U3-G2	103	11399	B2-U3-G2	104	11880	B1-U3-G2	108
VX651-48-G3-C-5-x-740	48	530	4000	82	9324	B2-U3-G2	114	9760	B1-U3-G2	119	9848	B2-U3-G2	121	10262	B1-U3-G2	126
VX651-48-G3-C-7-x-740	48	700	4000	106	11706	B2-U3-G2	110	12253	B2-U3-G2	116	12363	B2-U3-G2	117	12884	B2-U3-G2	122
Frosted Panels																
VX651-16-G3-F-5-x-740	16	530	4000	29	2882	B1-U2-G1	99	3065	B1-U2-G1	105	3055	B1-U2-G1	105	3221	B1-U2-G1	110
VX651-16-G3-F-7-x-740	16	700	4000	39	3645	B1-U2-G1	95	3877	B1-U3-G1	101	3865	B1-U3-G1	100	4075	B1-U3-G1	106
VX651-16-G3-F-9-x-740	16	900	4000	49	4473	B1-U3-G1	90	4758	B1-U3-G1	96	4743	B1-U3-G2	96	5000	B1-U3-G1	101
VX651-16-G3-F-1-x-740	16	1050	4000	58	5041	B1-U2-G1	88	5363	B1-U3-G1	93	5345	B1-U3-G1	93	5636	B1-U3-G1	98
VX651-32-G3-F-5-x-740	32	530	4000	54	5610	B1-U3-G1	104	5873	B1-U3-G1	109	5926	B2-U3-G2	110	6175	B1-U3-G2	114
VX651-32-G3-F-7-x-740	32	700	4000	71	7084	B2-U3-G2	100	7415	B2-U3-G2	104	7482	B2-U3-G2	105	7797	B1-U3-G2	110
VX651-32-G3-F-8-x-740	32	800	4000	81	7885	B1-U3-G1	97	8253	B1-U3-G1	102	8328	B1-U3-G2	102	8679	B1-U3-G2	107
VX651-32-G3-F-1-x-740	32	1050	4000	110	9902	B2-U3-G2	90	10365	B2-U3-G2	95	10458	B2-U3-G2	95	10899	B1-U3-G2	99
VX651-48-G3-F-5-x-740	48	530	4000	82	8554	B2-U3-G2	105	8954	B1-U3-G2	110	9035	B2-U3-G2	111	9415	B1-U3-G2	115
VX651-48-G3-F-7-x-740	48	700	4000	106	10739	B2-U3-G2	101	11241	B2-U3-G2	106	11342	B2-U3-G2	107	11820	B2-U3-G2	112
Vertical Ribbed Panels																
VX651-16-G3-V-5-x-740	16	530	4000	29	3023	B1-U2-G1	103	3232	B1-U2-G1	111	3210	B1-U3-G1	110	3404	B2-U3-G1	116
VX651-16-G3-V-7-x-740	16	700	4000	39	3825	B1-U2-G1	99	4089	B1-U2-G1	106	4061	B1-U3-G1	105	4306	B2-U3-G1	112
VX651-16-G3-V-9-x-740	16	900	4000	49	4693	B1-U3-G1	95	5017	B1-U3-G1	101	4983	B1-U3-G1	101	5284	B3-U3-G1	107
VX651-16-G3-V-1-x-740	16	1050	4000	58	5289	B1-U3-G1	92	5655	B1-U3-G1	98	5616	B1-U3-G1	98	5955	B3-U3-G1	104
VX651-32-G3-V-5-x-740	32	530	4000	54	5914	B1-U3-G1	110	6158	B1-U3-G1	114	6168	B1-U3-G1	114	6468	B3-U3-G2	120
VX651-32-G3-V-7-x-740	32	700	4000	71	7467	B2-U3-G2	105	7775	B1-U3-G2	110	7788	B1-U3-G2	110	8167	B3-U3-G2	115
VX651-32-G3-V-8-x-740	32	800	4000	81	8312	B2-U3-G2	102	8654	B2-U3-G2	106	8668	B2-U3-G2	107	9090	B3-U3-G2	112
VX651-32-G3-V-1-x-740	32	1050	4000	110	10438	B2-U3-G2	95	10868	B2-U3-G2	99	10886	B2-U3-G2	99	11416	B4-U3-G2	104
VX651-48-G3-V-5-x-740	48	530	4000	82	9017	B2-U3-G2	110	9389	B2-U3-G2	115	9404	B2-U3-G2	115	9862	B4-U3-G2	121
VX651-48-G3-V-7-x-740	48	700	4000	106	11321	B2-U3-G2	107	11787	B2-U3-G2	111	11806	B2-U3-G2	111	12381	B4-U3-G2	117

Actual performance may vary due to installation variables including optics, mounting/ceiling height, dirt depreciation, light loss factor, etc.; highly recommended to confirm performance with a layout - contact Applications at outdoorlighting.applications@signify.com.
Note: Some data may be scaled based on tests of similar. But not identical luminaires.

Specifications

Housing

Roof: Tool-less latch made of stainless steel allows for quick access inside of the hinged roof to locate the driver, surge protector and optional FAWs (field adjustable wattage solution). Roof and Cage made of 360 low-copper die-cast aluminum alloy.

Panels: Three panel options. Clear panels are made of an U.V. Stabilized sheet material and include a frosted decorative glass chimney. Vertical Rib panels are U.V. stabilized, injection molded with internal vertical ribs. Frosted Panels are U.V. Stabilized sheet material. All panels have tool-less removal for ease of cleaning.

Fitter: Slip Fitter Dimensions: 3" I.D. x 3" deep. Tool-less hinge door to access photocontrol components.

LED Module

Composed of high-performance white LEDs. Color temperature as per ANSI/NEMA bin 2700 Kelvin nominal (2725 ±145K) CRI 80 min, 3000 Kelvin nominal (3045K +/- 175K) or 4000 Kelvin nominal (3985K +/- 275K), CRI 70 Min. 75 Typical. Other CCT/CRI also available, consult factory.

Light Engine

Composed of 4 main components: LED Module / Optical System / Heat Sink / Driver. Electrical components are RoHSCompliant, IP66 sealed light engine LEDs tested by ISO 17025-2005 accredited lab in accordance with IESNA LM-80 guidelines, extrapolations in accordance with IESNA TM-21. Metal core board ensures greater heat transfer and longer lifespan.

Optical System

Composed of high performance UV stabilized optical grade polymer refractor lenses to achieve desired distribution optimized to get maximum spacing, target lumens and a superior lighting uniformity. System is rated IP66. Performance shall be tested per LM-63, LM-79 and TM-15 (IESNA) certifying its photometric performance. Type 2S, 3S, 3W and Type 5 Street side indicated. House side shield optional (can be field installed) 2SH: Type 2 with House Side Shield, 3SH: Type 3 short with house side shield, 3WH: Type 3 Wide with House side shield.

Heat Sink

Made of die cast aluminum optimizing the LEDs efficiency and life. Product does not use any cooling device with moving parts (only passive cooling device). Entire luminaire is rated for operation in ambient temperature of -40°C / -40°F up to +40°C / +104°F.

VX651 Baltimore

Post top

Specifications (continued)

Driver

Driver comes standard with 0-10V dimming capability. High power factor of 95%. Electronic driver, operating range 50/60 Hz. Auto adjusting universal voltage input from 120 to 277 VAC rated for both application line to line or line to neutral, Class I, THD of 20% max. Maximum ambient operating temperature from 40°F (4°C) to 130°F (55°C). Certified in compliance to UL1310 cULus requirement (dry and damp location). Assembled on a unitized removable tray with Tyco quick disconnect plug resisting to 221°F (105°C). The current supplying the LEDs will be reduced by the driver if the driver experiences internal overheating as a protection to the LEDs and the electrical components. Output is protected from short circuits, voltage overload and current overload. Automatic recovery after correction. Standard built in driver surge protection of 2.5kV (min).

Driver and Luminaire Options

FAWS: Field Adjustable Wattage Selector, pre-set to the highest position, can be easily switched in the field to the required position. This reduces total luminaire wattage consumption and reduces the light level – see the FAWS multiplier chart for more details.

Note: It is not recommended to use FAWS with other dimming or controls; if you do, set the switch to position 10 (maximum output) to enable the other dimming or controls. Switching FAWS to any position other than 10 will disable the other dimming or controls.

SRD: Sensor Ready Driver including SR communication (used for dimming and other functionalities), 24V auxiliary supply and a logical signal input (LSI) connected to the top NEMA twist lock receptacle.

SRD1: Sensor Ready Driver including SR communication (used

for dimming and other functionalities) but with 24V auxiliary supply and a logical signal input (LSI) not connected to the top NEMA twist lock.

Dimming Options:

DA: 4 Hrs 25% reduction
DB: 4 Hrs 50% reduction
DC: 4 Hrs 75% reduction
DD: 6 Hrs 25% reduction

DE: 6 Hrs 50% reduction

DF: 6 Hrs 75% reduction

DG: 8 Hrs 25% reduction

DH: 8 Hrs 50% reduction

DJ: 8 Hrs 75% reduction

DL: Pre-set driver compatible with the DALI control system. Logarithmic standard

Surge Protection

Surge protector tested in accordance with ANSI/IEEE C62.45 per ANSI/IEEE C62.41.2 Scenario I Category C High Exposure 10kV/10kA waveforms for Line Ground, Line Neutral and Neutral Ground, and in accordance with U.S. DOE (Department of Energy) MSSLC (Municipal Solid State Street Lighting Consortium) model specification for LED roadway luminaires electrical immunity requirements for High Test Level 10kV / 10kA. Option for SP2 20kV/20kA.

Luminaire Useful Life

Refer to IES files for energy consumption and delivered lumens for each option. Based on ISTMT in situ thermal testing in accordance with UL1598 and UL8750, using LM-80 data from LED manufacturers and engineering prediction methods, the cv luminaire useful life is expected to reach 100,000+ hours with >L70 lumen maintenance @ 25°C (48 LED and 64LED at 530mA is 68,000). Luminaire useful life accounts for LED lumen maintenance and additional factors, including LED life, driver life, PCB substrate, solder joints on/off cycles and burning hours for nominal applications.

Hardware

All non-ferrous fasteners prevent corrosion and ensure longer life.

Wiring

18 AWG wire, 6" (152mm) minimum exceeding from luminaire.

Options



2H, SP2
3SH, 20kV/20kA
3WH: integral surge
House side protector
shield option (optional)

Finish

Color in accordance with the AAMA 2603 standard. Application of polyester powder coat paint (4 mils/100 microns) with ± 1 mils / 24 microns of tolerance. The Thermosetting resins provides a discoloration resistant finish in accordance with the ASTM D2244 standard, as well as luster retention in keeping with the ASTM D523 standard and humidity proof in accordance with the ASTM D2247 standard. The surface treatment achieves a minimum of 2000 hours for salt spray resistant finish in accordance with testing performed and per ASTM B117 standard.

LED products manufacturing standard

The electronic components sensitive to electrostatic discharge (ESD) such as light emitting diodes (LEDs) are assembled in compliance with IEC61340 5.1 and ANSI/ESD S20.20 standards so as to eliminate ESD events that could decrease the useful life of the product.

Quality Control

The manufacturer must provide a written confirmation of its ISO 9001:2008 and ISO 14001:2004 International Quality Standards Certification. Meets the ANSI C136.31 2010, American national Standard for Roadway Luminaire Vibration specifications for Normal Applications.

Certifications and Compliance

cETL listed to Canadian safety standards for wet locations. Manufactured to ISO 9001:2008 Standards. UL8750 and UL1598 compliant. ETL listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations. LM80 & LM79 tested. Listed on the DesignLightsTM Consortium (DLC) Qualified Products List (QPL).

IP Rating

The LED optics chamber is IP66 rated.

Warranty

5 year extended warranty.

LED Performance

Predicted lumen depreciation data ¹				
Ambient Temperature (°C)	Driver mA	Calculated L ₇₀ hours ^{1,2}	L ₇₀ per TM-21 ^{2,3}	Lumen Maintenance % @ 60,000 hours
25°C	up to 700 mA	>100,000	>60,000	90%

1. Predicted performance derived from LED manufacturer's data and engineering design estimates, based on IESNA LM-80 methodology. Actual experience may vary due to field application conditions.
2. L₇₀ is the predicted time when LED performance depreciates to 70% of initial lumen output.
3. Calculated per IESNA TM21-11. Published L₇₀ hours limited to 6 times actual LED test hours.



© 2022 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation
400 Crossing Blvd, Suite 600
Bridgewater, NJ 08807
Telephone 855-486-2216

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.