



Flexibility at your fingertips

Benefit from budget-friendly, commercial grade quality downlighting suitable for renovation, retrofit, and new construction projects. Meeting job timelines and navigating changing decisions just got a lot easier with modular design that puts flexibility at your fingertips.

Frame-optional design architecture and modular optics that can be field or factory-installed, you can be confident that ModuLyte is equipped to support a variety of project conditions. If decisions change during design, or when unexpected conditions on-site call for change, you can rest assured that ModuLyte puts flexibility at your fingertips.

Meet deadlines and project schedules without the stress by quickly connecting the light engine to its driver via a screw-on Communications Multipurpose Plenum (CPM) cable. This 2-piece assembly gives project crews on-site options when coordinating installation and work in ceilings and makes post-install work a breeze.

Selectable CCT and lumen output options create peace-of-mind during design and installation. Convenient switches make it easy for contractors to toggle between options to ensure lighting creates the right environment on any project.

M4R, M6R, M8R ModuLyte

4in 6in 8in downlight

Features

Efficacy: up to 117lm/W
 Lumens: 500-5000lm selectable
 Watts: 4-49W
 CRI: 90 Accurender
 CCT: 2700K, 3000K, 3500K, 4000K, & 5000K selectable
 Volts: 120-277V, 347V
 Lifetime: L80 @ 72,000 hours
 Labels: cULus listed and ENERGY STAR® certified.
 Warranty: 5 year



Visit signify.com/warranties for more information on Signify's standard 5-year limited warranty.


Engine

example: M6RDL259CSWCCZ10U

Series	Styles	Lumens	CRI/CCT	Beam	Reflector	Flange	Dimming	Voltage	Options
M4R 4" Round ¹	DL Downlight	10 500lm, 750lm,	9CS 90 CRI with 2700K, 3000K, 3500K, 4000K, 5000K CCTs	M Medium W Wide	CL Specular clear CD Comfort clear diffuse	B White (matte)	Z10 0-10V 1%	U Universal 120/277V 3 347V ⁴	- None LC Chicago plenum ⁴ AT Air-tight (factory-installed gasket on trim flange) ⁵ EM6R Emergency battery pack w/ remote test switch ⁶ EM6I Emergency battery pack w/ integral test switch to trim ⁷
M6R 6" Round ¹	LW Lensed Wall Wash ²	25 1500lm, 2000lm, 2500lm				B Black (matte)			
M8R 8" Round ¹		40 3000lm, 3500lm, 4000lm ³				P Polished (matches aperture)			
		50 4500lm, 5000lm ³				WH White BK Black (matte)			

Accessories

- LCEM6** Bodine BSL06 6W EM pack and self-test/self-diagnostic, remote with with plate included
- M4RLW** 4" round lensed wall wash optic
- M6RLW** 6" round lensed wall wash optic
- M8RLW** 8" round lensed wall wash optic
- 4RSNR** 4" new construction frame with 24" telescoping bar hangers
- 6RSNR** 6" new construction frame with 24" telescoping bar hangers
- 8RNR** 8" new construction frame with 24" telescoping bar hangers
- M4MED** 4" round medium beam diffuser lens
- M6MED** 6" round medium beam diffuser lens
- M8MED** 8" round medium beam diffuser lens
- M4GRW** 4" goof ring - white (matte)
- M6GRW** 6" goof ring - white (matte)
- M8GRW** 8" goof ring - white (matte)
- SBA** Interact Ready System Bridge Accessory (refer to Philips System Bridge Accessory spec sheet for options and details)



1. The M4R is IC rated up to 1500lm and the M6R/M8R are IC rated up to 2000lm.
2. Integral lensed wall wash optic factory installed.
May also be field installed with M_RLW accessory with DL style light engine/trim.
3. The 4000, 4500, and 5000lm flux are marked spacings (5000lm available only with M6 & M8).
4. Luminaires using 347V (3) and Chicago plenum (LC) are not available with EM6R & EM6I options.
5. Stock Ready light engines include a factory-installed gasket and are AirSeal in compliance with ASTM E283. All other configurations require air-tite (AT) option for factory-installed gasket.
6. Factory installed Bodine BSL06 6W battery pack for remote mount test switch (ceiling mounting plate included). May also be field installed with LCEM6 accessory.
7. Factory installed Bodine BSL06 6W battery pack for mounting test switch integrally to trim.

Ceiling Cutout (new construction & retrofit)	4"	6"	8"
Standard	4 ⁷ / ₁₆ "	6 ³ / ₁₆ "	8 ³ / ₁₆ "
With goof ring	5 ³ / ₁₆ "	7 ¹ / ₂ "	9 ¹ / ₄ "

See spec sheet for additional drawings and technical information.



© 2024 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.



Signify North America Corp.
 400 Crossing Blvd, Suite 600
 Bridgewater, NJ 08807
 Telephone: 800-555-0050

Signify Canada Ltd.
 281 Hillmount Road,
 Markham, ON, Canada L6C 2S3
 Telephone: 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.