

Ordering guide

Example: B1 A

Product Code	Finish
<input type="text" value="B1"/>	
B1 Aluminum Bullyte	A Black H Bronze

Project: _____

Location: _____

Cat.No: _____

Type: _____

Lamps: _____ Qty: _____

Notes: _____

Specifications

Housing

Die-cast aluminum. Fully-adjustable swivel arm with vibration-proof locking teeth. 1/2" NPS male threads to screw onto accessory mounting stake or junction box, sold separately. Gasketing is silicone. Fasteners are 300 series stainless steel. Shroud is optional.

Finish

Thermoset polyester powdercoat is electrostatically applied after a five-stage conversion cleaning process and bonded by heat fusion thermosetting. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B117 specifications.

Optical Assembly

Provided with optional shrouds only.

Lamping

100W maximum PAR20/R20 medium base lamp. Incandescent lamp is not included. Lower wattage lamps are acceptable. Note: If HID or R lamp is used, accessory shroud must also be used.

Electrical Assembly

4kv rated porcelain mini-can base. Nickel-plated screw shell with center contact. Fixture is pre-wired with 18 AWG black, white, and ground wires.

Ballast

Must order in-ground (IBH) or above ground (ABH) ballast housing separately.

Warranty

Three-year limited warranty.

Certifications

ETL listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations. Manufactured to ISO 9001:2008 Standards.

Width	Length	Max. Weight
3 7/8" (98mm)	8 1/2" (216mm)	1.4 lb.

