

# Day-Brite

## CFI

by ignify

Linear industrial

APX

High bay



## Meet the needs of your demanding environment

The Day-Brite / CFI APX LED linear high bay provides durability and high performance for your customer's demanding environments. With packages ranging from 8,000 to 24,000 nominal lumens, the APX can be specified for many areas requiring a sealed luminaire, such as laboratories, food processing, parking areas, and other industrial applications.



# APX LED high bay

## Linear industrial

The rugged housing and clear or frosted lens options combine for durable and effective lighting that is also comfortable for the occupants. LED technology provides efficiency, long life, and reduces energy costs. The additional capability of dimming and optional sensors can ensure even more energy savings.



### Ordering guide

Example: APX24LL40-UNV

Family	Lumens	Lamp Source	CCT	Voltage	Optics	Options
APX		L	—	—	—	
APX	<b>08L</b> 8000 nominal delivered lumens <b>12L</b> 12000 nominal delivered lumens <b>16L</b> 16000 nominal delivered lumens <b>20L</b> 20000 nominal delivered lumens <b>24L</b> 24000 nominal delivered lumens	L LED	<b>40</b> 4000K (CRI 80) <b>50</b> 5000K (CRI 80)	<b>UNV</b> 120-277V <b>120</b> 120V <b>208</b> 208V <b>240</b> 240V <b>277</b> 277V <b>347</b> 347V <b>480</b> 480V	<b>Blank</b> General Distribution <b>N</b> Narrow <b>M</b> Medium <b>W</b> Wide <b>A</b> Aisle	<b>WP6<sup>56</sup></b> Wired 6' 16/3 cord & NEMA twist lock plug <b>WC6</b> Wired 6' 16/3 cord <b>WP6D<sup>56</sup></b> Wired 6' 16/3 cord & NEMA twist lock plug for line voltage and wired 6' 16/3 cord & plug for dimming control <b>WC6D</b> Wired 6' 16/3 cord for line voltage and wired 6' 16/3 cord for dimming control <b>MD360W</b> 360° Motion detector (ON/OFF) <b>EMLED</b> Emergency battery (25°C max) <b>LFA</b> Frosted acrylic lens <b>LCP</b> Clear polycarbonate lens <b>LFP</b> Frosted polycarbonate lens <b>TP</b> Tamperproof screws <b>C</b> Ceiling mount hangers

### Footnotes

56 Must specify voltage

### Wiring Notes

Standard cords have 3 wires. Consult factory for other cord options.

### Predicted L<sub>70</sub> Lifetime

Max. Ambient > 100,000 hours  
(based upon LED manufacturer's supplied LM-80 data and in-situ laboratory testing)

### General Notes

All options factory installed.

All accessories are field installed.

Designlights Consortium® qualified. Please check the DLC Qualified Products List to confirm ([www.designlights.org/QPL](http://www.designlights.org/QPL)).

Certain luminaire components may be adversely affected by contaminants. If sulfur, chlorine, petroleum based solutions, or other contaminants will be in the area of operation, please consult factory as damage caused by these contaminants is not covered under our limited warranty.

The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract.

