

Panel Load Schedule

Panel Type	Panel Dimensions	Contains	Panel Name
DBC120-DALI-ENC	14-9/16" W x 12-7/32" H x 3-9/16" D (370 mm W x 310 mm H x 91 mm D)	DDBC120-DALI	
Mains	Voltage	Derated Total Allowed Load	Mounting Location
		11 Amps per relay output 160 mA per driver output	

DEVICE	DDBC120-DALI				Device ID	
Channel	Room	Room #	Zone	Fixture	Circuit	Notes
1						
2						
3						
4						
5						
6						
7						
8						
9						
10						
11						
12						
13						
14						
15						
16						
17						
18						
19						
20						
21						
22						
23						
24						
25						
26						
27						
28						
29						
30						
31						
32						

Panel Load Schedule

Panel Type	Panel Dimensions	Contains	Panel Name
DBC120-DALI-ENC	14-9/16" W x 12-7/32" H x 3-9/16" D (370 mm W x 310 mm H x 91 mm D)	DDBC120-DALI	
Mains	Voltage	Derated Total Allowed Load	Mounting Location
		11 Amps per relay output 160 mA per driver output	

DEVICE	DDBC120-DALI				Device ID	
Channel	Room	Room #	Zone	Fixture	Circuit	Notes
33						
34						
35						
36						
37						
38						
39						
40						
41						
42						
43						
44						
45						
46						
47						
48						
49						
50						
51						
52						
53						
54						
55						
56						
57						
58						
59						
60						
61						
62						
63						
64						