



GENLYTE
SOLUTIONS

a signify business

Warehouse Product Guide

2024


Tackle your lighting project quickly

Tight project timelines can't hold you back; get quality lighting delivered within 5-10 shipping days. Our solutions can light the way for your next project with the Design Ready portfolio.

The selected QuickShip, high performance LED lamps and award-winning luminaires from Genlyte Solutions brands include Lightolier, Day-Brite, Chloride, and Stonco offerings.

Illuminate your space with ease

Genlyte Solutions provides the lighting solution for every project. Whether it's lighting and connecting your public spaces, giving your space an energy-saving upgrade, or working on a yet-to-be constructed project, we've got you covered. Our Design Ready portfolio makes it easy for you to find highly configurable lighting with modern designs within your timeline and your budget.





Design Build

Our stocking solutions are now ready to go with your stock and design ready needs



Stock ready
Stock and Flow
Ships in **2 days**




Design ready
Design Build
Ships in **5-10 days**

Warehouse applications

Around the clock lighting solutions

Lighting can account for a significant portion of a warehouse's energy bill, so it must be as efficient and cost-effective as possible when running 24/7. Longer-lasting and energy-efficient LED lighting can have an enormous impact on your bottom line, reducing operational costs through reduced downtime and lower energy consumption while providing a sense of security on the work floor.



Best in class optics with less fixtures

FBZ's targeted optics solution puts the lighting where you need it all while offering you a leaner design resulting in fewer luminaires and less complexity.

Better overall efficiency¹

A 13% overall improved efficacy rating contributes to a better overall cost of ownership.



On average, a typical application with FBZ versus alternate products can use

up to 38%²
fewer fixtures



1. Based on a typical warehouse aisle application (10' x 300' x 28') using closest competitor comparison luminaires. Actual savings may vary depending on application.

2. Compared to our previous generation luminaire.

Stock ready

2 day shipping

Design ready

5-10 day shipping

Storage, Production & Manufacturing

High Bay (rectangular) luminaires

Day-Brite
CFI



FCY High Bay

- Convenient specification
- Multiple lumen options
- Standard 0-10V dimming
- Simple mounting methods
- Color selectable 4000K/5000K

Stock ready

Day-Brite
CFI



FBY High Bay

- Designed for a host of applications
- 12,000-60,000 lumen options
- A variety of mounting accessories available
- Components are DesignLights Consortium qualified

Stock ready

Design ready

Day-Brite
CFI



FBZ High Bay

- Targeted optics solution
- Reduced total cost of ownership with lower capital investment and lower energy costs
- Advanced smart lighting capabilities with adaptive and future proof controls

Design ready

High Bay (round) luminaires

Day-Brite
CFI



HCY High Bay

- Multiple lumen options
- Simple mounting methods
- Color selectable 4000K/5000K
- Field mount microwave sensor and programming remote
- Lumen selectable large size 28,000/33,000

Stock ready



Industrial Linear

Day-Brite
CFI



V3W Vaporlume

- Ideally suited for use in refrigerated cold storage, industrial, parking garage, and canopy applications
- Acceptable for outdoor as well as indoor installations
- NSF Certified option for Non-Food Zone/Splash Zone installations

Stock ready

Design ready

Day-Brite
CFI



VTS Sealed Strip

- Acceptable for outdoor and indoor installations
- Can be surface mounted or suspended
- Selectable default setting is 4000K correlated CCT with max available power

Stock ready

General Purpose Linear

Day-Brite
CFI



FluxStream Strip

- 2', 3', 4' and 8' tandem lengths available to accommodate many field applications
- Frosted acrylic diffuser provides wide light distribution, superior glare control
- Diffuser and LED plate snap into place allowing tool-free access

Stock ready

Design ready

Day-Brite
CFI



FluxSpace Strip

- 4 different styles in a 4" housing
- State of the art smart lighting capabilities with adaptive and future proof controls
- Endless possibilities for a host of applications

Design ready

Stock ready 2 day shipping

Design ready 5-10 day shipping



Packing, Staging, Shipping & Docking

High Bay (rectangular) luminaires

Day-Brite
CFI



FCY High Bay

- Convenient specification
- Multiple lumen options
- Standard 0-10V dimming
- Simple mounting methods
- Lumen output selectable

Stock ready

Day-Brite
CFI



FBY High Bay

- Designed for a host of applications
- 12,000-60,000 lumen options
- A variety of mounting accessories available
- Components are DesignLights Consortium qualified

Stock ready

Design ready

Day-Brite
CFI



FBZ High Bay

- Targeted optics solution
- Reduced total cost of ownership with lower capital investment and lower energy costs
- Advanced smart lighting capabilities with adaptive and future proof controls

Design ready

High Bay (round) luminaires

Day-Brite
CFI



HCY High Bay

- Multiple lumen options
- Simple mounting methods
- Color selectable 4000K/5000K
- Field mount microwave sensor and programming remote
- Lumen selectable large size 28,000/33,000

Stock ready



Industrial Linear

Day-Brite
CFI



V3W Vaporlume

- Ideally suited for use in refrigerated cold storage, industrial, parking garage, and canopy applications
- Acceptable for outdoor as well as indoor installations
- NSF Certified option for Non-Food Zone/Splash Zone installations

Stock ready

Design ready

General Purpose Linear

Day-Brite
CFI



FluxStream Strip

- 2', 3', 4' and 8' tandem lengths available to accommodate many field applications
- Frosted acrylic diffuser provides wide light distribution, superior glare control
- Diffuser and LED plate snap into place allowing tool-free access

Stock ready

Design ready

Day-Brite
CFI



FluxSpace Strip

- 4 different styles in a 4" housing
- State of the art smart lighting capabilities with adaptive and future proof controls
- Endless possibilities for a host of applications

Design ready

Day-Brite
CFI



SDS Selectable Strip

- Frosted glare-free lens
- Simple mounting method
- CCT & Lumen selectability
- Durable construction
- Ease of installation and maintenance

Stock ready

Stock ready 2 day shipping

Design ready 5-10 day shipping

General Illumination



Recessed Troffers

Day-Brite
CFI



FluxPanel Selectable

- Low glare
- Wireless control options available
- NSF rating is offered as standard for areas with high sanitization needs
- DLC listed

Stock ready

Design ready

Day-Brite
CFI



FluxGrid Recessed

- High quality and performance for optimum energy savings
- Drivers and boards are easily accessible from below
- 3-1/8" deep low profile configuration
- Wireless control options available

Stock ready

Design ready

Downlights

LIGHTOLIER



EasyLyte

- Field adjustable springs adjust to ceiling thicknesses of 1.5" and 2" fixtures
- Emergency frame option with emergency battery pack and remote test switch
- Modular design saves time and cost

Stock ready

Design ready

LIGHTOLIER



LyteProfile

- The combined light engine and reflector allow tool-free installation
- Standard 120/277V frame simplifies planning and installation
- UniFrame infrastructure allows 50K+ product configurations

Stock ready

Design ready


LIGHTOLIER



Commercial Retrofit

- 4 sizes to accommodate applications with varying ceiling heights
- Simplified installation
- 90 CRI for crisp color clarity
- 120-347V (UN3) voltage sensing driver
- 0-10V Dimming

Stock ready



Outdoor

Outdoor Floodlighting

KEENE



SlimFlood DualSelect

- Can be mounted on the ground, wall, or pole
- Field selectable CCT of 3000K-5000K
- 7 housings and 4 sizes available
- IP65 rated, 5-year limited warranty

Stock ready

Outdoor Canopy

KEENE



Garage & Canopy

- IP65 rated luminaire
- Die-cast round housing protect LEDs and driver
- DLC Premium
- 10kV surge protection
- 120-347V

Stock ready

Outdoor Wall Pack

KEENE



LytePro Wall

- Low-profile design
- Three sizes to accommodate multiple mounting heights
- Optical distributions offer full cutoff performance and excellent uniformity for precise wall and area illumination

Stock ready

Design ready

KEENE



Adjustable Slim Wall Pack

- Die-cast aluminum, hinged
- Simplified solution – dual select
- 2 housing sizes (25W & 75W)
- CCT Selectable (3K/4K/5K) & 120-277V
- IP65 / IK07 Rated / DLC 5.1
- Button Photocontrol

Stock ready

Stock ready

2 day shipping

Design ready

5-10 day shipping

Retrofit options

TLEDs

PHILIPS



CorePro InstantFit Linear T5 & T8 LED Lamps

Simply replace traditional fluorescent lamps with budget friendly InstantFit TLED lamps to help save on energy costs.

Stock ready

PHILIPS



MasterClass InstantFit Linear T5 & T8 LED Lamps

Install lamps with proven energy savings with the shatter-proof option that only Philips can offer.

Stock ready

PHILIPS



CorePro MainsFit Linear T5 & T8 LED lamps

Bypass the ballast in fluorescent fixtures to upgrade your general lighting and conserve energy.

Stock ready

TLEDs

PHILIPS



MasterClass MainsFit Linear T5 & T8 LED lamps

Provide consistent light output for quality illumination and available in plastic for shatter prevention.

Stock ready

Glass Lamps

PHILIPS



Glass LED HID Replacement Lamps

Easy upgrade from HID lamps to LED with a seamless solution.

Stock ready

High Bay Lamps


PHILIPS



MasterClass TrueForce LED High Bay Lamps

Couple light distribution and high color rendering with energy efficiency to create a comfortable, safe and high productivity environment.

Stock ready



LED Corn Cobs

PHILIPS



CorePro LED Corn Cob

Maximize energy savings at an affordable price.

Stock ready

PHILIPS



MasterClass TrueForce LED Corn Cob

Provide the "perfect fit" with uncompromising efficacy and color quality to keep outdoor areas brightly lit.

Stock ready

PHILIPS



MasterClass LED Color-selectable Corn Cob lamps

Provide the "perfect fit" with uncompromising efficacy and color quality to keep outdoor areas brightly lit.

Stock ready

LED Retrofit Kits

PHILIPS



EvoKit Click

Easily upgrade existing fluorescent troffers to fast-track payback with energy-efficient LEDs in just 5 minutes.

Stock ready

Get started with the Design Ready catalog



Ready to create your vision?

Check out the Design Ready website and catalog for ordering information on the product families fit for bringing your Design Build project to life. Scan or click the QR code to learn more.





GENLYTE
SOLUTIONS
a  signify business

© 2024 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation
400 Crossing Blvd, Suite 600
Bridgewater, NJ 08807
Telephone 800-555-0500

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.