

**GENLYTE**  
**SOLUTIONS**

a signify business



**Commercial Building  
Product Guide**

2025



# Tackle your lighting project quickly

Tight project timelines can't hold you back; get quality lighting delivered within 5-10 shipping days. Our solutions can light the way for your next project with the Design Ready portfolio.

The selected QuickShip high performance luminaires from Genlyte Solutions brands include Lightolier, Day-Brite, Chloride, and Stonco offerings.

## Illuminate your space with ease

Genlyte Solutions provides the lighting solution for every project. Whether it's lighting and connecting your public spaces, giving your space an energy-saving upgrade, or working on a yet-to-be constructed project, we've got you covered. Our Design Ready portfolio makes it easy for you to find highly configurable lighting with modern designs within your timeline and your budget.





# Design Build

Our stocking solutions are now ready to go with your stock and design ready needs



Stock ready  
Stock and Flow  
Ships in **2 days**



Design ready  
Design Build  
Ships in **5-10 days**



# ModuLyte

Benefit from budget-friendly, commercial grade quality downlighting

Frame-optional design architecture and modular optics that can be field or factory-installed, you can be confident that ModuLyte is equipped to support a variety of project conditions.

Meet deadlines and project schedules without the stress by quickly connecting the light engine to its driver via a screw-on Communications Multipurpose Plenum (CPM) cable.

Selectable CCT and lumen output options create peace-of-mind during design and installation. Convenient switches make it easy for contractors to toggle between options to ensure lighting creates the right environment on any project.



Product Highlight



Flexibility at your fingertips

**LIGHTOLIER**



Product Highlight


Slim, sturdy, and selectable

**Day-Brite**

# Selectable Troffer (DSRT)

Robust low glare luminaire designed to provide three lumen and three CCT field selectable options per size at 80CRI. Available for use in recessed, suspended, and surface mount applications with optional daylight and occupancy sensor.

DSRT is 120-277V (UNV), with 0-10V dimming, and a 3in deep housing.





# Commercial building applications

## Around the clock lighting solutions

Lighting is more than just a necessity; it's a vital component that can significantly impact a business's success. Invest in superior lighting solutions to transform a commercial space into a vibrant, efficient, and safe environment.

At [Genlyte Solutions](#), our portfolio of lighting brands offers the perfect solutions to create an optimal commercial environment. Explore our product suggestions to elevate your space and foster a more productive and comfortable atmosphere for your team and customers.




Stock ready 2 day shipping

Design ready 5-10 day shipping



# Reception Area

**LEDALITE**



ArcForm Duo Pique Duo

## ArcForm Duo & Pique Duo

- Flawless lens aesthetic with premium metal trims with a budget friendly price point
- Best in class efficacy with AccuRender CRI 90+ technology
- Low weight for ease of handling

Design ready

**LEDALITE**



## SilkSpace Definition

- High efficiency with a fully luminous optic, minimizing harsh shadows
- Accessible from the bottom with lift-and-shift lenses
- Interact Ready
- Available in traditional and uncommon grid sizes

Design ready

**LIGHTOLIER**




Core Track Head (THC) Performance Track Head (THP)

## THC & THP Track Heads

- Molded polycarbonate track attachment fitting and push tab
- Solid brass movable contact
- Integrated heat sink: Passive cooling, integrated into optic and driver housing
- (Matte) white and black finishes

Stock ready

**LIGHTOLIER**




## LyteProfile

- Utilizes UniFrame, Lightolier's adaptable single frame solution
- Multiple finishes, styles, flanges, shapes, and sizes (4"/6") available
- CRI 90+
- Controls solutions from basic to advance connected networks

Stock ready

Design ready

**LIGHTOLIER**



## ModuLyte Downlight

- Field interchangeable downlight and lensed wall wash optics
- 59° physical cutoff provides reduced high angle glare and low UGR to optimize visual comfort
- Field selectable for 5 CCTs and up to 3 lumen levels

Stock ready

Design ready

**LIGHTOLIER**



## ModuLyte Cylinders

- Excellent combination of aesthetic and lighting appeal with field modularity
- Designed for use with standard ModuLyte recessed Downlight
- Field selectable for 5 CCTs

Stock ready

Design ready



# Corridors



LIGHTOLIER



## Modulyte Downlight

- Field interchangeable downlight and lensed wall wash optics
- 59° physical cutoff provides reduced high angle glare and low UGR to optimize visual comfort
- Field selectable for 5 CCTs and up to 3 lumen levels

Stock ready

Design ready

LIGHTOLIER



## LyteProfile

- Utilizes UniFrame, Lightolier's adaptable single frame solution
- Multiple finishes, styles, flanges, shapes, and sizes (4"/6") available
- CRI 90+
- Controls solutions from basic to advance connected networks

Stock ready

Design ready

LIGHTOLIER



## Commercial Retrofit

- 4 sizes for applications with varying ceiling heights
- Simplified installation
- 90 CRI for crisp color clarity
- 120-347V (UN3) voltage sensing driver
- 0-10V Dimming

Stock ready

Day-Brite




## NWL Selectable Wraparound

- White polycarbonate housing
- Frosted polycarbonate lens for even, low glare lighting
- Hardware for surface mounting incl.
- Field CCT selectable for 3000K, 3500K or 4000K

Stock ready

Day-Brite



## Selectable Troffer (DSRT)

- Strong and well constructed 3in deep 5VA housing
- Field selectable lumens and CCT opt.
- Polystyrene diffuser provides visual comfort, even light distribution and high efficiency illumination
- Sensor versions available

Stock ready



Stock ready

2 day shipping


Design ready

5-10 day shipping

# Conference & Meeting Rooms

**LEDALITE**

Pique Duo



ArcForm Duo

## ArcForm Duo & Pique Duo

- Flawless lens aesthetic with premium metal trims with a budget friendly price point
- Best in class efficacy with AccuRender CRI 90+ technology
- Low weight for ease of handling

Design ready

**LEDALITE**



## SilkSpace Definition

- High efficiency with a fully luminous optic, minimizing harsh shadows
- Accessible from the bottom with lift-and-shift lenses
- Interact Ready
- Available in traditional and uncommon grid sizes

Design ready

**LEDALITE**



## Shine

- High efficiency with a fully luminous optic, minimizing harsh shadows
- Multiple lumen packages and CCTs
- Accessible from below with lift-and-shift lenses
- Available in traditional and uncommon grid sizes

Design ready

**LIGHTOLIER**



## LyteProfile

- Utilizes UniFrame, Lightolier's adaptable single frame solution
- Multiple finishes, styles, flanges, shapes, and sizes (4"/6") available
- CRI 90+
- Controls solutions from basic to advance connected networks

Stock ready

Design ready

**LIGHTOLIER**



## Commercial Retrofit

- 4 sizes for applications with varying ceiling heights
- Simplified installation
- 90 CRI for crisp color clarity
- 120-347V (UN3) voltage sensing driver
- 0-10V Dimming

Stock ready

**LIGHTOLIER**



## ModuLyte Cylinders

- Excellent combination of aesthetic and lighting appeal with field modularity
- Designed for use with standard ModuLyte recessed Downlight
- Field selectable for 5 CCTs

Stock ready

Design ready

# Private Offices Spaces

LIGHTOLIER



## LyteProfile

- Utilizes UniFrame, Lightolier's adaptable single frame solution
- Multiple finishes, styles, flanges, shapes, and sizes (4"/6") available
- CRI 90+
- Controls solutions from basic to advance connected networks

Stock ready

Design ready

LIGHTOLIER



## Commercial Retrofit

- 4 sizes for applications with varying ceiling heights
- Simplified installation
- 90 CRI for crisp color clarity
- 120-347V (UN3) voltage sensing driver
- 0-10V Dimming

Stock ready

LIGHTOLIER



## ModuLyte Downlight

- Field interchangeable downlight and lensed wall wash optics
- 59° physical cutoff provides reduced high angle glare and low UGR to optimize visual comfort
- Field selectable for 5 CCTs and up to 3 lumen levels

Stock ready

Design ready




Stock ready 2 day shipping

Design ready 5-10 day shipping



# Exit and Emergency

CHLORIDE



**Value+**

- Snap together design
- Nicad battery
- Smaller compact housing
- Operating temperature range: 10°C (50°F) to 40°C (104°F)

Stock ready

CHLORIDE




**Value+ Low End Family**

- Snap together design
- Nicad battery
- Smaller compact housing
- Operating temperature range: 10°C (50°F) to 40°C (104°F)

Stock ready

CHLORIDE



**44R Line Edge Lit**


- A lower profile design is less obtrusive than traditional signs, making it more aesthetically appealing
- Ceiling, wall and end surface mounting

Stock ready



# Break Room

**LIGHTOLIER**




**Modulyte Downlight**

- Field interchangeable downlight and lensed wall wash optics
- 59° physical cutoff provides reduced high angle glare and low UGR to optimize visual comfort
- Field selectable for 5 CCTs and up to 3 lumen levels

Stock ready    Design ready

**LIGHTOLIER**



**LyteProfile**

- Utilizes UniFrame, Lightolier's adaptable single frame solution
- Multiple finishes, styles, flanges, shapes, and sizes (4"/6") available
- CRI 90+
- Controls solutions from basic to advance connected networks

Stock ready    Design ready

**LIGHTOLIER**



**Commercial Retrofit**

- 4 sizes for applications with varying ceiling heights
- Simplified installation
- 90 CRI for crisp color clarity
- 120-347V (UN3) voltage sensing driver
- 0-10V Dimming

Stock ready

**Day-Brite**



**NWL Selectable Wraparound**

- White polycarbonate housing
- Frosted polycarbonate lens for even, low glare lighting
- Hardware for surface mounting incl.
- Field CCT selectable for 3000K, 3500K or 4000K

Stock ready

**Day-Brite**



**Selectable Troffer (DSRT)**

- Strong and well constructed 3in deep 5VA housing
- Field selectable lumens and CCT opt.
- Polystyrene diffuser provides visual comfort, even light distribution and high efficiency illumination
- Sensor versions available

Stock ready



Stock ready 2 day shipping

Design ready 5-10 day shipping



# Restrooms

Day-Brite



## NWL Selectable Wraparound

- White polycarbonate housing
- Frosted polycarbonate lens for even, low glare lighting
- Hardware for surface mounting incl.
- Field CCT selectable for 3000K, 3500K or 4000K

Stock ready

Day-Brite



## FluxStream Wraparound

- Up to 100,000 hour predicted L70 LED lumen maintenance
- Suitable for damp locations
- Multiple mounting methods
- Ease of installation and maintenance

Stock ready

Design ready

Day-Brite



## VTS Sealed Strip

- Field selectable CCT & lumen options
- Durable construction
- Simple mounting method
- Convenient specification
- Ease of installation and maintenance
- Simple form

Stock ready

LIGHTOLIER



## Modulyte Downlight

- Field interchangeable downlight and lensed wall wash optics
- 59° physical cutoff provides reduced high angle glare and low UGR to optimize visual comfort
- Field selectable for 5 CCTs and up to 3 lumen levels

Stock ready

Design ready

LIGHTOLIER



## Commercial Retrofit

- 4 sizes for applications with varying ceiling heights
- Simplified installation
- 90 CRI for crisp color clarity
- 120-347V (UN3) voltage sensing driver
- 0-10V Dimming

Stock ready

LIGHTOLIER



## Commercial Retrofit

- 4 sizes for applications with varying ceiling heights
- Simplified installation
- 90 CRI for crisp color clarity
- 120-347V (UN3) voltage sensing driver
- 0-10V Dimming

Stock ready

# Storage Rooms

Day-Brite



## SDS Selectable Strip

- Frosted glare-free lens
- Simple mounting method
- CCT & Lumen selectability
- Durable construction
- Ease of installation and maintenance

Stock ready

Day-Brite



## VTS Sealed Strip

- Field selectable CCT & lumen options
- Durable construction
- Simple mounting method
- Convenient specification
- Ease of installation and maintenance
- Simple form

Stock ready

Day-Brite



## NWL Selectable Wraparound

- White polycarbonate housing
- Frosted polycarbonate lens for even, low glare lighting
- Hardware for surface mounting incl.
- Field CCT selectable for 3000K, 3500K or 4000K

Stock ready

Day-Brite



## FCY High Bay

- Convenient specification
- Multiple lumen options
- Standard 0-10V dimming
- Simple mounting methods
- Color selectable 4000K/5000K

Stock ready

LIGHTOLIER



## ModuLyte Downlight

- Field interchangeable downlight and lensed wall wash optics
- 59° physical cutoff provides reduced high angle glare and low UGR to optimize visual comfort
- Field selectable for 5 CCTs and up to 3 lumen levels

Stock ready

Design ready

LIGHTOLIER



## SlimSurface Downlight

- The thinnest available solution with an integral driver for existing J-boxes or new construction
- Glare controlling lens for comfortable light distribution
- Choice of design with square and round apertures

Stock ready

Design ready



# Parking Lots & Exterior Lighting

Stonco



## LytePro Wall

- Low-profile design
- Three sizes to accommodate multiple mounting heights
- Optical distributions offer full cutoff performance and excellent uniformity for precise wall and area illumination

Stock ready

Design ready

Stonco



## LytePro Garage & Canopy

- SpiroGuide light engine that reduces glare and increases uniformity
- Luminous white uplight option with a halo bezel that glows
- Dimming controls and UL924 emergency options
- Lightweight and "click!" no-screw surface mounting

Design ready

Stonco



## LytePro Area

- Mounting to round or square pole without need for accessories
- Large bolt spacing range for easy retrofit application
- Button or twist-lock photocell, motion response, and field adjustable wattage

Stock ready

Design ready

Stonco



## Garage & Canopy

- IP65 rated luminaire
- Die-cast round housing protect LEDs and driver
- DLC Premium
- 10kV surge protection
- 120-347V

Stock ready

Stonco



## Wall Pack

- Equipped with an integrated Daylight Sensor
- Rugged robust design
- Uniform illumination
- IP65 rated luminaire
- Die-cast housings protect LEDs and drivers

Stock ready


Stonco



## SlimFlood DualSelect

- Can be mounted on the ground, wall, or pole
- Field selectable CCT of 3000K-5000K
- 7 housings and 4 sizes available
- IP65 rated, 5-year limited warranty

Stock ready



**Day-Brite**



### VTS Sealed Strip

- Field selectable CCT & lumen options
- Durable construction
- Simple mounting method
- Convenient specification
- Ease of installation and maintenance
- Simple form

Stock  
ready

 **GARDCO**



### QuickShip Poles

- Gardco straight round steel (SRS) or straight square steel (SSS) pole configurations

Design  
ready



# Get started with the Design Ready catalog



## Ready to create your vision?

Check out the Design Ready website and catalog for ordering information on the product families fit for bringing your Design Build project to life. Scan the QR code to learn more.







**GENLYTE**  
SOLUTIONS

საქართველო

საქართველო



**GENLYTE**  
**SOLUTIONS**  
a  Signify business

© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation  
400 Crossing Blvd, Suite 600  
Bridgewater, NJ 08807  
Telephone 800-555-0500

Signify Canada Ltd.  
281 Hillmount Road,  
Markham, ON, Canada L6C 2S3  
Telephone 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.